

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00						
			W1	REVISED PER ECO-11-004820	11MAR11	RK	HMR

- 1

0.00203 [.000080] MIN BRIGHT TIN-LEAD OVER
0.00127 [.000050] MIN NICKEL.
- 2

0.00330 [.000130] MAX PRE-TIN.
- 3




0.00013 [.000005] GOLD OVER 0.00127 [.000050]
MIN NICKEL ALL OVER AND 0.00076 [.000030] MIN
GOLD ON CONTACT AREA.
- 4

WIRE RANGE: 0.2-0.9mm² (24-18 AWG).
INSULATION RANGE: 2.79 [.110] DIA MAX.
- 5


DIMENSIONS IN BRACKETS ARE IN INCHES.

- 6


0.00203 [.000080] MIN BRIGHT TIN OVER
0.00127 [.000050] MIN NICKEL.




SECTION D-D
SCALE 10:1



SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1



SECTION C-C
SCALE 10:1

MINI	SEE 3-640706-1	6	3-640252-1
MINI	SEE 640706-2	2	640252-2
MINI	SEE 640706-1	1	640252-1
APPLICATOR	LOOSE PIECE	FINISH	PART NO

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 21AUG2003	TE Connectivity			
DIMENSIONS: INCHES		CHK J. ELLIS 21AUG2003				
		APVD J. ELLIS 21AUG2003	NAME RECEPTACLE, SL-156			
		PRODUCT SPEC				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC				
0 PLC ± 1 PLC ± 2 PLC ± 0.13 [.005] 3 PLC ± 4 PLC ±		WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C-640252	RESTRICTED TO -
MATERIAL 0.33 [.013] BRASS		FINISH SEE TABLE	CUSTOMER DRAWING			
			SCALE 5:1	SHEET 1 of 1	REV W1	