

Messrs. Rockwell Automation Co.,Ltd.

SPECIFICATION

Device Name : IGBT

Type Name : 1MBH20D-060-S06TT

Spec. No. : MS5F-4086

Date : June-11-1998

This material and the information herein is the property of Fuji Electric Co.,Ltd. They shall be neither reproduced, copied, loaned, or disclosed in any way whatsoever for the use of any third party nor used for the manufacturing purposes without the express written consent of Fuji Electric Co.,Ltd.

Fuji Electric Co.,Ltd.
Matsumoto Factory

	DATE	NAME	APPROVED	Fuji Electric Co.,Ltd.	
DRAWN	June-11-98	K. Asada		DWG. NO.	MS5F4086
CHECKED	June-11-98	T. Igarashi			

Revised Records

[illegible]

This material and the information herein is the property of Fuji Electric Co. Ltd. They shall be neither reproduced, copied, lent, or disclosed in any way whatsoever for the use of any third party nor used for the manufacturing purposes without the express written consent of Fuji Electric Co. Ltd.

• Scope

This specification is applied to Fuji discrete IGBT 1MBH200-060
supplied for Rockwell Automation Co., Ltd.

• Construction

1. Package dimension
There is a package dimension in 4/14 page .
2. Outview
There are no remarkable flaws on a product .
3. Indication
 - ① Trademark
 - ② Type Name
 - ③ Lot No.

• Ratings and Characteristics

1. There are some ratings and characteristics tables in 4/14 page and 5/14 page .
2. There are some performance curves in from 6/14 page to 14/14 page .

• Packing

Packing style follows our packing specification ~~MS500026~~.



MS5G CC3C (A)

This material and the information herein is the property of
Fuji Electric Co. Ltd. They shall be neither reproduced, copied,
lent, or disclosed in any way whatsoever for the use of any
third party nor used for the manufacturing purposes without
the express written consent of Fuji Electric Co., Ltd.

Ratings and characteristics of Fuji IGBT

1MBH20D-060


1. Outline Drawing



CONNECTION

- ① GATE
- ② COLLECTOR
- ③ EMITTER

2. Equivalent circuit



3. Absolute maximum ratings (Tc=25°C)

Items			Symbols	Ratings	Units
Collector-Emitter Voltage			V_{CES}	600	V
Gate-Emitter Voltage			V_{GES}	±22	V
Collector Current	DC	Tc=25 °C	I_{C25}	45	A
		Tc=110°C	I_{C110}	20	A
	1ms	Tc=25 °C	I_{cp}	152	A
IGBT Max. Power Dissipation			P_c	170	W
FWD Max. Power Dissipation			P_c	95	W
Operating Temperature			T_j	+ 150	°C
Storage Temperature			T_{stg}	-40 ~ +150	°C
Mounting Screw Torque			—	70	N · cm

4. Electrical Characteristics (at $T_c=25^{\circ}\text{C}$ unless otherwise specified)


Items		Symbols	Characteristics			Conditions	Unit
			min.	typ.	max.		
Zero gate voltage Collector Current		I_{CES}			1.0	$V_{GE} = 0V$ $V_{CE} = 600V$	mA
Gate-Emitter leakage Current		I_{GES}			20	$V_{CE} = 0V$ $V_{GE} = \pm 22V$	μA
Gate-Emitter Threshold Voltage		$V_{GE(th)}$	5.5		8.5	$V_{CE} = 20V$ $I_C = 20mA$	V
Collector-Emitter Saturation Voltage		$V_{CE(sat)}$			3.0	$V_{GE} = 15V$ $I_C = 20A$	V
Input capacitance		C_{ies}		1300		$V_{GE} = 0V$	pF
Output capacitance		C_{oes}		300		$V_{CE} = 10V$	
Reverse transfer capacitance		C_{res}		70		$f = 1MHz$	
Switching Time	Turn-on time	t_{on}			1.2	$V_{CC} = 300V$ $I_C = 20A$ $V_{GE} = \pm 15V$ $R_G = 120\Omega$ (Half Bridge)	μs
		t_r			0.6		
	Turn-off time	t_{off}			1.0		
		t_f			0.35		
	Turn-on time	t_{on}		0.16		$V_{CC} = 300V$ $I_C = 20A$ $V_{GE} = \pm 15V$ $R_G = 12\Omega$ (Half Bridge)	
		t_r		0.11			
	Turn-off time	t_{off}		0.30			
		t_f			0.35		
FWD forward voltage drop		V_F			3.0	$I_F = 20A$	V
Reverse recovery time		t_{rr}			0.3	$I_F=20A, V_{GE}=-10V$ $V_R= 200V$ $di/dt=100A/\mu s$	μs

5. Thermal resistance characteristics

Items	Symbols	Characteristics			Conditions	Unit
		min.	typ.	max.		
Thermal resistance	$R_{th(j-c)}$			0.73	IGBT	$^{\circ}\text{C}/\text{W}$
	$R_{th(j-c)}$			1.31	FWD	


This material and the information herein is the property of Fuji Electric Co. Ltd. They shall be neither reproduced, copied, lent, or disclosed in any way whatsoever for the use of any third party nor used for the manufacturing purposes without the express written consent of Fuji Electric Co. Ltd.

Collector Current vs. Collector-Emitter Voltage
 $T_j = 125^\circ\text{C}$



Collector-Emitter Voltage : V_{CE} [V]

Collector Current vs. Collector-Emitter Voltage
 $T_j = 25^\circ\text{C}$



Collector-Emitter Voltage : V_{CE} [V]

Fuji Electric Co., Ltd.


DWG NO.

MS5F4086


6/14

Top electric Co., Ltd. hereby grants permission to reproduce all, copied
 lent, or disclosed in any way whatsoever for the use of any
 third party or used for the manufacturing purposes without
 the express written consent of Fuji Electric Co., Ltd.

Collector-Emitter Voltage vs Gate-Emitter Voltage
 $T_j = 25^\circ\text{C}$




Collector-Emitter Voltage vs Gate-Emitter Voltage
 $T_j = 125^\circ\text{C}$



This material and the information herein is the property of Fuji Electric Co. Ltd. They shall be neither reproduced, copied, lent, or distributed in any way whatsoever for the use of any third party nor used for the manufacturing purposes without the express written consent of Fuji Electric Co. Ltd.


Switching time vs. Collector current

$V_{cc}=300V$, $R_G=12\Omega$, $V_{GE}=\pm 15V$, $T_j=25^\circ C$



Switching time vs. Collector current

$V_{cc}=300V$, $R_G=12\Omega$, $V_{GE}=\pm 15V$, $T_j=125^\circ C$



Fuji Electric Co., Ltd.

DWG NO.


MS5F4086

7/14


H04-004-03

This material and the information herein is the property of Fuji Electric Co. Ltd. They shall be neither reproduced, copied, lent, or disclosed in any way whatsoever for the use of any third party nor used for the manufacturing purposes without the express written consent of Fuji Electric Co. Ltd.

Switching time vs. RG
 $V_{ce}=300V$, $I_C=20A$, $V_{GE}=\pm 15V$, $T_j=25^\circ C$




Switching time vs. RG
 $V_{ce}=300V$, $I_C=20A$, $V_{GE}=\pm 15V$, $T_j=125^\circ C$




This material and the information herein is the property of Fuji Electric Co. Ltd. They shall be neither reproduced, copied, lent, or disclosed in any way whatsoever for the use of any third party nor used for the manufacturing purposes without the express written consent of Fuji Electric Co. Ltd.

Dynamic input characteristics

$T_j = 25^\circ\text{C}$



Capacitance vs. Collector-Emitter voltage $T_j = 25^\circ\text{C}$



Fuji Electric Co., Ltd.

DWG NO.


MS5F4086

10/14


H04-004-03

This data sheet contains the information that is the property of
 Fuji Electric Co. Ltd. It shall be neither reproduced, copied
 nor disclosed in any way whatsoever for the use of any
 third party nor used for the manufacturing purposes without
 the express written consent of Fuji Electric Co. Ltd.

Reverse Biased Safe Operating Area
 $-V_{GE} = -15V, -V_{GE} \leq 15V, T_j \leq 125^\circ C, R_G \geq 12\Omega$



Typical short circuit capability
 $V_{CC} = 400V, R_G = 12\Omega, T_j = 125^\circ C$



Fuji Electric Co., Ltd.

DWG.NO.


MS5F4086

11/14


H04-004-03

This material and the information herein is the property of Fuji Electric Co. Ltd. They shall be neither reproduced, copied, lent, or disclosed in any way whatsoever for the use of any third party nor used for the manufacturing purposes without the express written consent of Fuji Electric Co. Ltd.

Reverse recovery time vs. Forward current
VR=200V, $-di/dt=100A/\mu sec$



Reverse recovery current vs. Forward current
VR=200V, $-di/dt=100A/\mu sec$



Fuji Electric Co., Ltd.

DWG. NO.


MS5F4086

12/14


H04-004-03

This material and the information herein is the property of Fuji Electric Co. Ltd. They shall be neither reproduced, copied, lent, or disclosed in any way whatsoever for the use of any third party nor used for the manufacturing purposes without the express written consent of Fuji Electric Co., Ltd.

Forward voltage vs. Forward current



Reverse recovery characteristics vs. $-di/dt$
 $I_F = 20\text{A}$, $T_j = 125^\circ\text{C}$



Fuji Electric Co., Ltd.


DWG. NO.

MS5F4036

11/14

H04-004-03

Transient thermal resistance



This material and the information herein is the property of Fuji Electric Co., Ltd. They shall be neither reproduced, copied, lent, or disclosed in any way whatsoever for the use of any third party nor used for the manufacturing purposes without the express written consent of Fuji Electric Co., Ltd.

Fuji Semiconductor, Inc. - P.O. Box 702708 - Dallas, TX 75370 - 972-733-1700
www.fujisemiconductor.com

Fuji Electric Co., Ltd.

DWG. NO.

MS5F4086

14/14

H04-004-03