








MATERIAL NUMBER	NUMBERS OF PORTS	DIM -C-	DIM -D-	SEE NOTE
85586-1005	6/6	4.0/0.157	3.8/0.150	12

PATENTS PENDING

NOTES:




- 1- SHIELD MATERIAL: BRASS, PLATING: NICKEL
- 2- HOUSING MATERIAL: THERMOPLASTIC UL 94-V0, COLOR BLACK
- 3- TERMINAL: PHOSPHOR BRONZE
- 4- JACK TO BE MATCHED WITH F.C.C. 68.5 PLUGS (MOLEX-PLUGS: 85568,95043,90075-SERIES)
- 5- PRODUCT SPECIFICATION: PS-85586-001
- 6- PLEASE REQUEST MOLEX FOR A FRENCH INSTALLATION MANUAL IF DISTRIBUTED IN CANADA.
- 7- RECOMMENDED PCB LAYOUT AND PANEL CUT OUT SEE SHEET 2 AND 3
- 8- NO TRACES WITHOUT INSULATION ALLOWED ON BOARD PCB IN THIS DASHED AREAS UNDER THE METAL SHIELD
- 9- PIN LENGTH FOR RECOMMENDED PCB MAX. THICKNESS OF .140" REFER TO STANDARD IPC 610 REVISION C, CLASS 2
- 10- STAND-OFF PLANE TO CUSTOMER PCB
- 11- PACKAGING SPECIFICATION: PK-85586-001

EC NO: MG2010-0061		2012/08/07		QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
DRWN: JBADER		2012/08/07				mm INCH			DRAWN BY DATE		TITLE				
CHKD: MWANGARUDOV		2012/08/07				4 PLACES ± --- ± ---			RSCHIEBER 2005/12/08		HYPERJACK 1000 POE-MODULE WITH POWER OVER PIN (POP), SWAPPED PORTS				
APPR: SSTEINKE		2012/12/04				3 PLACES ± --- ± .006			CHECKED BY DATE						
REV: A						2 PLACES ± .15 ± .01			SSTEINKE 2005/12/08						
				1 PLACE ± .25 ± ---			APPROVED BY DATE		MOLEX MOLEX INCORPORATED						
				ANGULAR ± .5 °			AVOGT 2005/12/08								
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		DOCUMENT NO.		SHEET NO.				
							SEE CHART		SD-85586-012		1 OF 3				
						SIZE A2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							



PATENTS PENDING

EC NO: ME2010-0061 DRWN: BADER 2012/08/07 CHKD: MANGARUDOV 2012/08/07 APPR: SSTEINKE 2012/12/04 A	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
		=0 =0	mm	INCH	MM/IN		2:1	METRIC			
		4 PLACES ± --- ± ---	RSCHIEBER	2005/12/08	TITLE HYPERJACK 1000 POE-MODULE WITH POWER OVER PIN (POP), SWAPPED PORTS						
		3 PLACES ± --- ± .001	CHECKED BY	DATE							
		2 PLACES ± 0.15 ± .01	SSTEINKE	2005/12/08							
		1 PLACE ± 0.25 ± ---	APPROVED BY	DATE							
		ANGULAR ± .5 °		AVOGT	2005/12/08	MOLEX INCORPORATED					
				MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 1		SD-85586-012		2 OF 3			
				SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
		A2									



NOTES:

- 1 - MOLEX LOGO, TUV LOGO AND INSCRIPTION TO BE MARKED WITH LASER PRINTER
- 2 - INSCRIPTION:
 - 1st LINE: PART NAME
 - 2nd LINE: PART NUMBER
 - 3rd LINE: SERIES NUMBER -> MANUFACTURER ID - CONNECTOR REVISION - DATE CODE (YEAR, MONTH, DAY) - CONSECUTIVE NUMBER
 - 4th LINE: COUNTRY OF ORIGIN

PATENTS PENDING

EC NO: MG2010-0061 DRWN: JBADER 2012/08/07 CHKD: MWANGARDONOV 2012/08/07 APPR: SSTE INKE 2012/12/04 A	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION ⊙ □						
				mm	INCH	DRAWN BY RSCHIEBER	DATE 2005/12/08	HYPERJACK 1000 POE-MODULE WITH POWER OVER PIN (POP), SWAPPED PORTS MOLEX MOLEX INCORPORATED							
			4 PLACES	± ---	± ---	CHECKED BY	DATE								
			3 PLACES	± ---	± .006	SSTE INKE	2005/12/08								
			2 PLACES	± 0.15	± .01	APPROVED BY	DATE								
			1 PLACE	± 0.25	± ---	AVOGT	2005/12/08								
			ANGULAR ± .5 °			MATERIAL NO.		DOCUMENT NO.		SHEET NO.					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE SHEET 1		SD-85586-012		3 OF 3					
						SIZE A2					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				