

Product Summary



BV_{DSS}	$R_{DS(ON)} \text{ max}$	$I_D \text{ max}$ $T_A = +25^\circ\text{C}$
60V	1.8Ω @ $V_{GS} = 5\text{V}$	630mA
	2.4Ω @ $V_{GS} = 3\text{V}$	

Description and Applications

DMN61D8LVTQ provides a single component solution for switching inductive loads such as relays, solenoids, and small DC motors in automotive applications, without the need of a freewheeling diode. DMN61D8LVTQ accepts logic level inputs, thus allowing it to be driven by logic gates, inverters and microcontrollers. It is ideally suited for door, window and antenna relay coils.


TSOT26


Top View



Equivalent Circuit


Ordering Information (Note 5)

Part Number	Case	Packaging
DMN61D8LVTQ-7	TSOT26	3,000/Tape & Reel
DMN61D8LVTQ-13	TSOT26	10,000/Tape & Reel

Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
2. See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
4. Automotive products are AEC-Q101 qualified and are PPAP capable. Refer to http://www.diodes.com/product_compliance_definitions.html.
5. For packaging details, go to our website at <http://www.diodes.com/products/packages.html>.

Marking Information



1D8 = Product Type Marking Code
 YM = Date Code Marking
 Y = Year (ex: D = 2016)
 M = Month (ex: 9 = September)

Date Code Key

Year	2016	2017	2018	2019	2020	2021	2022					
Code	D	E	F	G	H	I	J					
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	O	N	D

Maximum Ratings (@ $T_A = +25^\circ\text{C}$, unless otherwise specified.)

Characteristic			Symbol	Value	Units
Drain-Source Voltage			V_{DSS}	60	V
Gate-Source Voltage			V_{GSS}	± 12	V
Continuous Drain Current (Note 7)	Steady State	$T_A = +25^\circ\text{C}$ $T_A = +70^\circ\text{C}$	I_D	630 500	mA
Maximum Continuous Body Diode Forward Current (Note 7)			I_S	0.5	A
Single Pulse Drain-to-Source Avalanche Energy (For Relay's Coils/Inductive Loads of 80Ω or Higher) (T_J Initial = $+85^\circ\text{C}$)			E_Z	200	mJ
Peak Power Dissipation, Drain-to-Source (Non repetitive current square pulse 1.0ms duration) (T_J Initial = $+85^\circ\text{C}$)			PPK	20	W
Load Dump Pulse, Drain-to-Source, $R_{\text{SOURCE}} = 0.5\Omega$, $t = 300\text{ms}$ (For Relay's Coils/Inductive Loads of 80Ω or Higher) (T_J Initial = $+85^\circ\text{C}$)			ELD1	60	V
Inductive Switching Transient 1, Drain-to-Source (Waveform: $R_{\text{SOURCE}} = 10\Omega$, $t = 2.0\text{ms}$) (For Relay's Coils/Inductive Loads of 80Ω or Higher) (T_J Initial = $+85^\circ\text{C}$)			ELD2	100	V
Inductive Switching Transient 2, Drain-to-Source (Waveform: $R_{\text{SOURCE}} = 4.0\Omega$, $t = 50\mu\text{s}$) (For Relay's Coils/Inductive Loads of 80Ω or Higher) (T_J Initial = $+85^\circ\text{C}$)			ELD3	300	V
Reverse Battery, 10 Minutes (Drain-to-Source) (For Relay's Coils/Inductive Loads of 80Ω or more)			Rev-Bat	-14	V
Dual Voltage Jump Start, 10 Minutes (Drain-to-Source)			Dual-Volt	28	V
ESD Human Body Model (HBM)			ESD	4,000	V

Thermal Characteristics (@ $T_A = +25^\circ\text{C}$, unless otherwise specified.)

Characteristic		Symbol	Value	Units
Total Power Dissipation (Note 6)		P_D	820	mW
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	$R_{\theta JA}$	154	$^\circ\text{C}/\text{W}$
Total Power Dissipation (Note 7)		P_D	1,090	mW
Thermal Resistance, Junction to Ambient (Note 7)	Steady State	$R_{\theta JA}$	116	$^\circ\text{C}/\text{W}$
Operating and Storage Temperature Range		T_J, T_{STG}	-55 to +150	$^\circ\text{C}$

Notes: 6. Device mounted on FR-4 PCB, with minimum recommended pad layout.

7. Device mounted on 1" x 1" FR-4 PCB with high coverage 2oz. copper, single sided.

Electrical Characteristics (@ $T_A = +25^\circ\text{C}$, unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 8)						
Drain-Source Breakdown Voltage	BV_{DSS}	60	—	—	V	$\text{V}_{\text{GS}} = 0\text{V}$, $\text{I}_D = 10\text{mA}$
Zero Gate Voltage Drain Current	I_{DSS}	—	—	50 0.5	μA	$\text{V}_{\text{DS}} = 60\text{V}$, $\text{V}_{\text{GS}} = 0\text{V}$ $\text{V}_{\text{DS}} = 12\text{V}$, $\text{V}_{\text{GS}} = 0\text{V}$
Gate-Source Leakage	I_{GSS}	—	—	± 90 ± 60	μA	$\text{V}_{\text{GS}} = \pm 5\text{V}$, $\text{V}_{\text{DS}} = 0\text{V}$ $\text{V}_{\text{GS}} = \pm 3\text{V}$, $\text{V}_{\text{DS}} = 0\text{V}$
ON CHARACTERISTICS (Note 8)						
Gate Threshold Voltage	$\text{V}_{\text{GS}(\text{TH})}$	1.3	—	2.0	V	$\text{V}_{\text{DS}} = \text{V}_{\text{GS}}$, $\text{I}_D = 1\text{mA}$
Static Drain-Source On-Resistance	$\text{R}_{\text{DS}(\text{ON})}$	—	1.1 1.4	1.8 2.4	Ω	$\text{V}_{\text{GS}} = 5\text{V}$, $\text{I}_D = 0.15\text{A}$ $\text{V}_{\text{GS}} = 3\text{V}$, $\text{I}_D = 0.15\text{A}$
Forward Transfer Admittance	$ \text{Y}_{\text{fs}} $	80	—	—	ms	$\text{V}_{\text{DS}} = 12\text{V}$, $\text{I}_D = 0.15\text{A}$
Diode Forward Voltage	V_{SD}	—	—	1.2	V	$\text{V}_{\text{GS}} = 0\text{V}$, $\text{I}_s = 0.15\text{A}$
DYNAMIC CHARACTERISTICS (Note 9)						
Input Capacitance	C_{iss}	—	12.9	—	pF	$\text{V}_{\text{DS}} = 12\text{V}$, $\text{V}_{\text{GS}} = 0\text{V}$ $f = 1.0\text{MHz}$
Output Capacitance	C_{oss}	—	17	—	pF	
Reverse Transfer Capacitance	C_{rss}	—	0.84	—	pF	
Total Gate Charge	Q_{g}	—	0.74	—	nC	
Gate-Source Charge	Q_{gs}	—	0.19	—	nC	$\text{V}_{\text{GS}} = 5\text{V}$, $\text{V}_{\text{DS}} = 12\text{V}$, $\text{I}_D = 150\text{mA}$
Gate-Drain Charge	Q_{gd}	—	0.16	—	nC	$\text{V}_{\text{DD}} = 12\text{V}$, $\text{V}_{\text{GS}} = 5\text{V}$
Turn-On Delay Time	$\text{t}_{\text{D}(\text{ON})}$	—	131	—	ns	
Turn-On Rise Time	t_{R}	—	301	—	ns	
Turn-Off Delay Time	$\text{t}_{\text{D}(\text{OFF})}$	—	582	—	ns	
Turn-Off Fall Time	t_{F}	—	440	—	ns	

Notes: 8. Short duration pulse test used to minimize self-heating effect.

9. Guaranteed by design. Not subject to product testing.




Figure 1 Typical Output Characteristic














Figure 2 Typical Transfer Characteristics






Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

TSOT26




TSOT26			
Dim	Min	Max	Typ
A	—	1.00	—
A1	0.010	0.100	—
A2	0.840	0.900	—
D	2.800	3.000	2.900
E	2.800 BSC		
E1	1.500	1.700	1.600
b	0.300	0.450	—
c	0.120	0.200	—
e	0.950 BSC		
e1	1.900 BSC		
L	0.30	0.50	—
L2	0.250 BSC		
θ	0°	8°	4°
θ1	4°	12°	—

All Dimensions in mm

Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

TSOT26



Dimensions	Value (in mm)
C	0.950
X	0.700
Y	1.000
Y1	3.199

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2016, Diodes Incorporated

www.diodes.com