


DESCRIPTION: HIGH PROFILE FEMALE CONNECTOR



SPECIFICATIONS:


MATERIALS:

SHELL: STEEL, TIN OR YELLOW CHROMATE PLATED
 INSULATOR: UL 94V-0 RATED PBT
 +30% FIBER-GLASS OR NYLON-66


ELECTRICALS:

CURRENT RATING: 5 AMPS
 CONTACT RESISTANCE: 15 mOHMS MAX
 INSULTOR RESISTANCE: 1000 MOHMS MIN
 VOLTAGE: 500V AC FOR 1 MINUTE
 TEMPERATURE: -50°C TO +100°C

POS.	A	B	C	D	E	F	G
09	1.213	0.984	0.642	0.436	0.311	0.109	0.496
	30.80	24.99	16.30	11.07	7.90	2.77	12.60
15	1.541	1.312	0.971	0.763	0.311	0.109	0.496
	39.14	33.32	24.65	19.38	7.90	2.77	12.60
25	2.087	1.852	1.512	1.308	0.311	0.109	0.496
	53.00	47.04	38.40	33.22	7.90	2.77	12.60
37	2.728	2.500	2.157	1.962	0.311	0.109	0.496
	69.29	63.50	54.80	49.83	7.90	2.77	12.60
50	2.079	2.406	2.055	1.744	0.429	0.109	0.602
	52.81	61.00	52.20	44.32	10.90	2.77	15.30



(9, 15, 25, 37 POSITIONS)



(50 POSITION)

SERIES _____
 POSITIONS _____
 009
 015
 025
 037
 050
 GENDER _____
 1 = MALE
 2 = FEMALE
 TERMINATION _____
 8 = HIGH PROFILE VERTICAL
 SHELL PLATING _____
 1 = YELLOW CHROMATE
 2 = TIN
 HARDWARE OPTIONS _____
 00 = NO HARDWARE
 01 = .065 4-40 CLINCH NUT BOARD SIDE
 02 = .250 4-40 CLINCH NUT BOARD SIDE
 03 = .250 4-40 CLINCH NUT MATING SIDE
 PLATING OPTIONS _____
 01 = GOLD FLASH



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

NorComp

DRAWN: WAYNE ROBBINS		DATE: 8-23-98	
CHECKED: PAM JENKINS		DATE: 8-24-98	
SCALE:	SHEET 1	OF 1	REV 5
DWG NO. 172-XXX-28X-XX1			