




Features

- ✧ UL Recognized File # E-96005
- ✧ Glass passivated junction
- ✧ Ideal for printed circuit board
- ✧ Reliable low cost construction
- ✧ Plastic material has Underwriters Laboratory Flammability Classification 94V-0
- ✧ Surge overload rating to 175 amperes peak
- ✧ High temperature soldering guaranteed: 260°C / 10 seconds / .375" (9.5mm) lead lengths at 5 lbs., (2.3kg) tension
- ✧ Weight: 0.3 ounce, 8.0 grams
- ✧ Mounting torque: 5 in. lb. max.
- ✧ Green compound with suffix "G" on packing code & prefix "G" on datecode.

KBU601G - KBU607G


Single Phase 6.0 AMPS.
Glass Passivated Bridge Rectifiers

KBU



Dimensions in inches and (millimeters)

Marking Diagram



KBU60XG = Specific Device Code
G = Green Compound
Y = Year
WW = Work Week

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	KBU 601G	KBU 602G	KBU 603G	KBU 604G	KBU 605G	KBU 606G	KBU 607G	Units
Maximum Recurrent Peak Reverse Voltage	VRRM	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	VRMS	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	VDC	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current @T _A = 65 °C	I(AV)	6.0							A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	IFSM	175							A
Maximum Instantaneous Forward Voltage @ 3.0A @ 6.0A	V _F	1.0 1.1							V
Maximum DC Reverse Current @ T _A =25 °C at Rated DC Blocking Voltage @ T _A =125 °C	I _R	5.0 500							uA uA
Typical Thermal resistance (Note 1) (Note 2)	R _{θJA} R _{θJC}	8.6 3.1							°C/W
Operating Temperature Range	T _J	-55 to +150							°C
Storage Temperature Range	T _{STG}	-55 to + 150							°C

- Notes:
1. Thermal resistance from Junction to Ambient with units in Free Air, P.C.B. Mounted on 0.5" x 0.5" (12mm x 12mm) Copper Pads, 0.375" (9.5mm) Lead Length.
 2. Thermal Resistance from Junction to Case with units Mounted on 2" x 3" x 0.25" Al-Plate.

RATINGS AND CHARACTERISTIC CURVES (KBU601G THRU KBU607G)

FIG.1- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.2- TYPICAL REVERSE CHARACTERISTICS PER BRIDGE ELEMENT




FIG.3- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT PER BRIDGE ELEMENT




FIG.4- TYPICAL JUNCTION CAPACITANCE




FIG.5- TYPICAL FORWARD CHARACTERISTICS PER BRIDGE ELEMENT

