


Power Schottky Rectifier with common cathode


Preliminary Data

$$\begin{aligned} I_{FAV} &= 2 \times 8 \text{ A} \\ V_{RRM} &= 100 \text{ V} \\ V_F &= 0.62 \text{ V} \end{aligned}$$

V_{RSM} V	V_{RRM} V	Type
100	100	DSSK 16-01C



TO-220 AB



A = Anode, C = Cathode, TAB = Cathode

Symbol	Test Conditions	Maximum Ratings	
I_{FRMS}		35	A
I_{FAV}	$T_C = 165^\circ\text{C}$; rectangular, $d = 0.5$	8	A
I_{FAV}	$T_C = 165^\circ\text{C}$; rectangular, $d = 0.5$; per device	16	A
I_{FSM}	$T_{VJ} = 45^\circ\text{C}$; $t_p = 10 \text{ ms}$ (50 Hz), sine	120	A
E_{AS}	$I_{AS} = 8 \text{ A}$; $L = 180 \mu\text{H}$; $T_{VJ} = 25^\circ\text{C}$; non repetitive	tbd	mJ
I_{AR}	$V_A = 1.5 \cdot V_{RRM}$ typ.; $f = 10 \text{ kHz}$; repetitive	tbd	A
$(dv/dt)_{cr}$		5000	V/ μs
T_{VJ}		-55...+175	$^\circ\text{C}$
T_{VJM}		175	$^\circ\text{C}$
T_{stg}		-55...+150	$^\circ\text{C}$
P_{tot}	$T_C = 25^\circ\text{C}$	90	W
M_d	mounting torque	0.4...0.6	Nm
Weight	typical	2	g

Features

- International standard package
- Very low V_F
- Extremely low switching losses
- Low I_{RM} -values
- Epoxy meets UL 94V-0

Applications

- Rectifiers in switch mode power supplies (SMPS)
- Free wheeling diode in low voltage converters

Advantages

- High reliability circuit operation
- Low voltage peaks for reduced protection circuits
- Low noise switching
- Low losses

Symbol	Test Conditions	Characteristic Values	
		typ.	max.
I_R ①	$T_{VJ} = 25^\circ\text{C}$; $V_R = V_{RRM}$ $T_{VJ} = 125^\circ\text{C}$; $V_R = V_{RRM}$		0.3 mA 20 mA
V_F	$I_F = 8 \text{ A}$; $T_{VJ} = 125^\circ\text{C}$ $I_F = 8 \text{ A}$; $T_{VJ} = 25^\circ\text{C}$ $I_F = 16 \text{ A}$; $T_{VJ} = 125^\circ\text{C}$		0.62 V 0.79 V 0.73 V
R_{thJC} R_{thCH}	0.5		1.7 K/W K/W

Pulse test: ① Pulse Width = 5 ms, Duty Cycle < 2.0 %
Data according to IEC 60747 and per diode unless otherwise specified

Dimensions see IXYS Databook 2001

IXYS reserves the right to change limits, test conditions and dimensions.

IXYS Semiconductor GmbH
Edisonstr. 15, D-68623 Lampertheim
Phone: +49-6206-503-0, Fax: +49-6206-503627

1 - 1

© 2002 IXYS All rights reserved

IXYS Corporation
3540 Bassett Street, Santa Clara CA 95054
Phone: (408) 982-0700, Fax: 408-496-0670

204