

AS85049/49-2 and MS27506 Straight Strain Relief Self-Locking or Non-Self-Locking



CONNECTOR DESIGNATOR:

F MIL-DTL-27599,
MIL-DTL-38999 Series I & II

Basic
Part Number

Dash No.

M85049/49-2

S

10



W

**FOR NEW DESIGN
USE AS85049/121**

S = Self-Locking
Use Dash for Non-Self-Locking
N = Non-Detented

Material and Finish Designator

A = Aluminum, Black Anodize
N = Aluminum, Electroless Nickel
S = 300 Series Steel, Passivated
W = Aluminum, 1000 Hour Cadmium
Olive Drab over Electroless Nickel



Note: Screw orientation shown is for non-self-locking configuration. Screws on self-locking configurations are on the same side/face of the clamp.

TABLE I: Shell Size, Cable Entry and Backshell Dimensions

Shell Size	Shell Size Ref.	A Thread Class 2B	Ø E Max Self-Locking Only	F Max Self-Locking Only	H Max	Cable Entry			
						Min		Max	
8	8/9	.438 - 28 UNEF	.86 (21.8)	.91 (23.1)	.85 (21.6)	.098 (2.5)	.234 (5.9)		
10	10/11	.562 - 24 UNEF	.98 (24.9)	.91 (23.1)	.90 (22.9)	.153 (3.9)	.234 (5.9)		
12	12/13	.688 - 24 UNEF	1.16 (29.5)	1.01 (25.7)	1.10 (27.9)	.190 (4.8)	.328 (8.3)		
14	14/15	.813 - 20 UNEF	1.28 (32.5)	1.06 (26.9)	1.15 (29.2)	.260 (6.6)	.457 (11.6)		
16	16/17	.938 - 20 UNEF	1.41 (35.8)	1.16 (29.5)	1.30 (33.0)	.283 (7.2)	.614 (15.6)		
18	18/19	1.063 - 18 UNEF	1.52 (38.6)	1.41 (35.8)	1.50 (38.1)	.325 (8.3)	.634 (16.1)		
20	20/21	1.188 - 18 UNEF	1.64 (41.7)	1.51 (38.4)	1.60 (40.6)	.343 (8.7)	.698 (17.7)		
22	22/23	1.313 - 18 UNEF	1.77 (45.0)	1.66 (42.2)	1.70 (43.2)	.381 (9.7)	.823 (20.9)		
24	24/25	1.438 - 18 UNEF	1.89 (48.0)	1.76 (44.7)	1.80 (45.7)	.418 (10.6)	.853 (21.7)		

APPLICATION NOTES

1. Assembly to be identified with manufacturer's name and part number, space permitting.
2. Cable Entry is defined as the accommodation entry for the wire bundle or cable. Dimensions are not intended for inspection criteria.
3. For complete dimensions, see the applicable Military Specification.
4. Metric dimensions (mm) are in parentheses.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[M85049/49-2S10N](#) [M85049/49-2-12A](#) [M85049/49-2-20A](#) [M85049/49-2-10A](#) [M85049/49-2-10N](#) [M85049/49-2-10W](#)
[M85049/49-2-12N](#) [M85049/49-2-12W](#) [M85049/49-2-14N](#) [M85049/49-2-14W](#) [M85049/49-2-16N](#) [M85049/49-2-16W](#)
[M85049/49-2-18N](#) [M85049/49-2-18W](#) [M85049/49-2-20N](#) [M85049/49-2-20W](#) [M85049/49-2-22N](#) [M85049/49-2-22W](#)
[M85049/49-2-24N](#) [M85049/49-2-24W](#) [M85049/49-2-8N](#) [M85049/49-2S10W](#) [M85049/49-2S12N](#) [M85049/49-2S12W](#)
[M85049/49-2S14N](#) [M85049/49-2S14W](#) [M85049/49-2S16N](#) [M85049/49-2S18N](#) [M85049/49-2S18W](#) [M85049/49-2S20N](#)
[M85049/49-2S22N](#) [M85049/49-2S22W](#) [M85049/49-2S24N](#) [M85049/49-2S24W](#) [M85049/49-2S8N](#)
[M85049/49-2S8W](#) [MS27506A10-2](#) [MS27506A12-2](#) [MS27506A16-2](#) [MS27506A18-2](#) [MS27506A24-2](#) [MS27506A8-2](#)
[MS27506B10-2](#) [MS27506B12-2](#) [MS27506B14-2](#) [MS27506B16-2](#) [MS27506B18-2](#) [MS27506B20-2](#) [MS27506B24-2](#)
[MS27506B8-2](#) [MS27506C10-2](#) [MS27506C16-2](#) [MS27506F10-2](#) [MS27506F12-2](#) [MS27506F14-2](#) [MS27506F16-2](#)
[MS27506F18-2](#) [MS27506F20-2](#) [MS27506F24-2](#) [MS27506F8-2](#) [M85049/49-2-8W](#) [MS27506B22-2](#) [M85049/49-2S16W](#)
[MS27506A142](#) [M85049/49-2N10A](#) [M85049/49-2N10N](#) [M85049/49-2N10S](#) [M85049/49-2N10W](#) [M85049/49-2N12A](#)
[M85049/49-2N12N](#) [M85049/49-2N12S](#) [M85049/49-2N12W](#) [M85049/49-2N14A](#) [M85049/49-2N14N](#) [M85049/49-2N14S](#)
[M85049/49-2N14W](#) [M85049/49-2N16A](#) [M85049/49-2N16N](#) [M85049/49-2N16S](#) [M85049/49-2N16W](#) [M85049/49-2N18A](#)
[M85049/49-2N18N](#) [M85049/49-2N18S](#) [M85049/49-2N18W](#) [M85049/49-2N20A](#) [M85049/49-2N20N](#) [M85049/49-2N20S](#)
[M85049/49-2N20W](#) [M85049/49-2N22A](#) [M85049/49-2N22N](#) [M85049/49-2N22S](#) [M85049/49-2N22W](#) [M85049/49-2N24A](#)
[M85049/49-2N24N](#) [M85049/49-2N24S](#) [M85049/49-2N24W](#) [M85049/49-2N8A](#) [M85049/49-2N8N](#) [M85049/49-2N8S](#) [M85049/49-2N8W](#)