

Metallized Polyphenylene-Sulphide (PPS) SMD Film Capacitors with Box Encapsulation. Capacitances from 0.01 μF to 2.2 μF . Rated Voltages from 63 VDC to 1000 VDC. Size Codes from 1812 to 6054.

Special Features

- Size codes 1812, 2220, 2824, 4030, 5040 and 6054 with PPS and encapsulated
- Operating temperature up to 140° C
- Self-healing
- Suitable for lead-free soldering
- Low dissipation factor
- Low dielectric absorption
- Very constant capacitance value versus temperature
- According to RoHS 2011/65/EU

Typical Applications

For general applications in high temperature circuits e.g.

- By-pass
- Blocking
- Coupling and decoupling
- Timing
- Filtering
- Oscillating circuits

Construction


Dielectric:

Polyphenylene-sulphide (PPS) film

Capacitor electrodes:

Vacuum-deposited

Internal construction:



Encapsulation:

Solvent-resistant, flame-retardant plastic case, UL 94 V-0

Terminations:

Tinned plates.

Marking:

Box colour: Black.

Electrical Data

Capacitance range: 0.01 μF to 2.2 μF

Rated voltages:

63 VDC, 100 VDC, 250 VDC, 400 VDC, 630 VDC, 1000 VDC

Capacitance tolerances:

$\pm 20\%$, $\pm 10\%$ ($\pm 5\%$ available subject to special enquiry)

Operating temperature range:

-55°C to $+140^\circ\text{C}$

Climatic test category:

55/140/56 in accordance with IEC

Insulation resistance at $+20^\circ\text{C}$:

U_r	U_{test}	$C \leq 0.33 \mu\text{F}$	$0.33 \mu\text{F} < C \leq 2.2 \mu\text{F}$
63 VDC 100 VDC	50 V 100 V	$\geq 1 \times 10^4 \text{ M}\Omega$	$\geq 3000 \text{ sec (M}\Omega \times \mu\text{F)}$
$\geq 250 \text{ VDC}$	100 V	$\geq 3 \times 10^4 \text{ M}\Omega$	$\geq 6000 \text{ sec (M}\Omega \times \mu\text{F)}$

Measuring time: 1 min.

Dissipation factors at $+20^\circ\text{C}$: $\tan \delta$

at f	$C \leq 0.1 \mu\text{F}$	$0.1 \mu\text{F} < C \leq 1.0 \mu\text{F}$	$C > 1.0 \mu\text{F}$
1 kHz	$\leq 15 \times 10^{-4}$	$\leq 20 \times 10^{-4}$	$\leq 20 \times 10^{-4}$
10 kHz	$\leq 25 \times 10^{-4}$	$\leq 25 \times 10^{-4}$	–
100 kHz	$\leq 50 \times 10^{-4}$	–	–

Maximum pulse rise time: for pulses equal to the rated voltage

Capacitance μF	Pulse rise time V/ μsec max. operation/test					
	63 VDC	100 VDC	250 VDC	400 VDC	630 VDC	1000 VDC
0.01 ... 0.022	25/250	25/250	30/300	35/350	40/400	45/450
0.033 ... 0.068	15/150	15/150	20/200	25/250	28/280	32/320
0.1 ... 0.22	10/100	10/100	12/120	15/150	–	–
0.33 ... 0.68	5/50	5/50	6/60	8/80	–	–
1.0 ... 2.2	3/30	3/30	–	–	–	–

Dip Solder Test/Processing

Resistance to soldering heat:

Test Tb in accordance with DIN IEC

60068-2-58/DIN EN 60384-20.

Soldering bath temperature max. 260°C .

Soldering duration max. 5 sec.

Change in capacitance $\Delta C/C < 5\%$.

Soldering process:

Re-flow soldering (see temperature/time graphs page 13).

Packing

Available taped and reeled in blister pack.

Detailed taping information and graphs at the end of the catalogue.

For further details and graphs please refer to Technical Information.

Continuation

General Data

Capacitance	63 VDC/40 VAC*			100 VDC/63 VAC*			250 VDC/160 VAC*		
	Size code	H ± 0.3	Part number	Size code	H ± 0.3	Part number	Size code	H ± 0.3	Part number
0.01 µF	1812 2220	3.0 3.5	SMDIC02100KA00_____ SMDIC02100QA00_____ SMDIC02100TA00_____ SMDIC02100VA00_____	1812 2220	3.0 3.5	SMDID02100KA00_____ SMDID02100QA00_____ SMDID02100TA00_____ SMDID02100VA00_____	2220	3.5	SMDIF02100QA00_____ SMDIF02100TA00_____ SMDIF02100VA00_____
0.015 "	1812 2220	3.0 3.5	SMDIC02150KA00_____ SMDIC02150QA00_____ SMDIC02150TA00_____ SMDIC02150VA00_____	1812 2220	3.0 3.5	SMDID02150KA00_____ SMDID02150QA00_____ SMDID02150TA00_____ SMDID02150VA00_____	2220	3.5	SMDIF02150QA00_____ SMDIF02150TA00_____ SMDIF02150VA00_____
0.022 "	1812 2220	3.0 3.5	SMDIC02220KA00_____ SMDIC02220QA00_____ SMDIC02220TA00_____ SMDIC02220VA00_____	1812 2220	3.0 3.5	SMDID02220KA00_____ SMDID02220QA00_____ SMDID02220TA00_____ SMDID02220VA00_____	2220 2824	3.5 3.0	SMDIF02220QA00_____ SMDIF02220TA00_____ SMDIF02220VA00_____
0.033 "	1812 2220 2824	3.0 3.5 3.0	SMDIC02330KA00_____ SMDIC02330QA00_____ SMDIC02330TA00_____ SMDIC02330VA00_____	1812 2220 2824	3.0 3.5 3.0	SMDID02330KA00_____ SMDID02330QA00_____ SMDID02330TA00_____ SMDID02330VA00_____	2824 4030	3.0 5.0	SMDIF02330QA00_____ SMDIF02330TA00_____ SMDIF02330VA00_____
0.047 "	1812 2220 2824	3.0 3.5 3.0	SMDIC02470KA00_____ SMDIC02470QA00_____ SMDIC02470TA00_____ SMDIC02470VA00_____	1812 2220 2824	3.0 3.5 3.0	SMDID02470KA00_____ SMDID02470QA00_____ SMDID02470TA00_____ SMDID02470VA00_____	2824 4030	5.0 5.0	SMDIF02470TB00_____ SMDIF02470QA00_____ SMDIF02470TA00_____ SMDIF02470VA00_____
0.068 "	1812 2220 2824	3.0 3.5 3.0	SMDIC02680KA00_____ SMDIC02680QA00_____ SMDIC02680TA00_____ SMDIC02680VA00_____	2220 2824	3.5 3.0	SMDID02680QA00_____ SMDID02680TA00_____ SMDID02680VA00_____	2824 4030	5.0 5.0	SMDIF02680TB00_____ SMDIF02680QA00_____ SMDIF02680TA00_____ SMDIF02680VA00_____
0.1 µF	1812 2220 2824	3.0 3.5 3.0	SMDIC03100KA00_____ SMDIC03100QA00_____ SMDIC03100TA00_____ SMDIC03100VA00_____	2220 2824	3.5 3.0	SMDID03100QA00_____ SMDID03100TA00_____ SMDID03100VA00_____	2824 4030 5040	5.0 5.0 6.0	SMDIF03100TB00_____ SMDIF03100QA00_____ SMDIF03100TA00_____ SMDIF03100VA00_____
0.15 "	1812 2220 2824	4.0 3.5 3.0	SMDIC03150KB00_____ SMDIC03150QA00_____ SMDIC03150TA00_____ SMDIC03150VA00_____	2824	3.0	SMDID03150TA00_____ SMDID03150VA00_____	4030 5040 6054	5.0 6.0 7.0	SMDIF03150VA00_____ SMDIF03150QA00_____ SMDIF03150TA00_____ SMDIF03150VA00_____
0.22 "	2220 2824	4.5 5.0	SMDIC03220QB00_____ SMDIC03220TB00_____ SMDIC03220VA00_____	2220 2824	4.5 5.0	SMDID03220QB00_____ SMDID03220TB00_____ SMDID03220VA00_____	4030 5040 6054	5.0 6.0 7.0	SMDIF03220QA00_____ SMDIF03220TB00_____ SMDIF03220VA00_____ SMDIF03220VA00_____
0.33 "	2220 2824 4030	4.5 5.0 5.0	SMDIC03330QB00_____ SMDIC03330TB00_____ SMDIC03330VA00_____ SMDIC03330VA00_____	2824 4030	5.0 5.0	SMDID03330TB00_____ SMDID03330VA00_____ SMDID03330VA00_____	5040 6054	6.0 7.0	SMDIF03330QA00_____ SMDIF03330TB00_____ SMDIF03330VA00_____ SMDIF03330VA00_____
0.47 "	2220 2824 4030	4.5 5.0 5.0	SMDIC03470QB00_____ SMDIC03470TB00_____ SMDIC03470VA00_____ SMDIC03470VA00_____	2824 4030	5.0 5.0	SMDID03470TB00_____ SMDID03470VA00_____ SMDID03470VA00_____	6054	7.0	SMDIF03470QA00_____ SMDIF03470TB00_____ SMDIF03470VA00_____ SMDIF03470VA00_____
0.68 "	2824 4030	5.0 5.0	SMDIC03680TB00_____ SMDIC03680VA00_____ SMDIC03680VA00_____	4030	5.0	SMDID03680VA00_____ SMDID03680VA00_____			
1.0 µF	2824 4030 5040	5.0 5.0 6.0	SMDIC04100TB00_____ SMDIC04100VA00_____ SMDIC04100XA00_____ SMDIC04100XA00_____	5040	6.0	SMDID04100XA00_____ SMDID04100XA00_____			
1.5 "	4030 5040	5.0 6.0	SMDIC04150VA00_____ SMDIC04150XA00_____ SMDIC04150XA00_____	6054	7.0	SMDID04150YA00_____ SMDID04150YA00_____			
2.2 "	6054	7.0	SMDIC04220YA00_____ SMDIC04220YA00_____	6054	7.0	SMDID04220YA00_____ SMDID04220YA00_____			

* AC voltages: $f \leq 400 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_r$
Dims. in mm.

Rights reserved to amend design data without prior notification.

Part number completion:

Tolerance: 20 % = M
10 % = K
5 % = J

Packing: bulk = S

Pin length: none = 00

Taped version see page 148.

Continuation


General Data

Capacitance	400 VDC/200 VAC*			630 VDC/300 VAC*			1000 VDC/400 VAC*		
	Size code	H ± 0.3	Part number	Size code	H ± 0.3	Part number	Size code	H ± 0.3	Part number
0.01 μF				5040	6.0	SMDIJ02100XA00_	5040	6.0	SMDIO12100XA00_
0.015 "				5040	6.0	SMDIJ02150XA00_	5040	6.0	SMDIO12150XA00_
0.022 "	4030 5040	5.0 6.0	SMDIG02220VA00_ SMDIG02220XA00_	5040	6.0	SMDIJ02220XA00_	6054	7.0	SMDIO12220YA00_
0.033 "	4030 5040	5.0 6.0	SMDIG02330VA00_ SMDIG02330XA00_	5040	6.0	SMDIJ02330XA00_	6054	7.0	SMDIO12330YA00_
0.047 "	4030 5040	5.0 6.0	SMDIG02470VA00_ SMDIG02470XA00_	5040	6.0	SMDIJ02470XA00_			
0.068 "	4030 5040	5.0 6.0	SMDIG02680VA00_ SMDIG02680XA00_	6054	7.0	SMDIJ02680YA00_			
0.1 μF	4030 5040 6054	5.0 6.0 7.0	SMDIG03100VA00_ SMDIG03100XA00_ SMDIG03100YA00_						
0.15 "	5040 6054	6.0 7.0	SMDIG03150XA00_ SMDIG03150YA00_						
0.22 "	6054	7.0	SMDIG03220YA00_						
0.33 "	6054	7.0	SMDIG03330YA00_						

* AC voltages: $f \leq 400 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_{\text{r}}$

Dims. in mm.

Solder pad recommendation



Part number completion:

Tolerance: 20 % = M
10 % = K
5 % = J

Packing: bulk = S

Pin length: none = 00

Taped version see page 148.

Size code	L ±0.3	W ±0.3	d	a min.	b min.	c max.
1812	4.8	3.3	0.5	1.2	3.5	3.5
2220	5.7	5.1	0.5	1.2	4	4.5
2824	7.2	6.1	0.5	1.2	4	6.5
4030	10.2	7.6	0.5	2.5	6	9
5040	12.7	10.2	0.7	2.5	6	11.5
6054	15.3	13.7	0.7	2.5	6	14

Rights reserved to amend design data without prior notification.


Recommendation for Processing and Application of SMD Capacitors



Layout Form

The components can generally be positioned on the carrier material as desired. In order to prevent soldering shadows or ensure regular temperature distribution, extreme concentration of the components should be avoided. In practice, it has proven best to keep a minimum distance of the soldering surfaces between two WIMA SMDs of twice the height of the components.

Solder Pad Recommendation



Size code	L ± 0.3	W ± 0.3	d	a min.	b min.	c max.
1812	4.8	3.3	0.5	1.2	3.5	3.5
2220	5.7	5.1	0.5	1.2	4	4.5
2824	7.2	6.1	0.5	1.2	4	6.5
4030	10.2	7.6	0.5	2.5	6	9
5040	12.7	10.2	0.7	2.5	6	11.5
6054	15.3	13.7	0.7	2.5	6	14

The solder pad size recommendations given for each individual series are to be understood as minimum dimensions which can at any time be adjusted to the layout form.

Processing


The processing of SMD components

- assembling
- soldering
- electrical final inspection/calibrating

must be regarded as a complete process. The soldering of the printed circuit board, for example, can constitute considerable stress on all the electronic components. The manufacturer's instructions on the processing of the components are mandatory.

Soldering Process

Re-flow soldering



SMD-PET	
Size code	Tmax.
1812	220° C
2220	230° C
2824	230° C
4030	230° C
5040	240° C
6054	250° C

SMD-PEN	
Size code	Tmax.
1812	220° C
2220	230° C
2824	230° C

SMD-PPS	
Size code	Tmax.
1812	250° C
2220	250° C
2824	250° C
4030	250° C
5040	250° C
6054	250° C

Temperature/time graph for the permissible processing temperature of the WIMA SMD film capacitor for typical convection soldering processes.

Due to versatile procedures exact processing parameters for re-flow soldering processes cannot be specified. The graph depicted is to be understood as a recommendation to help establishing a suitable soldering profile fulfilling the requirements

in practice at the user. During processing a max. temperature of $T=210^{\circ}\text{C}$ inside the component should not be exceeded. Due to the differing heat absorption the length of the soldering process should be kept as short as possible for smaller size codes.

SMD Handsoldering

WIMA SMD capacitors with plastic film dielectric are generally suitable for hand-soldering, e. g. for lab purposes, with a soldering iron where, however, similar to automated soldering processes, a certain duration and temperature should not be exceeded. These parameters are dependent on the physical size of the components and the relevant heat absorption involved.

The below data are to be regarded as guideline values and should serve to avoid damage to the dielectric caused by excessive heat during the soldering process. The soldering quality depends on the tool used and on the skill and experience of the person with the soldering iron in hand.

Size code	Temperature °C / °F	Time duration
1812	250 / 482	2 sec plate 1 / 5 sec off / 2 sec plate 2
2220	250 / 482	3 sec plate 1 / 5 sec off / 3 sec plate 2
2824	260 / 500	3 sec plate 1 / 5 sec off / 3 sec plate 2
4030	260 / 500	5 sec plate 1 / 5 sec off / 5 sec plate 2
5040	260 / 500	5 sec plate 1 / 5 sec off / 5 sec plate 2
6054	260 / 500	5 sec plate 1 / 5 sec off / 5 sec plate 2

Recommendation for Processing and Application of SMD Capacitors (Continuation)

Solder Paste

To achieve reliable soldering results one of the following solder alloys have from case to case proven being workable:

Lead free solder paste

Sn - Bi
Sn - Zn (Bi)
Sn - Ag - Cu (suitable for SMD-PET 5040/6054, SMD-PEN and SMD-PPS)

Solder paste with lead

Sn - Pb - Ag (Sn60-Pb40-A, Sn63-Pb37-A)

Washing

WIMA SMD components with plastic encapsulation - like all other components of similar construction irrespective of the make - cannot be regarded as hermetically sealed. Due to today's common washing substances, e. g. on aqueous basis instead of the formerly used halogenated hydrocarbons, with enhanced washing efficiency it became obvious that assembled SMD capacitors may show an impermissibly high deviation of the electrical parameters after a corresponding washing process. Hence it is recommended to refrain from applying industrial washing processes for WIMA SMD capacitors in order to avoid possible damages.

Initial Operation/Calibration

Due to the stress which the components are subjected to during processing, reversible parameter changes occur in almost all electronic components. The capacitance recovery accuracy to be expected with careful processing is within a scope of

$$|\Delta C/C| \leq 5 \%$$

For the initial operation of the device a minimum storage time of

$$t \geq 24 \text{ hours}$$

is to be taken into account. With calibrated devices or when the application is largely dependent on capacitance it is

advisable to prolong the storage time to

$$t \geq 10 \text{ days}$$

In this way ageing effects of the capacitor structure can be anticipated. Parameter changes due to processing are not to be expected after this period of time

Humidity Protection Bags

Taped WIMA SMD capacitors are shipped in humidity protection bags according to JEDEC standard (ESD/EMI-shield/water-vapour proof).

Under controlled conditions the components can be stored two years and more in the originally sealed bag. Opened packing units should immediately be used up for processing. If storage is necessary the opened packing units should be stored air-tight in the original plastic bag.

Reliability

Taking account of the manufacturer's guidelines and compatible processing, the WIMA SMD stand out for the same high quality and reliability as the analogous through-hole WIMA series. The technology of metallized film capacitors used e.g. in WIMA SMD-PET achieves the best values for all fields of application. The expected value is about:

$$\lambda_0 \leq 2 \text{ fit}$$

Furthermore the production of all WIMA components is subject to the regulations laid down by ISO 9001:2015 as well as the guidelines for component specifications set out by IEC quality assessment system (IECQ) for electronic components.

Electrical Characteristics and Fields of Application

Basically the WIMA SMD series have the same electrical characteristics as the analogous through-hole WIMA capacitors. Compared to ceramic or tantalum dielectrics WIMA SMD capacitors have a

number of other outstanding qualities:

- favourable pulse rise time
- low ESR
- low dielectric absorption
- available in high voltage series
- large capacitance spectrum
- stand up to high mechanical stress
- good long-term stability


As regards technical performance as well as quality and reliability, the WIMA SMD series offer the possibility to cover nearly all applications of conventionally through-hole film capacitors with SMD components. Furthermore, the WIMA SMD series can now be used for all the demanding capacitor applications for which, in the past, the use of through-hole components was mandatory:

- measuring techniques
- oscillator circuits
- differentiating and integrating circuits
- A/D or D/A transformers
- sample and hold circuits
- automotive electronics


With the WIMA SMD programme available today, the major part of all plastic film capacitors can be replaced by WIMA SMD components. The field of application ranges from standard coupling capacitors to use in switch-mode power supplies as filter or charging capacitors with high voltage and capacitance values, as well as in telecommunications e.g. the well-known telephone capacitor $1 \mu\text{F}/250\text{VDC}$.

Blister Tape Packaging and Packing Units of the WIMA SMD Capacitors

Tape reel:




Tape advance and return:



All dims. in mm.

Type	W _{2max}	W ₁ ± 0.2	N ± 1.5
1812	19	12.4	62
2220	19	12.4	62
2824	19	12.4	62
4030	22.4	16.4	60
5040	30.4	24.4	90
6054	30.4	24.4	90



Packing units

Size Code 1812		A ₀ ± 0.1	A ₁	B ₀ ± 0.1	B ₁	D ₀ +0.1 -0	D ₁ +0.1 -0	P ± 0.1	P ₀ * ± 0.1	P ₂ ± 0.05	E ± 0.1	F ± 0.05	G	W ± 0.3	W ₀ ± 0.2	K ± 0.1	T ± 0.1
Box size	Code																
4.8x3.3x3	KA	3.55	3.3	5.1	4.8	Ø1.5	Ø1.5	8	4	2	1.75	5.5	2.2	12	9.5	3.4	0.3
4.8x3.3x4	KB	3.55	3.3	5.1	4.8	Ø1.5	Ø1.5	8	4	2	1.75	5.5	2.2	12	9.5	4.4	0.3

taped Reel 180 mm Ø	taped Reel 330 mm Ø	bulk Standard
700	2500	3000
500	2000	3000

Size Code 2220		A ₀ ± 0.1	A ₁	B ₀ ± 0.1	B ₁	D ₀ +0.1 -0	D ₁ +0.1 -0	P ± 0.1	P ₀ * ± 0.1	P ₂ ± 0.05	E ± 0.1	F ± 0.05	G	W ± 0.3	W ₀ ± 0.2	K ± 0.1	T ± 0.1
Box size	Code																
5.7x5.1x3.5	QA	6.3	5.7	5.6	5.1	Ø1.5	Ø1.5	8	4	2	1.75	5.5	1.95	12	9.5	3.7	0.3
5.7x5.1x4.5	QB	6.3	5.7	5.6	5.1	Ø1.5	Ø1.5	8	4	2	1.75	5.5	1.95	12	9.5	4.7	0.3

taped Reel 180 mm Ø	taped Reel 330 mm Ø	bulk Standard
500	1800	3000
400	1500	3000

Size Code 2824		A ₀ ± 0.1	A ₁	B ₀ ± 0.1	B ₁	D ₀ +0.1 -0	D ₁ +0.1 -0	P ± 0.1	P ₀ * ± 0.1	P ₂ ± 0.05	E ± 0.1	F ± 0.05	G	W ± 0.3	W ₀ ± 0.2	K ± 0.1	T ± 0.1
Box size	Code																
7.2x6.1x3	TA	6.6	6.1	7.7	7.2	Ø1.5	Ø1.5	12	4	2	1.75	5.5	0.9	12	9.5	3.4	0.3
7.2x6.1x5	TB	6.6	6.1	7.7	7.2	Ø1.5	Ø1.5	12	4	2	1.75	5.5	0.9	12	9.5	5.4	0.4

taped Reel 330 mm Ø	bulk Standard
1500	2000
750	2000

		Code	A ₀ ± 0.1	A ₁	B ₀ ± 0.1	B ₁	D ₀ +0.1 -0	D ₁ +0.1 -0	P ± 0.1	P ₀ * ± 0.1	P ₂ ± 0.05	E ± 0.1	F ± 0.05	G	W ± 0.3	W ₀ ± 0.2	K ± 0.1	T ± 0.1
Size Code 4030		VA	10.7	10.2	8.1	9.1	Ø1.5	Ø1.5	16	4	2	1.75	7.5	1.9	16	13.3	5.5	0.3
Size Code 5040		XA	13.5	12.7	11	11.5	Ø1.5	Ø1.5	16	4	2	1.75	11.5	4.7	24	21.3	6.5	0.3
Size Code 6054		YA	17.0	16.5	15.6	15.0	Ø1.5	Ø1.5	20	4	2	1.75	11.5	2.95	24	21.3	7.5	0.3

taped Reel 330 mm Ø	bulk Standard
775	2000
600	1000
450	500

* cumulative after 10 steps ± 0.2 mm max.
Samples and pre-production needs on request or 1 Reel minimum.

Part number codes for SMD packing

W (Blister)	Ø in mm	Code
12	180	P
12	330	Q
16	330	R
24	330	T
Bulk Standard		S

A WIMA part number consists of 18 digits and is composed as follows:

- Field 1 - 4: Type description
- Field 5 - 6: Rated voltage
- Field 7 - 10: Capacitance
- Field 11 - 12: Size and PCM
- Field 13 - 14: Version code (e.g. Snubber versions)
- Field 15: Capacitance tolerance
- Field 16: Packing
- Field 17 - 18: Pin length (untaped)

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
M	K	S	2	C	0	2	1	0	0	1	A	0	0	M	S	S	D
MKS 2				63 VDC		0.01 µF			2.5x6.5x7.2			-		20%	bulk	6 -2	
Type description:				Rated voltage:			Capacitance:			Size:			Tolerance:			Packing:	
SMD-PET = SMDT				50 VDC = B0			22 pF = 0022			4.8x3.3x3 Size 1812 = KA			±20% = M			AMMO H16.5 340x340 = A	
SMD-PEN = SMDN				63 VDC = C0			47 pF = 0047			4.8x3.3x4 Size 1812 = KB			±10% = K			AMMO H16.5 490x370 = B	
SMD-PPS = SMDI				100 VDC = D0			100 pF = 0100			5.7x5.1x3.5 Size 2220 = QA			±5% = J			AMMO H18.5 340x340 = C	
FKP 02 = FKPO				250 VDC = F0			150 pF = 0150			5.7x5.1x4.5 Size 2220 = QB			±2.5% = H			AMMO H18.5 490x370 = D	
MKS 02 = MKS0				400 VDC = G0			220 pF = 0220			7.2x6.1x3 Size 2824 = TA			±1% = E			REEL H16.5 360 = F	
FKS 2 = FKS2				450 VDC = H0			330 pF = 0330			7.2x6.1x5 Size 2824 = TB			...			REEL H16.5 500 = H	
FKP 2 = FKP2				520 VDC = H2			470 pF = 0470			10.2x7.6x5 Size 4030 = VA						REEL H18.5 360 = I	
FKS 3 = FKS3				600 VDC = I0			680 pF = 0680			12.7x10.2x6 Size 5040 = XA						REEL H18.5 500 = J	
FKP 3 = FK3P				630 VDC = J0			1000 pF = 1100			15.3x13.7x7 Size 6054 = YA						ROLL H16.5 = N	
MKS 2 = MKS2				700 VDC = K0			1500 pF = 1150			2.5x7x4.6 PCM 2.5 = 0B						ROLL H18.5 = O	
MKP 2 = MKP2				800 VDC = L0			2200 pF = 1220			3x7.5x4.6 PCM 2.5 = 0C						BLISTER W12 180 = P	
MKS 4 = MKS4				850 VDC = M0			3300 pF = 1330			2.5x6.5x7.2 PCM 5 = 1A						BLISTER W12 330 = Q	
MKP 4C = MKPC				900 VDC = N0			4700 pF = 1470			3x7.5x7.2 PCM 5 = 1B						BLISTER W16 330 = R	
MKP 4 = MKP4				1000 VDC = O1			6800 pF = 1680			2.5x7x10 PCM 7.5 = 2A						BLISTER W24 330 = T	
MKP 10 = MKP1				1100 VDC = P0			0.01 µF = 2100			3x8.5x10 PCM 7.5 = 2B						Bulk/TPS Standard = S	
FKP 1 = FK1P				1200 VDC = Q0			0.022 µF = 2220			3x9x13 PCM 10 = 3A						...	
MKP-X2 = MKX2				1250 VDC = R0			0.047 µF = 2470			4x9x13 PCM 10 = 3C							
MKP-X1 R = MKX1				1500 VDC = S0			0.1 µF = 3100			5x11x18 PCM 15 = 4B							
MKP-Y2 = MKY2				1600 VDC = T0			0.22 µF = 3220			6x12.5x18 PCM 15 = 4C							
MP 3-X2 = MPX2				2000 VDC = U0			0.47 µF = 3470			5x14x26.5 PCM 22.5 = 5A							
MP 3-X1 = MPX1				2500 VDC = V0			1 µF = 4100			6x15x26.5 PCM 22.5 = 5B							
MP 3-Y2 = MPY2				3000 VDC = W0			2.2 µF = 4220			9x19x31.5 PCM 27.5 = 6A							
MP 3R-Y2 = MPRY				4000 VDC = X0			4.7 µF = 4470			11x21x31.5 PCM 27.5 = 6B							
MKP 4F = MKPF				6000 VDC = Y0			10 µF = 5100			9x19x41.5 PCM 37.5 = 7A							
Snubber MKP = SNMP				250 VAC = 0V			22 µF = 5220			11x22x41.5 PCM 37.5 = 7B							
Snubber FKP = SNFP				275 VAC = 1V			47 µF = 5470			19x31x56 PCM 48.5 = 8D							
GTO MKP = GTOM				300 VAC = 2V			100 µF = 6100			25x45x57 PCM 52.5 = 9D							
DC-LINK MKP 3 = DCP3				305 VAC = AV			220 µF = 6220			...							
DC-LINK MKP 4 = DCP4				350 VAC = BV			1000 µF = 7100										
DC-LINK MKP 4S = DCP5				440 VAC = 4V			1500 µF = 7150										
DC-LINK MKP 5 = DCP5				500 VAC = 5V			...										
DC-LINK MKP 6 = DCP6				...													
DC-LINK HC = DCHC																	
DC-LINK HY = DCHY																	
										</							