

**Pb-Lead Free
RoHS Compliant**

Ltr	Revisions	Date	Appr

Electrical Specifications:

Nominal Frequency		32.768	KHz
Temperature Stability		±100	PPM Max
		±50	
		±30	
		±25	
		±20	
Aging per Year		±3	
Operating Temperature Range	Standard	0 to +70	°C
	Extended	-40 to +85	
Storage Temperature Range		-55 to +125	
Supply Voltage		3.3 ± 10%	Vdd
Output Voltage	Logic High (Voh)	90%	Vdd Min
	Logic Low (Vol)	10%	Vdd Max
Output Symmetry	Standard	40 to 60	%
	Tight	45 to 55	
Output Level		HCMOS	-
Output Load		15	pF Max
Rise and Fall Time		200	ns Max
Enable-Disable Function		Tri-State	-

Temperature stability is Inclusive of all conditions:

Calibration Tolerance at +25°C, frequency stability over the operating temperature range, supply voltage, supply voltage change, output load changes, shock, vibration, and 1st year aging at +25°C.



11-3 Chien-Kuo Rd T.E.P.Z. 4027 Taiwan, ROC

All dimensions are millimeters.

CAD: TCR

Review: EG

Appr: SL

Page: 1/4 Date: Nov 27, 2007

Specification Title:

Clock Oscillator

Time of Day - 32.678 KHz




HCMOS - 3.3 V

5 x 7 millimeter Surface Mount

General Product Specification


Part Number: S7-32.768 KHz Series

Mechanical Outline:



#1 : E/D #2 : GND
#4 : VDC #3 : OUTPUT

Bottom




Recommended Land Pattern

Pin1	Pin 3
INH	Output
High or Open	Operating
Low	High Impedance


Package is Seam Sealed Ceramic-Metal.
Terminator Pads are Ni/Au
Dimensions are millimeters.

Carrier Tape Dimensions:



Dimensions are millimeters.

Solder Reflow Characteristics:



How to build a Part Number:

Series	S	Parameter
Package	7	5.0 x 7.0 mm
Supply Voltage	33	+3.3 Vdd ± 10%
Temperature Stability	10	±100 PPM
	05	±50 PPM
	03	±30 PPM
	025	±25 PPM
	020	±20 PPM
Duty Cycle	See Notes	40 / 60 %
	T	45 / 55 %
Frequency	32.768K	KHz
Temperature Range	See Notes	0 to +70 °C
	X	-40 to +85 °C
Output Load	15	pF Max
Packaging	R	Tape and Reel

Part Number Example:

S73310-32.768K-15-X-R

S7: 5.0 x 7.0 mm SMD Package

33: +3.3 ± 5% Vdd Supply Voltage

10: ±100 PPM Temperature Stability

32.768 KHz Nominal Frequency

15 pF Load

X: -40 to + 85° C Extended Temperature Range

R: Tape and Reel Packaging

Notes:

- 1- Standard Duty Cycle and Temperature Range do not need to be included in Part Number description.
- 2- Product is shipped in Tape and Reel configuration. Each reel contains 1000 pieces.
- 3- Quantities less than 1000 are shipped bulk in ESD pouches.
- 4- Specification subject to change without notice.

Page: 4/4	Date: Nov. 27, 2007	P/N: S7-32.768 KHz Series	
-----------	---------------------	----------------------------------	--