




With up to 5 switching positions as well as multiple terminal, circuit and slider options, Bulgin's board mounted power slide switches can be configured to suit your needs. We also offer a wide range of voltage selector types that can be either snapped into a panel or flange mounted.

- Ratings up to 16A, 250V ac
- PCB and solder terminals
- Voltage Selector Models
- Snap in and flange mounting
- 2, 3, 4 and 5 position
- Choice of circuits
- Choice of actuators



2000 Slide Switches - up to 5 position

10A 250Vac



Key Features

- Slide switches
- Ratings up to 16A, 250V ac
- PCB and solder terminals
- 2, 3, 4 and 5 position
- Choice of circuits
- Choice of actuators

Approvals and specifications


CE 10A 250Vac T85
6(3)A 250Vac T85







UL CSA 16A 250Vac Non Inductive
UL CSA 4A 300Vac
UL 65°C, file no. E45221, CSA file no. LR10990

μ contact gap
Please specify: Standard action (SP116) or Light action (SP118).
2000 series lubrication is inorganic and does not degrade plastics.

Terminal	Series	Position	Circuit	Slider			
K 2.8 x 0.8	2	2 Switching positions	10 	0 	6 	D 	L
R 2.8 x 0.8			20 				
T Solder		3 Switching positions	30 				
X PCB 0.8 Sq.			40 				
Y PCB 0.8 Sq. For mounting stability switches have extra "support" terminals * Nominal - Dimension varies with body type. For exact figure call sales		4 Switching positions	10 	1 	7 	E 	N
	20 						
	30 						
	40 						
	5 Switching positions	10 	2 	9 	G 	P 	
		20 					
		30 					
		40 					
	5 Switching positions	10 	3 	A 	H 	R 	
		20 					
		30 					
		40 					
	5 Switching positions	10 	4 	B 	J 	S 	
		20 					
		30 					
		40 					
	5 Switching positions	10 	5 	C 	K 	T 	
		20 					
		30 					
		40 					


Examples




Body		Options
C 2 positions 	H 2 positions 	Colour Call sales for custom colours. A full range is available for large orders. Legend printing A wide range is available For all options call sales
A 3 positions 	H 3 positions 	
A 4 positions 	H 4 positions 	
A 5 positions 		

Dimensions


C 2 positions




H 2 positions





Cut-out / PCB Matrix




A 3 positions





H 3 positions





A 4 positions



H 4 positions




A 5 positions



2000 Slide Switches - Snap fit and panel mount

10A 250Vac



115/230 is preferred legend

Key Features

- 2 way 'voltage selector'
- Ratings up to 16A, 250V ac
- Snap fit and panel mount
- PCB & solder terminals
- 2 and 3 position
- Choice of circuits
- Choice of actuators

Approvals and specifications

10A 250Vac T85
6(3)A 250Vac T85

UL CSA 16A 250Vac Non Inductive
UL CSA 4A 300Vac
UL 65°C, file no. E45221, CSA file no. LR10990

μ contact gap

Please specify: Standard action (SP116) or Light action (SP118).

2000 series lubrication is inorganic and does not degrade plastics.

Terminal	Series	Position	Circuit	Slider			
K 2.8 x 0.8	2	2 Switching positions	10 	0 	6 	C Ø2.0 Hole	L 2.3 Blade
R 2.8 x 0.8			20 	2 Ø2.0 Hole	7 	D 	M
T Solder			30 	3 2.4 Slot	8 	E 2.0 Blade	N
X PCB 0.8 Sq. For mounting stability switches have extra "support" terminals * Nominal - Dimension varies with body type. For exact figure call sales			40 	4 Ø2.5	9 	H 	P
	3 Switching positions	3 Switching positions	10 	5 Ø2.0 Hole	A 	K 2.3 Blade	R Ø5.0
			20 	S 2.2 Blade	T 		
			30 				
			40 				

Examples



T22208E ---



T22308E ---



T2230MF ---






T22205B ---



T22305B ---




T23204B ---


Body	Options
B With mounting holes  	Colour Call sales for custom colours. A full range is available for large orders. Standard body colour is black.
E Snap fit  	
F Snap fit (single pole ON OFF only)  	

Dimensions



2 Pos B



3 Pos B





2 Pos E



Panel thickness	Dim. Y
0.8-1.2	29.75/29.85
1.63	30.15/30.25
2.0	30.35/30.45
2.5	30.55/30.65

2 Pos F



Panel thickness	Dim. Y
0.8-1.2	29.75/29.85
1.63	30.15/30.25
2.0	30.35/30.45
2.5	30.55/30.65