



Product description **M16 IP40 cable connector, Contacts: 12, 4.0 - 6.0 mm, shieldable, solder, IP40**Area **M16 IP40 series 581**
Order number **99 2029 00 12****Illustration****Scale drawing****Contact arrangement**

	X	Y
A	0,44	-3,45
B	-2,29	-3,61
C	-4,10	-1,21
D	-3,20	1,34
E	-2,71	3,59
F	-0,41	3,45
G	2,29	3,61
H	4,10	1,21
J	3,20	-1,34
K	2,71	-3,59
L	-2,00	-1,51
M	2,00	1,51

You can find the component part drawing on the next page.**Technical data****General values**

Connector design	cable connector
Connector locking system	screw
Termination	solder
Wire gauge (mm)	0.25 mm ²
Wire gauge (AWG)	24
Cable outlet	4.0 - 6.0 mm
Upper limit temperature	85 °C
Lower limit temperature	- 40 °C
Customs tariff number	85369010
Packaging Unit	40

Electrical values

Rated current (40 °C)	3 A
Rated voltage	60 V
Rated impulse voltage	500 V
Pollution degree	1
Overshoot category	I
Insulating material group	III
Insulation resistance	$\geq 10^{10} \Omega$
EMC compliance	shieldable
Degree of protection	IP40
Mechanical operation	> 500 Mating cycles

Material

Contact material	CuZn (brass)
Contact plating	Au (gold)
Contact body material	PBT (UL94 V-0)

Product description

M16 IP40 cable connector, Contacts: 12, 4.0 - 6.0 mm, shieldable, solder, IP40


Area

M16 IP40 series 581

Order number

99 2029 00 12

Component part drawing



Product description **M16 IP40 cable connector, Contacts: 12, 4.0 - 6.0 mm, shieldable, solder, IP40**

Area

Order number

M16 IP40 series 581

99 2029 00 12

Security notices

The connectors are designed for use in plant, control system and electrical equipment. The end user is responsible for checking whether the connectors are suitable for use in other applications.

To lock the cable connector to the equipment connector, the threaded ring is tightened until it is 'finger-tight' (approx. 50 cNm).