



TYPE BST Marking Strips for terminal strips (302, 322, 323, 324, 326, 327)

Inventory Check



Typical application

LH:	1	2	3	4	5	6	7	8	9	10	11	12
RH:	12	11	10	9	8	7	6	5	4	3	2	1
VT:	1	2	3	4	5	6	7	8	9	10	11	12
VB:	12	11	10	9	8	7	6	5	4	3	2	1
VBR:	1	2	3	4	5	6	7	8	9	10	11	12
VTR:	12	11	10	9	8	7	6	5	4	3	2	1
RHR:	1	2	3	4	5	6	7	8	9	10	11	12
LHR:	12	11	10	9	8	7	6	5	4	3	2	1
SM:	Special marking (please provide sketch)											

Marking Orientation SM: Special Marking (please provide sketch)






Description

The BST marker strips are designed for mounting beneath or above the terminal strips to provide circuit identification. They are held in place by the same fastener that secures the terminal strip to the panel or chassis. The BST Marking Strips are available in marked and blank versions. The white PVC marking strips are supplied with black hot stamped characters. Standard marking orientations are listed in the table above, special marking can be supplied on request, please contact our customer service department.

- For circuit identification

Additional information:

Strips mount beneath or above the terminal strips and are secured by mounting screws.



Dimensions: mm (in.)

The length of the strip is the same as the length of corresponding connector. Length of Marking strips (L) $L = \text{No. of Poles} \times \text{Center to Center Spacing A} = \text{thickness}$

Width =

BST-302 /-322 : 21 mm (0.83 in.)

BST-323 : 28 mm (1.10 in.)

BST-324 : 31 mm (1.22 in.)

BST-326 BST-327: 39 mm (1.54 in.)

When locating connector, allow 0.5 mm clearance around it for process-induced variations.

Material

rigid PVC, color white matte finish

Temperature Resistance:, approximately 80°C (176°F)

Item BST Marking Strips for terminal strips (302, 322, 323, 324, 326, 327)

	TYPE:	POLES:	MARKING ORIENTATION:
	302, 322, 323, 324, 326, 327	01 to 12	See list above <u>Unmarked:</u> leave blank
BST-		/	-