

TOSHIBA BIPOLAR DIGITAL INTEGRATED CIRCUIT SILICON MONOLITHIC

TD62783AP,TD62783AFW,TD62784AP,TD62784AFW (Manufactured by Toshiba Malaysia)

8CH HIGH-VOLTAGE SOURCE DRIVER

The TD62783AP / AFW Series are comprised of eight source current Transistor Array.


These drivers are specifically designed for fluorescent display applications.

Applications include relay, hammer and lamp drivers.

FEATURES

- High output voltage Type-AP, AFW : $V_{CC} = 50 \text{ V MIN.}$
 Type-F : $V_{CC} = 35 \text{ V MIN.}$
- Output current (single output) $I_{OUT} = -500 \text{ mA MIN.}$
- Output clamp diodes
- Single supply voltage
- Input compatible with various types of logic
- Package Type-AP : DIP-18 pin
- Package Type-AFW: SOL-18 pin

TYPE	DESIGNATION
TD62783AP / AFW	TTL, 5 V CMOS
TD62784AP / AFW	6~15 V PMOS, CMOS




Weight


DIP18-P-300-2.54F : 1.478 g (Typ.)

SOL18-P-300-1.27 : 0.48 g (Typ.)

PIN CONNECTION (TOP VIEW)



SCHEMATICS (EACH DRIVER)



Note: The input and output parasitic diodes cannot be used as clamp diodes.

MAXIMUM RATINGS (Ta = 25°C)

CHARACTERISTIC		SYMBOL	RATING	UNIT
Supply Voltage		V _{CC}	50	V
Output Current		I _{OUT}	−500	mA / ch
Input Voltage		V _{IN} (Note 1)	15	V
		V _{IN} (Note 2)	30	
Clamp Diode Reverse Voltage		V _R	50	V
Clamp Diode Forward Current		I _F	500	mA
Power Dissipation	AP	P _D	1.47	W
	AFW		0.92 / 1.31 (Note 3)	
Operating Temperature		T _{opr}	−40~85	°C
Storage Temperature		T _{stg}	−55~150	°C

Note 1: Only TD62783AP / AFW

Note 2: Only TD62784AP / AFW

Note 3: On Glass Epoxy PCB (75 × 114 × 1.6 mm Cu 20%)

RECOMMENDED OPERATING CONDITIONS (Ta = −40~85°C)

CHARACTERISTIC			SYMBOL	TEST CONDITION		MIN	TYP.	MAX	UNIT	
Supply Voltage			V _{CC}	—		—	—	50	V	
Output Current			I _{OUT}	Ta = 85°C T _j = 120°C T _{pw} = 25ms	Duty = 10% 8Circuits	—	—	−260	mA / ch	
					Duty = 50% 8Circuits	—	—	−59		
					Duty = 10% 8Circuits	—	—	−180		
					Duty = 50% 8Circuits	—	—	−38		
Input Voltage		TD62783AP / AFW	V _{IN}	—		—	—	12	V	
		TD62784AP / AFW		—		—	—	24		
Input Voltage	Output On	TD62783AP / AFW	V _{IN} (ON)	—		2.0	5.0	15	V	
		TD62784AP / AFW		—		4.5	12.0	30		
	Output Off	TD62783AP / AFW	V _{IN} (OFF)	—		0	—	0.8		
		TD62784AP / AFW		—		0	—	2.0		
Clamp Diode Reverse Voltage			AP	V _R	—		—	—	50	V
			AFW		—		—	—	35	
Clamp Diode Forward Current			I _F	—		—	—	400	mA	
Power Dissipation			AP	P _D	Ta = 85°C		—	—	0.76	W
			AFW		Ta = 85°C (Note)		—	—	0.48	


Note: On Glass Epoxy PCB (75 × 114 × 1.6 mm Cu 20%)

ELECTRICAL CHARACTERISTICS (Ta = 25°C)


CHARACTERISTIC		SYMBOL	TEST CIR- CUIT	TEST CONDITION	MIN	TYP.	MAX	UNIT
Output Leakage Current		I _{CEX}	1	V _{CC} = V _{CC} MAX. V _{IN} = 0.4 V Ta = 25°C	—	—	100	μA
Output Saturation Voltage		V _{CE} (sat)	2	V _{IN} = V _{IN} (ON), I _{OUT} = -350 mA	—	—	2.0	V
				V _{IN} = V _{IN} (ON), I _{OUT} = -225 mA	—	—	1.9	
				V _{IN} = V _{IN} (ON), I _{OUT} = -100 mA	—	—	1.8	
Input Current	TD62783AP / AFW	I _{IN} (ON)	3	V _{IN} = 2.4 V	—	36	52	μA
				V _{IN} = 3.85 V	—	180	260	
	TD62784AP / AFW			V _{IN} = 5 V	—	92	130	
				V _{IN} = 12 V	—	790	1130	
Input Voltage	TD62783AP / AFW	V _{IN} (ON)	4	V _{CE} = 2.0 V	—	—	2.0	V
	TD62784AP / AFW			I _{OUT} = -350 mA	—	—	4.5	
	TD62783AP / AFW	V _{IN} (OFF)		I _{OUT} = -500 μA	0.8	—	—	
	TD62784AP / AFW				2.0	—	—	
Supply Current		I _{CC} (ON)	3	V _{IN} = V _{IN} (ON), V _{CC} = 50 V	—	—	2.5	mA / ch
Clamp Diode Reverse Current		I _R	5	V _R = 50 V	—	—	50	μA
Clamp Diode Forward Voltage		V _F	6	I _F = 350 mA	—	—	2.0	V
Turn-On Delay		t _{ON}	7	V _{CC} = V _{CC} MAX. R _L = 125 Ω C _L = 15 pF, R _L = 88 Ω (F)	—	0.15	—	μs
Turn-Off Delay		t _{OFF}			—	1.8	—	

TEST CIRCUIT


1. I_{CEX}




2. $V_{CE(sat)}$




3. $I_{IN(ON)}$, I_{CC}




4. $V_{IN(ON)}$, $V_{IN(OFF)}$





5. I_R



6. V_F



7. t_{ON} , t_{OFF}



Note 1: Pulse width 50 μ s, duty cycle 10%

Output impedance 50 Ω , $t_r \leq 5$ ns, $t_f \leq 10$ ns







Note 2: C_L includes probe and jig capacitance


PRECAUTIONS for USING

This IC does not integrate protection circuits such as overcurrent and overvoltage protectors.

Thus, if excess current or voltage is applied to the IC, the IC may be damaged. Please design the IC so that excess current or voltage will not be applied to the IC.

Utmost care is necessary in the design of the output line, VCC and GND line since IC may be destroyed due to short-circuit between outputs, air contamination fault, or fault by improper grounding.






PACKAGE DIMENSIONS

DIP18-P-300-2.54F

Unit: mm




Weight: 1.478 g (Typ.)

PACKAGE DIMENSIONS

SOL18-P-300-1.27

Unit: mm



Weight: 0.48 g (Typ.)

RESTRICTIONS ON PRODUCT USE

000707EBA

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.