

A




Diagram illustrating the cross-section of a cable with the following components and dimensions:

- BLACK**: PVC INSULATION AVERAGE THICKNESS: 0.76mm ID: 3.40 ± 0.1 mm
- WHITE**: Aluminum/Mylar (Conducting face drainage wire)
- GREEN**: Drain wire 16/0.16TXR
- PVC JACKET AVERAGE THICKNESS: 0.76mm OD: 9.10 ± 0.15 mm**

- E243929(UL) SJT 3 x 16AWG(1.31MM²)
VW-1 Shielded, 60°C 300V
- CSA 228191 SJT 3 x 16AWG(1.31MM²)
FT2 Shielded 60°C 300V -LF-
- Jacket Color: Black
- E- Green; L - Black; N - White

- 100% Open & Short Testing
- Insulation Resistance: 100MΩ (Min.)
- Voltage: 500V DC / 1 Min.

Unit: MM

[illegible]

AK500/16-OE-5-1.5

Title	Power Cord - SJT, 60°C, Shielded, Open End, 16AWG, 1.5 Meters
--------------	--

Drawing No.

rev00

Replace

Sheet

RoHS
Complaint

ASSMANN
WSV components