





IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	75 Ω	192 Ω	380 Ω
Minimum	- Ω	154 Ω	- Ω

Z vs. FREQUENCY
(REF. ONLY)



FERRITE CORE DIMENSIONS (SPEC): mm [in]

A	28.00 [1.102]	± 0.51 [.020]
B	23.00 [.906]	± 0.35 [.014]
C	20.00 [.787]	± 0.40 [.016]
D	5.80 [.228]	+ 0.36 [.014] - 0.25 [.010]
E	0.80 [.031]	+ 0.30 [.012] - 0.25 [.010]

WEIGHT/1000 13.98 kgs [30.82 Lbs]

**UNCONTROLLED
DOCUMENT**

DETAIL "A"
CHAMFER
SCALE=15:1

DIMENSIONS ARE IN mm[INCHES].				THIS DOCUMENT CONTAINS INFORMATION WHICH IS PROPRIETARY AND CONFIDENTIAL TO STEWARD. NO PRODUCTION OR PUBLICATION OF THIS DOCUMENT IN WHOLE OR IN PART SHALL BE MADE WITHOUT WRITTEN AUTHORIZATION FROM STEWARD. Steward a unit of Laird Technologies				
C	UPDATE MIN Z SPEC & COMPANY LOGO	07/27/07	JRK	PROJECT/PART NUMBER: 28R1102-100		REV C	PART TYPE: FERRITE RIBBON CORE	DRAWN BY: JRK
B	UPDATE MIN Z SPEC @100Mhz, ADD REF #	01/27/04	JRK	DATE: 07/10/03		SCALE: 3 : 1		MATERIAL: NiZn FERRITE
A	ORIGINAL DRAFT	07/10/03	JRK	CAD # 28R1102-100-C		TOOL # R1102		
REV	DESCRIPTION	DATE	INT					