



REV	DESCRIPTION	DET	DATE
D	ITEM 3, 130050 WAS 123188	EL	11/09/11
E	128538 WAS 128637. ADDED 128488	JJC	08/02/12
F	99-3748-1 WAS 99-1348-1 IN TITLE BLOCK	JJC	02/22/17



NOTES:

- 1 MAXIMUM RECOMMENDED STROKE .500
- 2 FOR USE WITH THE 206-375 TOOL. FOR OTHER TOOLS AND/OR STROKE COMBINATIONS, REFER TO THE STROKE LIMITER CHART (HK1122) OR CONSULT AN AFS/HUCK SPECIALIST.
- 3 SHIP WITH: STOP 126747, DEFLECTOR 126748-3 AND (2) .030 SHIMS 128290 REFERENCE PB563 FOR PROPER USE.
- 4 128647 ASSEMBLY CONSISTS OF 128538 COLLET AND 128488 DRAWBAR.



128488	1	DRAWBAR	9
126748-3	1	UNITIZED DEFLECTOR	8
128538	1	COLLET	7
126745	1	GUARD	6
120095	1	DEFLECTOR	5
122727-1	1	BARBED RETAINER	4
130050	1	UNITIZED CHUCK JAW	3
126746	1	TOP GUARD	2
128306	1	ANVIL	1
PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ ETCH		HUCK INTERNATIONAL, INC., I.S.D 1 CORPORATE DR KINGSTON, NEW YORK 12401	
ITAR/ECCN: EAR99		NOSE ASSEMBLY -04 MGP STRADDLE LONG	
SCH B#: 8467.99.0190		FINAL ASSY: -	
HTS: 8467.99.0190		ENG: MLK CK: DATE: 10/13/06 SCALE: 2:1	
		B	99-3748-1