


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	REVISED PER ECO-16-004223	20JUL2016	NK	MZ



- $\triangle 1$ 0.76 μ m [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27 μ m [.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76 μ m [.000030] MIN NICKEL PER QQ-N-290.
- $\triangle 2$ GOLD PLATING NEED NOT APPEAR IN THIS AREA.
- 3 REELED FOR MINI-APPLICATOR.
- 4 WIRE RANGE 28-30 AWG. INSULATION RANGE $\varnothing 3.81$ [.015]-7.62 [.030]
- $\triangle 5$ 0.38 μ m [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27 μ m [.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76 μ m [.000030] MIN NICKEL PER QQ-N-290.

OBSOLETE	PER DETAIL F	$\triangle 1$	788088-3
	-	$\triangle 5$	788088-2
	-	$\triangle 1$	788088-1
LOOSE PIECE		FINISH SOCKET BODY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 21 NOV 96		 TE Connectivity					
		CHK R.STONE 22 NOV 96							
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G.STEINHAUER 22 NOV 96		NAME			
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-10042		SOCKET ASSEMBLY, .062, TYPE III+			
				APPLICATION SPEC 114-10004					
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS		WEIGHT -		SIZE A2	CAGE CODE 00779	DRAWING NO C-788088	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 8:1		SHEET 1 of 1		REV C1	