


ENERGIZER NO. L92




Dimensions in mm (inches)





AAA

Chemical System:	Lithium/Iron Disulfide (Li/FeS ₂)
Designation:	ANSI-24LF, IEC-FR03
Battery Voltage:	1.5 Volts
Typical Weight:	7.6 grams (0.3 oz.)
Typical Volume:	3.8 cubic centimeters (0.2 cubic inch)
Average Capacity:	1250 mAh (to 1.0 volts) (Rated capacity at 100 mA drain)
Max Discharge:	1.5 Amps Continuous 2.0 Amps Pulse, 2 sec on/8 sec off (to 1.0 volts)
Storage Temp:	-40°C to 60°C (-40°F to 140°F)
Operating Temp:	-40°C to 60°C (-40°F to 140°F)
Lithium Content:	Less than 0.5 grams (0.02 oz.) per cell
Jacket:	Non-magnetic Plastic Label
Transportation:	Meets requirements of 49CFR 173.185 (b) and IATA special provisions A45
Shelf Life:	15 years

Projected Percent Service Maintenance



Typical Battery Performance









 CONSTANT POWER DISCHARGE
 Continuous @21°C to 0.9V

 CONSTANT POWER DISCHARGE
 Continuous @21°C to 1.0V


Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

© Energizer - All Rights Reserved

**ENERGIZER NO. L92****Typical Battery Performance****Temperature Effects****ANSI - IEC Industry Standard Tests @ 20° C****Important Notice**

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

© Energizer - All Rights Reserved