

ATTENUATORS

Type N, up to 18 GHz, 10 Watts

SPECIFICATIONS:

Models: XXN10W-XX, XXN10W-XXF & XXN10W-XXM

RoHS
Compliant

AEROFLEX
A passion for performance.

Electrical:

Frequency Range _____ DC - 18 GHz
Standard Freq. Values _____ 6, & 18 GHz
Standard dB Values* _____ 0 - 10, 12, 20, 30 & 40 dB
In 1 dB Increments

Attenuation Accuracy DC - 12.4 GHz 12.4 - 18 GHz
0 - 6 dB _____ ± 0.3 dB _____ ± 0.5 dB
7 - 20 dB _____ ± 0.5 dB _____ ± 0.7 dB
21 - 40 dB _____ ± 0.7 dB _____ ± 1.0 dB

VSWR

DC - 6 GHz _____ 1.20:1 Max.
6 - 12.4 GHz _____ 1.30:1 Max.
12.4 - 18 GHz _____ 1.40:1 Max.

Input Power _____ 10 Watts Avg. @ 25°C
Derated Linearly to 2 Watts @ +125°C

Peak Power _____ 500 Watts Max.
(5uSec Pulse, .05% Duty Cycle)

Impedance _____ 50 Ohms

Operating Temp Range _____ -65°C to +125°C

Mechanical:

Type N Connectors _____ Passivated Stainless Steel
Mates with MIL-STD-348

Conductors _____ Gold Plated Beryllium Copper

Housing _____ Anodized Aluminum

Model Number: **XXN10W-XX**


Male/Female Connectors
Length: $2.41 \pm .05$ [61.2 $\pm$ 1.3]
Pictured

Model Number: **XXN10W-XXF**

Female/Female Connectors
Length: $2.49 \pm .05$ [63.2 $\pm$ 1.3]

Model Number: **XXN10W-XXM**

Male/Male Connectors
Length: $2.34 \pm .05$ [59.4 $\pm$ 1.3]



HOW TO ORDER:

Model Number: **XXN10W-XXY**

Freq. Range
6 = DC - 6 GHz
18 = DC - 18 GHz

Connector Configuration
= Male/Female
F = Fem/Fem
M = Male/Male

dB Value

Ordering Examples:

Model Number: **18N10W-20**
DC - 18 GHz; 20 dB; Type N - Male/Fem

Model Number: **6N10W-06F**
DC - 6 GHz; 6 dB; Type N - Fem/Fem

Model Number: **18N10W-03M**
DC - 18 GHz; 3 dB; Type N - Male/Male

Note: Dimensions in Brackets are Expressed in Millimeters and are for Reference Only.

XXN10W-ATT: REV M (M)

AEROFLEX
INMET

Aeroflex / Inmet, Inc. • 300 Dino Drive, Ann Arbor, MI 48103 • U.S.A.
888-244-6638 or 734-426-5553 • FAX: 734-426-5557
www.aeroflex.com/inmet • inmet-sales@eroflex.com