

**Relay compatible
with sockets:**

S4-B, S4-L, S4-P, S4-PO




Table 1 Electrical Life, ops. x 10⁶






Table 2 Max. DC Load



Dimensions - mm



C4-A40



General purpose

Four change-over contacts

10 A 250 V AC1 0.5 A 110 V DC1
6 A 30 V DC1 0.2 A 220 V DC1

Contacts

Materials: Standard, code 0 AgNi
Optional, code 8 AgNi + 10μ Au
Optional, code 9 AgNi + 0.2μ Au
Max. switching current 10 A
Max. peak inrush current (20 ms) 30 A
Max. switching voltage 250 V
Max. AC load (Table 1) 2.5 KVA
Max. DC load (Table 2)

Coils (Ohms ±10% @ 20°C)

Pull-in voltage ≤0.8 x U_n
Drop-out voltage ≥0.1 x U_n
Nominal coil power 2.4 VA (AC)/1.4 W (DC)

VAC	Ω	mA	VDC	Ω	mA
24	65	100	24	414	58
48	286	50	48	1K6	30
115	1K7	21	110	8K1	13
230	6K8	10	220	35K7	6.2

Insulation

Dielectric strength (1 minute): Open contacts 1,000 V
Between adjacent poles 2.5 KV
Between contacts and coil 2.5 KV
Isolation resistance at 500 V ≥1 GΩ
Isolation, IEC 61810-5: 2.5 KV / 3

Specifications

Operate time + bounce time 20 ms
Release time + bounce time 8 ms
Ambient temperature -40°C (no ice) to +70°C
Mechanical life ops. 10 Mill. AC, 20 Mill. DC relays
Electrical life at nominal load ≥100,000 ops.
Operating frequency at nominal load 1,200/hour
Protection degree IP 40/RT1
Weight avg. 90 g

Standard Types

AC 50 Hz, (60 Hz): 24, 48, 115, (120), 230, (240)

X = LED (standard)

RC suppressor

C4-A40X..... VAC

C4-A40R..... VAC

DC 24, 48, 110, 220

X = LED no polarity (standard)

Free-wheeling diode

Polarity and free-wheeling diodes

AC/DC bridge rectifier (24, 48 or 60 V)

C4-A40X..... VDC

C4-A40DX VDC

C4-A40FX..... VDC

C4-A40BX VDC



Lloyd's IEC 61810 EN 60947