


HDSL TRANSFORMER

For Level One Chipsets



- Matched to Level One's ICs SK70704/06 and SK70721/25
- Excellent THD performance
- Maximum height .485" (12,32 mm)
- Approved to UL 1950 supplementary insulation requirements for working voltages up to 250 Vrms

Electrical Specifications @ 25°C — Operating Temperature -40°C to +85°C

Part Number	Matched To Level One IC Numbers	Application (Kbps)	Turns Ratio Chip-Line (± 2%)	Inductance Line Side (10-7)(w/6-9 shorted)	Leakage Inductance (10-7)(w/6-9, 1-4, 2-5 shorted)	Isolation Voltage (Vrms MIN)
B1013	SK70704/06 & SK70721/25	784	1CTS:1.8CTS	3.00 mH ± 10%	30 µH MAX	2000

Additional Information



Part Number	DCR Line Side (10-6)=(9-7)	DCR Chip Side (1-5)(w/2-4 shorted)	Return Loss (40 -200 KHz)	Longitudinal Balance (dB MIN @ 135 Ω)	THD (db TYP @ 135 Ω)
B1013	1.5 Ω (MAX)	2.3 Ω (MAX)	16.5 dB MIN	50 @ 5-196 KHz	-75 (5 KHz, 6 V p-p)

NOTE: Transformers are shipped in trays, unless Tape & Reel packaging is specified by adding the suffix "T" to the part number (ex: B1013T)

Mechanicals

Schematic

B1013



Weight6.2 grams
Tray60/tray

Dimensions: $\frac{\text{Inches}}{\text{mm}}$
Unless otherwise specified,
all tolerances are ± $\frac{.010}{0.25}$

For More Information :

UNITED STATES (Worldwide)

12220 World Trade Drive
San Diego, CA 92128
U.S.A.
<http://www.pulseeng.com>
TEL: 858 674 8100
FAX: 858 674 8262

UNITED KINGDOM (Northern Europe)

1 & 2 Huxley Road
The Surrey Research Park
Guildford, Surrey GU2 5RE
United Kingdom
TEL: 44 1483 401700
FAX: 44 1483 401701

FRANCE (Southern Europe)

Zone Industrielle
F-39270
Orgelet
France
TEL: 33 3 84 35 04 04
FAX: 33 3 84 25 46 41

SINGAPORE (Southern Asia)

150 Kampong Ampat
#07-01/02
KA Centre
Singapore 368324
TEL: 65 287 8998
FAX: 65 280 0080

TAIWAN, R.O.C. (Northern Asia)

3F-4, No. 81, Sec. 1
HsinTai Wu Road
Hsi-Chih, Taipei Hsien
Taiwan, R.O.C.
Tel: 886 2 2698 0228
FAX: 886 2 2698 0948

DISTRIBUTOR

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.