


# MBR10H100CT, MBRF10H100CT & MBRB10H100CT Series


## Dual High-Voltage Schottky Rectifiers

Reverse Voltage 90 to 100V  
Forward Current 10A




*New Product*

**TO-220AB (MBR10H90CT, MBR10H100CT)**




**Mounting Pad Layout TO-263AB**




Dimensions in inches and (millimeters)

**ITO-220AB (MBRF10H90CT, MBRF10H100CT)**



**TO-263AB (MBRB10H90CT, MBRB10H100CT)**



## Mechanical Data

**Case:** JEDEC TO-220AB, ITO-220AB & TO-263AB molded plastic body

**Terminals:** Plated leads, solderable per MIL-STD-750, Method 2026

High temperature soldering guaranteed: 250°C/10 seconds, 0.25" (6.35mm) from case

**Polarity:** As marked

**Mounting Position:** Any

**Mounting Torque:** 10 in-lbs maximum

**Weight:** 0.08oz., 2.24g

## Features

- Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- Dual rectifier construction, positive center tap
- Metal silicon junction, majority carrier conduction
- Low power loss, high efficiency
- Guardring for overvoltage protection
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications

# MBR10H100CT, MBRF10H100CT & MBRB10H100CT Series

## Dual High-Voltage Schottky Rectifiers

### Maximum Ratings (T<sub>C</sub> = 25°C unless otherwise noted)

| Parameter                                                                                                      | Symbol                            | MBR10H90CT                                                        | MBR10H100CT | Unit |
|----------------------------------------------------------------------------------------------------------------|-----------------------------------|-------------------------------------------------------------------|-------------|------|
| Maximum repetitive peak reverse voltage                                                                        | V <sub>RRM</sub>                  | 90                                                                | 100         | V    |
| Working peak reverse voltage                                                                                   | V <sub>RWM</sub>                  | 90                                                                | 100         | V    |
| Maximum DC blocking voltage                                                                                    | V <sub>DC</sub>                   | 90                                                                | 100         | V    |
| Maximum average forward rectified current <i>Total device<br/>at T<sub>C</sub> = 105°C<br/>Per leg</i>         | I <sub>F(AV)</sub>                | 10<br>5                                                           |             | A    |
| Peak forward surge current<br>8.3ms single half sine-wave superimposed<br>on rated load (JEDEC Method) per leg | I <sub>FSM</sub>                  | 150                                                               |             | A    |
| Peak repetitive reverse current per leg at t <sub>p</sub> = 2μs, 1KHz                                          | I <sub>RRM</sub>                  | 0.5                                                               |             | A    |
| Voltage rate of change (rated V <sub>R</sub> )                                                                 | dv/dt                             | 10,000                                                            |             | V/μs |
| Operating junction and storage temperature range                                                               | T <sub>J</sub> , T <sub>STG</sub> | -65 to +150                                                       |             | °C   |
| RMS Isolation voltage (MBRF type only) from terminals<br>to heatsink with t = 1 second, RH ≤ 30%               | V <sub>ISOL</sub>                 | 4500 <sup>(1)</sup><br>3500 <sup>(2)</sup><br>1500 <sup>(3)</sup> |             | V    |

### Electrical Characteristics (T<sub>C</sub> = 25°C unless otherwise noted)

| Parameter                                                                                                                                                                                                                                                                | Symbol         | Value                        | Unit     |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|------------------------------|----------|
| Maximum instantaneous forward voltage per leg <sup>(4)</sup><br>at I <sub>F</sub> = 5.0A, T <sub>J</sub> = 25°C<br>at I <sub>F</sub> = 5.0A, T <sub>J</sub> = 125°C<br>at I <sub>F</sub> = 10A, T <sub>J</sub> = 25°C<br>at I <sub>F</sub> = 10A, T <sub>J</sub> = 125°C | V <sub>F</sub> | 0.76<br>0.61<br>0.85<br>0.71 | V        |
| Maximum reverse current per leg<br>at working peak reverse voltage (Note 4)<br>T <sub>J</sub> = 25°C<br>T <sub>J</sub> = 100°C                                                                                                                                           | I <sub>R</sub> | 3.5<br>4.5                   | μA<br>mA |

### Thermal Characteristics (T<sub>C</sub> = 25°C unless otherwise noted)

| Parameter                          | Symbol           | MBR | MBRF | MBRB | Unit |
|------------------------------------|------------------|-----|------|------|------|
| Typical thermal resistance per leg | R <sub>θJC</sub> | 2.2 | 4.2  | 2.2  | °C/W |

#### Notes:

- (1) Clip mounting (on case), where lead does not overlap heatsink with 0.110" offset
- (2) Clip mounting (on case), where leads do overlap heatsink
- (3) Screw mounting with 4-40 screw, where washer diameter is ≤ 4.9 mm (0.19")
- (4) Pulse test: 300μs pulse width, 1% duty cycle




GENERAL  
SEMICONDUCTOR®

# MBR10H100CT, MBRF10H100CT & MBRB10H100CT Series


## Dual High-Voltage Schottky Rectifiers

### Ratings and Characteristic Curves ( $T_A = 25^\circ\text{C}$ unless otherwise noted)


**Fig. 1 – Forward Derating Curve  
Per Leg**




**Fig. 2 – Typical Instantaneous  
Forward Characteristics Per Leg**



**Fig. 3 – Typical Reverse  
Characteristics Per Leg**



**Fig. 4 – Typical Junction Capacitance**



**Fig. 5 – Typical Transient  
Thermal Impedance Per Leg**

