



Aluminum Electrolytic Capacitors

+105°C Long Life Snap-Mount



FEATURES

Multiple Case Sizes - High Voltage – High Current

APPLICATIONS

Filtering – Switching Power Supplies

Operating Temperature Range		-40°C to +105°C (≤250WVDC) -25°C to +105°C (>250WVDC)													
Capacitance Tolerance		+20% at 120 Hz, 20°C													
Surge Voltage	WVDC	10	16	25	35	50	63	80	100	160	200	250	350	400	450
	SVDC	13	20	32	44	63	79	100	120	200	250	300	400	450	500
Dissipation Factor tan δ (120 Hz)	WVDC	10	16	25	35	50	63	80	100	160	200	250	350	400	450
		.55	.5	.45	.4	.35	.3	.25	.2	.15	.15	.15	.15	.15	.15
		For capacitances above 33000uF, add to DF value (Capacitance-33000) *0.1 10000													
Leakage Current @20°C, Rated WVDC applied		Time				5 Minutes									
						3√CV									
Impedance Ratio (120 Hz)	WVDC	10	16	25	35	50	63	80	100	160	200	250	350	400	450
	-25°C/+20°C	4	4	4	4	4	4	4	4	3	3	3	8	8	8
	-40°C/+20°C	15	15	15	15	15	15	15	15	15	15	15	15	-	-
Load Life		2000 hours with rated voltage and rated ripple current applied at 105°C													
		Capacitance Change					≤20% of initial measured value								
		Dissipation Factor					≤200% of maximum specified value								
		Leakage Current					≤100% of maximum specified value								
Shelf Life		1000 hours at 105°C with no voltage applied													
		Capacitance Change					≤20% of initial measured value								
		Dissipation Factor					≤200% of maximum specified value								
		Leakage Current					≤100% of maximum specified value								
Ripple Current Multipliers		Frequency (Hz)							Temperature (°C)						
	WVDC	60	120	400	1k	10k	50k	40	60	70	85	105			
	≤100	0.8	1.0	1.1	1.15	1.25	1.25	1	1	1	1	1			
	>160	0.8	1.0	1.1	1.15	1.47	1.47	1	1	1	1	1			



Your Global Source for World-Class Capacitors

© 2017 Illinois Capacitor

North America

Tel: 847.675.1760

sales@illcap.com

Asia

Tel: 852.2793 0931

sales@illcap.com.hk



Lead Style Options

Code Z (standard) Diameter 20 to 40 mm	Code W Diameter 20 to 40 mm												
Code P Diameter 22 to 35 mm	Code D Diameter 30 to 40 mm												
Code 9 Diameter 25 to 35 mm	Code T Diameter 25 to 35 mm												
Code 4 Diameter 35 to 45 mm	Code 4S (straight leads) Diameter 35 to 45 mm												
Code 5 Diameter 40 to 50 mm	Code G <table><tr><td>D</td><td>35</td><td>40</td><td>50</td><td>63</td><td>76</td></tr><tr><td>P</td><td>14</td><td>14</td><td>18</td><td>25</td><td>25</td></tr></table> Diameter 35 to 76 mm	D	35	40	50	63	76	P	14	14	18	25	25
D	35	40	50	63	76								
P	14	14	18	25	25								

LMH

+105°C, standard 2000 hrs

Capacitance (μF)	WVDC	IC PART NUMBER	Maximum ESR (mΩ) 120 Hz, +20°C	Maximum RMS Ripple Current (A) 120 Hz, +105°C	Dims DxL (mm)
68	450	686LMH450MZBC	365.71	0.47	22x25
82	450	826LMH450MZBD	3032.68	0.55	22x30
100	400	107LMH400MZBC	2486.8	0.7	22x25
100	450	107LMH450MZBC	2486.8	0.64	22x25
100	450	107LMH450MZCC	2486.8	0.64	25x25
120	350	127LMH350MZBC	2072.33	0.75	22x25
120	400	127LMH400MZBD	2072.33	0.75	22x30
120	400	127LMH400MZBC	2072.33	0.68	22x25
120	450	127LMH450MZBD	2072.33	0.69	22x30
120	450	127LMH450MZCC	2072.33	0.69	25x25
120	450	127LMH450MZBE	2072.33	0.72	22x35
120	450	127LMH450MZCD	2072.33	0.72	25x30
150	160	157LMH160MZBD	1657.86	0.71	22x30
150	400	157LMH400MZBD	1657.86	0.88	22x30
150	400	157LMH400MZCC	1657.86	0.88	25x25
150	450	157LMH450MZCD	1657.86	0.79	25x30
150	450	157LMH450MZDC	1657.86	0.79	30x25
150	450	157LMH450MZBE	1657.86	0.79	22x35
180	350	187LMH350MZBD	1381.55	0.9	22x30
180	350	187LMH350MZCC	1381.55	0.9	25x25
180	400	187LMH400MZBE	1381.55	0.95	22x35
180	400	187LMH400MZCD	1381.55	0.95	25x30
180	400	187LMH400MZBD	1381.55	0.73	22x30
180	400	187LMH400MZCC	1381.55	0.73	25x25
180	450	187LMH450MZBF	1381.55	0.79	22x40
180	450	187LMH450MZCD	1381.55	0.79	25x30
180	450	187LMH450MZBG	1381.55	0.87	22x45
180	450	187LMH450MZCF	1381.55	0.87	25x40
180	450	187LMH450MZDD	1381.55	0.87	30x30
220	250	227LMH250MZBC	1130.62	0.89	22x25
220	350	227LMH350MZBE	1130.62	1	22x35
220	350	227LMH350MZCD	1130.62	1	25x30
220	400	227LMH400MZBG	1130.62	1.1	22x45
220	400	227LMH400MZCE	1130.62	1.1	25x35
220	400	227LMH400MZDC	1130.62	1.1	30x25
220	400	227LMH400MZBE	1130.62	0.85	22x35
220	400	227LMH400MZCD	1130.62	0.85	25x30
220	450	227LMH450MZBG	1130.62	0.87	22x45
220	450	227LMH450MZCE	1130.62	0.87	25x35
220	450	227LMH450MZCG	1130.62	1	25x45
220	450	227LMH450MZDD	1130.62	1	30x30
220	450	227LMH450MZEC	1130.62	1	35x25
270	250	277LMH250MZBC	921.04	1.1	22x25
270	350	277LMH350MZBF	921.04	1.1	22x40
270	350	277LMH350MZCD	921.04	1.1	25x30
270	350	277LMH350MZDC	921.04	1.1	30x25
270	400	277LMH400MZBH	921.04	1.22	22x50
270	400	277LMH400MZCF	921.04	1.22	25x40
270	400	277LMH400MZDD	921.04	1.22	30x30
270	400	277LMH400MZEC	921.04	1.22	35x25
270	400	277LMH400MZBF	921.04	1	22x40
270	400	277LMH400MZCE	921.04	1	25x35
270	400	277LMH400MZDC	921.04	1	30x25
270	450	277LMH450MZBH	921.04	1.05	22x50
270	450	277LMH450MZCF	921.04	1.05	25x40
270	450	277LMH450MZDD	921.04	1.05	30x30
270	450	277LMH450MZEC	921.04	1.05	35x25
270	450	277LMH450MZED	921.04	1.19	35x30

Capacitance (μF)	WVDC	IC PART NUMBER	Maximum ESR (mΩ) 120 Hz, +20°C	Maximum RMS Ripple Current (A) 120 Hz, +105°C	Dims DxL (mm)
270	450	277LMH450MZCH	921.04	1.19	25x50
270	450	277LMH450MZDF	921.04	1.19	30x40
330	250	337LMH250MZBD	753.58	1.2	22x30
330	250	337LMH250MZCC	753.58	1.2	25x25
330	350	337LMH350MZBG	753.58	1.2	22x45
330	350	337LMH350MZCG	753.58	1.2	25x45
330	350	337LMH350MZDD	753.58	1.2	30x30
330	400	337LMH400MZCG	753.58	1.44	25x45
330	400	337LMH400MZED	753.58	1.44	35x30
330	400	337LMH400MZDE	753.58	1.37	30x35
330	400	337LMH400MZBH	753.58	1.15	22x50
330	400	337LMH400MZCF	753.58	1.15	25x40
330	400	337LMH400MZDD	753.58	1.44	30x30
330	400	337LMH400MZEC	753.58	1.15	35x25
330	450	337LMH450MZCH	753.58	1.2	25x50
330	450	337LMH450MZDE	753.58	1.2	30x35
330	450	337LMH450MZED	753.58	1.38	35x30
330	450	337LMH450MZDG	753.58	1.38	30x45
330	450	337LMH450MZEE	753.58	1.38	35x35
390	200	397LMH200MZBC	637.64	1.31	22x25
390	250	397LMH250MZBE	637.64	1.3	22x35
390	250	397LMH250MZCC	637.64	1.3	25x25
390	250	397LMH250MZBD	637.64	1.3	22x30
390	350	397LMH350MZCG	637.64	1.3	25x45
390	350	397LMH350MZDE	637.64	1.3	30x35
390	400	397LMH400MZCH	637.64	1.55	25x50
390	400	397LMH400MZED	637.64	1.55	35x30
390	400	397LMH400MZDF	637.64	1.58	30x40
390	400	397LMH400MZCG	637.64	1.4	25x45
390	450	397LMH450MZDF	637.64	1.38	30x40
390	450	397LMH450MZEE	637.64	1.55	35x35
390	450	397LMH450MZDH	637.64	1.74	30x50
470	160	477LMH160MZBC	529.11	1.4	22x25
470	200	477LMH200MZBD	529.11	1.44	22x30
470	250	477LMH250MZBE	529.11	1.4	22x35
470	250	477LMH250MZBF	529.11	1.4	22x40
470	250	477LMH250MZCD	529.11	1.4	25x30
470	350	477LMH350MZCH	529.11	1.4	25x50
470	350	477LMH350MZDE	529.11	1.4	30x35
470	350	477LMH350MZED	529.11	1.4	35x30
470	400	477LMH400MZEE	529.11	1.68	35x35
470	400	477LMH400MZDG	529.11	1.68	30x45
470	400	477LMH400MZCH	529.11	1.55	25x50
470	400	477LMH400MZDF	529.11	1.55	30x40
470	400	477LMH400MZED	529.11	1.55	35x30
470	450	477LMH450MZDG	529.11	1.55	30x45
470	450	477LMH450MZEF	529.11	1.55	35x40
470	450	477LMH450MZEG	529.11	1.74	35x45
560	160	567LMH160MZBC	444.071	1.4	22x25
560	200	567LMH200MZBD	444.071	1.48	22x30
560	200	567LMH200MZCC	444.071	1.48	25x25
560	250	567LMH250MZCE	444.071	1.49	25x35
560	250	567LMH250MZDC	444.071	1.44	30x25
560	250	567LMH250MZBF	444.071	1.4	22x40
560	350	567LMH350MZDG	444.071	1.5	30x45
560	350	567LMH350MZEE	444.071	1.5	35x35
560	400	567LMH400MZDH	444.071	1.9	30x50
560	400	567LMH400MZEF	444.071	1.9	35x40

LMH

+105°C, standard 2000 hrs

Capacitance (µF)	WVDC	IC PART NUMBER	Maximum ESR (mΩ) 120 Hz, +20°C	Maximum RMS Ripple Current (A) 120 Hz, +105°C	Dims DxL (mm)
560	400	567LMH400MZDG	444.071	1.9	30x45
560	400	567LMH400MZEE	444.071	1.63	35x35
560	450	567LMH450MZEG	444.071	1.7	35x45
560	450	567LMH450MZEH	444.071	1.9	35x50
680	160	687LMH160MZBD	365.71	1.7	22x30
680	160	687LMH160MZCC	365.71	1.7	25x25
680	200	687LMH200MZBF	365.71	1.75	22x40
680	200	687LMH200MZCD	365.71	1.75	25x30
680	250	687LMH250MZBH	365.71	1.7	22x50
680	250	687LMH250MZEC	365.71	1.7	35x25
680	250	687LMH250MZCF	365.71	1.73	25x40
680	250	687LMH250MZDD	365.71	1.71	30x30
680	250	687LMH250MZBG	365.71	1.7	22x45
680	350	687LMH350MZDH	365.71	1.7	30x50
680	350	687LMH350MZEF	365.71	1.7	35x40
680	400	687LMH400MZEG	365.71	2.12	35x45
680	400	687LMH400MZDH	365.71	1.8	30x50
680	400	687LMH400MZEF	365.71	1.8	35x40
680	450	687LMH450MZEH	365.71	1.91	35x50
820	100	827LMH100MZBC	404.357	1.4	22x25
820	160	827LMH160MZBE	303.27	2	22x35
820	160	827LMH160MZCD	303.27	2	25x30
820	200	827LMH200MZDC	303.27	1.92	30x25
820	200	827LMH200MZBF	303.27	1.75	22x40
820	200	827LMH200MZBG	303.27	2.04	22x45
820	200	827LMH200MZCE	303.27	2.04	25x35
820	250	827LMH250MZED	303.27	2	35x30
820	250	827LMH250MZCG	303.27	2	25x45
820	250	827LMH250MZDE	303.27	2	30x35
820	350	827LMH350MZEG	303.27	2	35x45
820	400	827LMH400MZEH	303.27	2.3	35x50
820	400	827LMH400MZEG	303.27	1.9	35x45
1000	100	108LMH100MZBD	121.902	1.7	22x30
1000	160	108LMH160MZBF	248.68	2.2	22x40
1000	160	108LMH160MZCE	248.68	2.2	25x35
1000	160	108LMH160MZDC	248.68	2.2	30x25
1000	200	108LMH200MZBH	248.68	2.3	22x50
1000	200	108LMH200MZCG	248.68	2.3	25x45
1000	200	108LMH200MZDD	248.68	2.3	30x30
1000	200	108LMH200MZEC	248.68	2.3	35x25
1000	200	108LMH200MZBG	248.68	2.04	22x45
1000	250	108LMH250MZCH	248.68	2.2	25x50
1000	250	108LMH250MZDF	248.68	2.2	30x40
1000	250	108LMH250MZED	248.68	2.2	35x30
1200	80	128LMH080MZBC	365.71	1.5	22x25
1200	100	128LMH100MZBD	276.31	1.8	22x30
1200	100	128LMH100MZCC	276.31	1.8	25x25
1200	160	128LMH160MZDD	207.23	2.3	30x30
1200	160	128LMH160MZCF	207.23	2.3	25x40
1200	160	128LMH160MZEC	207.23	2.33	35x25
1200	200	128LMH200MZCG	207.23	2.65	25x45
1200	200	128LMH200MZEC	207.23	2.3	35x25
1200	200	128LMH200MZCH	207.23	2.65	25x50
1200	200	128LMH200MZDE	207.23	2.65	30x35
1200	200	128LMH200MZED	207.23	2.65	35x30
1200	250	128LMH250MZDG	207.23	2.3	30x45
1200	250	128LMH250MZEE	207.23	2.3	35x35
1500	80	158LMH080MZBD	276.21	1.7	22x30

Capacitance (µF)	WVDC	IC PART NUMBER	Maximum ESR (mΩ) 120 Hz, +20°C	Maximum RMS Ripple Current (A) 120 Hz, +105°C	Dims DxL (mm)
1500	80	158LMH080MZCC	276.21	1.7	25x25
1500	100	158LMH100MZBE	221.05	2.1	22x35
1500	100	158LMH100MZCD	221.05	2.1	25x30
1500	160	158LMH160MZED	165.786	2.5	35x30
1500	160	158LMH160MZCG	165.79	2.5	25x45
1500	160	158LMH160MZDE	165.79	2.5	30x35
1500	200	158LMH200MZCH	165.79	2.57	25x50
1500	200	158LMH200MZDF	165.79	2.8	30x40
1500	200	158LMH200MZED	165.786	2.49	35x30
1500	250	158LMH250MZDH	165.786	2.3	30x50
1500	250	158LMH250MZEF	165.786	2.3	35x40
1500	250	158LMH250MZEG	165.79	2.5	35x45
1800	80	188LMH080MZBE	230.26	1.8	22x35
1800	100	188LMH100MZBF	184.207	2.3	22x40
1800	100	188LMH100MZCE	184.207	2.3	25x35
1800	100	188LMH100MZDC	184.207	2.3	30x25
1800	160	188LMH160MZCH	138.16	2.7	25x50
1800	160	188LMH160MZDF	138.16	2.7	30x40
1800	160	188LMH160MZED	138.16	2.7	35x30
1800	200	188LMH200MZDG	138.16	2.68	30x45
1800	200	188LMH200MZEF	138.16	2.08	35x40
1800	250	188LMH250MZEH	138.16	2.7	35x50
1800	250	188LMH250MZEG	138.16	2.5	35x45
2200	63	228LMH063MZBC	226.07	2	22x25
2200	80	228LMH080MZBF	188.394	2.1	22x40
2200	80	228LMH080MZCD	188.394	2.1	25x30
2200	100	228LMH100MZCF	150.715	2.6	25x40
2200	100	228LMH100MZDD	150.715	2.6	30x30
2200	100	228LMH100MZEC	150.715	2.6	35x25
2200	160	228LMH160MZDG	113.06	2.9	30x45
2200	160	228LMH160MZEE	113.06	2.9	35x35
2200	200	228LMH200MZEG	113.06	3.48	35x45
2200	200	228LMH200MZDH	113.036	2.92	30x50
2200	200	228LMH200MZEF	113.036	2.92	35x40
2700	50	278LMH050MZBC	153.51	1.8	22x25
2700	63	278LMH063MZBD	184.207	2.2	22x30
2700	63	278LMH063MZCC	184.207	2.2	25x25
2700	80	278LMH080MZBG	92.104	2.4	22x45
2700	80	278LMH080MZCE	154.51	2.4	25x35
2700	80	278LMH080MZDC	154.51	2.4	30x25
2700	100	278LMH100MZCG	122.805	2.9	25x45
2700	100	278LMH100MZDE	122.805	2.9	30x35
2700	160	278LMH160MZDH	92.1	3.1	30x50
2700	160	278LMH160MZEF	92.1	3.1	35x40
2700	200	278LMH200MZEG	92.104	3.27	35x45
3300	50	338LMH050MZBD	175.83	2	22x30
3300	63	338LMH063MZBE	153.51	2.5	22x35
3300	80	338LMH080MZBH	153.51	2.6	22x50
3300	80	338LMH080MZCF	153.51	2.6	25x40
3300	80	338LMH080MZDD	153.51	2.6	30x30
3300	80	338LMH080MZEC	153.51	2.6	35x25
3300	100	338LMH100MZCH	100.48	3.2	25x50
3300	100	338LMH100MZDF	100.48	3.2	30x40
3300	100	338LMH100MZED	100.48	3.2	35x30
3300	160	338LMH160MZEG	75.358	3.1	35x45
3300	160	338LMH160MZEH	75.358	3.3	35x50
3900	50	398LMH050MZBE	148.78	2.2	22x35
3900	50	398LMH050MZCC	148.78	2.2	25x25

LMH

+105°C, standard 2000 hrs

Capacitance (μF)	WVDC	IC PART NUMBER	Maximum ESR (mΩ) 120 Hz, +20°C	Maximum RMS Ripple Current (A) 120 Hz, +105°C	Dims DxL (mm)
3900	63	398LMH063MZBF	127.528	2.7	22x40
3900	63	398LMH063MZCD	127.528	2.7	25x30
3900	63	398LMH063MZDC	127.528	2.7	30x25
3900	80	398LMH080MZCG	106.273	3	25x45
3900	80	398LMH080MZDE	106.273	3	30x35
3900	100	398LMH100MZDG	85.02	3.6	30x45
3900	100	398LMH100MZEE	85.02	3.6	35x35
4700	35	478LMH035MZBC	141.1	2.2	22x25
4700	50	478LMH050MZBF	123.46	2.5	22x40
4700	50	478LMH050MZCD	123.46	2.5	25x30
4700	63	478LMH063MZBG	105.82	3	22x45
4700	63	478LMH063MZCE	105.82	3	25x35
4700	80	478LMH080MZCH	141.1	3.3	25x50
4700	80	478LMH080MZDF	88.184	3.3	30x40
4700	80	478LMH080MZED	88.184	3.3	35x30
4700	100	478LMH100MZDH	70.547	3.8	30x50
5600	35	568LMH035MZBD	118.42	2.4	22x30
5600	35	568LMH035MZCC	118.42	2.4	25x25
5600	50	568LMH050MZBG	103.62	2.8	22x45
5600	50	568LMH050MZCE	103.62	2.8	25x35
5600	50	568LMH050MZDC	103.62	2.8	30x25
5600	63	568LMH063MZBH	88.81	3.3	22x50
5600	63	568LMH063MZCF	88.81	3.3	25x40
5600	63	568LMH063MZDD	88.81	3.3	30x30
5600	63	568LMH063MZEC	88.81	3.3	35x25
5600	80	568LMH080MZDG	74.01	3.7	30x45
5600	80	568LMH080MZEE	74.01	3.7	35x35
5600	100	568LMH100MZEG	59.21	4.1	35x45
6800	25	688LMH025MZBC	109.71	2.4	22x25
6800	35	688LMH035MZBE	97.52	2.6	22x35
6800	50	688LMH050MZBH	85.33	3.3	22x50
6800	50	688LMH050MZCF	85.33	3.3	25x40
6800	50	688LMH050MZDD	85.33	3.3	30x30
6800	50	688LMH050MZEC	85.33	3.3	35x25
6800	63	688LMH063MZCG	73.14	3.6	25x45
6800	63	688LMH063MZDE	73.14	3.6	30x35
6800	63	688LMH063MZED	73.14	3.6	35x30
6800	80	688LMH080MZDH	60.951	3.9	30x50
6800	80	688LMH080MZEF	60.951	3.9	35x40
8200	25	828LMH025MZBD	109.71	2.7	22x30
8200	25	828LMH025MZCC	109.71	2.7	25x25
8200	35	828LMH035MZBF	97.52	2.9	22x40
8200	35	828LMH035MZCD	97.52	2.9	25x30
8200	50	828LMH050MZCG	85.33	3.6	25x45
8200	50	828LMH050MZDE	85.33	3.6	30x35
8200	63	828LMH063MZDF	73.14	3.9	30x40
8200	63	828LMH063MZEE	73.14	3.9	35x35
8200	80	828LMH080MZEG	60.95	4.3	35x45
10000	16	109LMH016MZBC	82.89	2.6	22x25
10000	25	109LMH025MZBE	74.6	3	22x35
10000	35	109LMH035MZBG	66.32	3.2	22x45
10000	35	109LMH035MZCE	66.32	3.2	25x35
10000	35	109LMH035MZDC	66.32	3.2	30x25
10000	50	109LMH050MZCH	58.03	4	25x50
10000	50	109LMH050MZDF	58.03	4	30x40
10000	50	109LMH050MZED	58.03	4	35x30
10000	63	109LMH063MZDG	49.74	4.4	30x45
10000	63	109LMH063MZEF	49.74	4.4	35x40

Capacitance (μF)	WVDC	IC PART NUMBER	Maximum ESR (mΩ) 120 Hz, +20°C	Maximum RMS Ripple Current (A) 120 Hz, +105°C	Dims DxL (mm)
12000	10	129LMH010MZBC	75.99	2.2	22x25
12000	16	129LMH016MZBD	69.08	2.9	22x30
12000	16	129LMH016MZCC	69.08	2.9	25x25
12000	25	129LMH025MZBF	62.17	3.2	22x40
12000	25	129LMH025MZCD	62.17	3.2	25x30
12000	35	129LMH035MZBH	55.26	3.5	22x50
12000	35	129LMH035MZCF	55.26	3.5	25x40
12000	35	129LMH035MZDD	55.26	3.5	30x30
12000	35	129LMH035MZEC	55.26	3.5	35x25
12000	50	129LMH050MZDG	48.35	4.5	30x45
12000	50	129LMH050MZEE	48.35	4.5	35x35
12000	63	129LMH063MZEG	365.71	4.8	35x45
15000	10	159LMH010MZBD	60.79	2.3	22x30
15000	16	159LMH016MZBE	55.262	3.2	22x35
15000	25	159LMH025MZBG	49.74	3.6	22x45
15000	25	159LMH025MZCE	49.74	3.6	25x35
15000	25	159LMH025MZDC	49.74	3.6	30x25
15000	35	159LMH035MZCG	44.21	3.9	25x45
15000	35	159LMH035MZDE	44.21	3.9	30x35
15000	35	159LMH035MZED	44.21	3.9	35x30
15000	50	159LMH050MZDH	38.68	4.8	30x50
15000	50	159LMH050MZEF	38.68	4.8	35x40
15000	63	159LMH063MZEH	188.39	5.4	35x50
18000	10	189LMH010MZBD	50.657	2.4	22x30
18000	10	189LMH010MZCC	50.657	2.4	25x25
18000	16	189LMH016MZBF	46.05	3.5	22x40
18000	16	189LMH016MZCD	46.05	3.5	25x30
18000	25	189LMH025MZBH	41.45	3.9	22x50
18000	25	189LMH025MZCF	41.45	3.9	25x40
18000	25	189LMH025MZDD	41.45	3.9	30x30
18000	25	189LMH025MZEC	41.45	3.9	35x25
18000	35	189LMH035MZDF	36.84	4.3	30x40
18000	35	189LMH035MZEE	36.84	4.3	35x35
18000	50	189LMH050MZEG	32.24	5.2	35x45
22000	10	229LMH010MZBE	41.45	2.6	22x35
22000	10	229LMH010MZCD	41.45	2.6	25x30
22000	16	229LMH016MZBG	37.68	3.8	22x45
22000	16	229LMH016MZCE	37.68	3.8	25x35
22000	16	229LMH016MZDC	37.68	3.8	30x25
22000	25	229LMH025MZCG	33.91	4.3	25x45
22000	25	229LMH025MZDE	33.91	4.3	30x35
22000	25	229LMH025MZED	33.91	4.3	35x30
22000	35	229LMH035MZDG	30.14	5	30x45
22000	35	229LMH035MZEF	30.14	5	35x40
27000	10	279LMH010MZBF	33.77	3.1	22x40
27000	10	279LMH010MZCE	33.77	3.1	25x35
27000	16	279LMH016MZBH	30.7	4.2	22x50
27000	16	279LMH016MZCF	30.7	4.2	25x40
27000	16	279LMH016MZDD	30.7	4.2	30x30
27000	16	279LMH016MZEC	30.7	4.2	35x25
27000	25	279LMH025MZDF	27.63	4.8	30x40
27000	25	279LMH025MZEE	27.63	4.8	35x35
27000	35	279LMH035MZEG	24.56	5.3	35x45
33000	10	339LMH010MZBG	27.63	3.4	22x45
33000	10	339LMH010MZCF	27.63	3.4	25x40
33000	16	339LMH016MZCG	25.12	4.7	25x45
33000	16	339LMH016MZDE	25.12	4.7	30x35
33000	25	339LMH025MZDG	22.61	5.5	30x45

LMH

+105°C, standard 2000 hrs

Capacitance (μF)	WVDC	IC PART NUMBER	Maximum ESR (mΩ) 120 Hz, +20°C	Maximum RMS Ripple Current (A) 120 Hz, +105°C	Dims DxL (mm)
33000	25	339LMH025MZF	22.61	5.5	35x40
33000	35	339LMH035MZEH	20.1	5.9	35x50
39000	10	399LMH010MZCG	25.93	3.7	25x45
39000	10	399LMH010MZDD	25.93	3.7	30x30
39000	10	399LMH010MZEZ	25.93	3.7	35x25
39000	16	399LMH016MZDF	21.26	5.1	30x40
39000	16	399LMH016MZED	21.26	5.1	35x30
39000	25	399LMH025MZDH	19.13	5.8	30x50
39000	25	399LMH025MZEZ	19.13	5.8	35x45
47000	10	479LMH010MZCH	24.34	4.2	25x50
47000	10	479LMH010MZDE	24.34	4.2	30x35
47000	10	479LMH010MZED	24.34	4.2	35x30

Capacitance (μF)	WVDC	IC PART NUMBER	Maximum ESR (mΩ) 120 Hz, +20°C	Maximum RMS Ripple Current (A) 120 Hz, +105°C	Dims DxL (mm)
47000	16	479LMH016MZDG	22.58	5.5	30x45
47000	16	479LMH016MZEZ	22.58	5.5	35x35
47000	25	479LMH025MZEH	20.81	6.3	35x50
56000	10	569LMH010MZDF	23.09	5	30x40
56000	10	569LMH010MZEZ	23.09	5	35x35
56000	16	569LMH016MZDH	21.61	6	30x50
56000	16	569LMH016MZEH	21.61	6	35x50
68000	10	689LMH010MZDG	21.94	5.4	30x45
68000	10	689LMH010MZEZ	21.94	5.4	35x40
68000	16	689LMH016MZEZ	20.72	6.4	35x45
82000	10	829LMH010MZEZ	21.03	5.9	35x45
100000	10	104LMH010MZEZ	20.2259	6.5	35x50