






LOC		DIST	P	F	ZONE	LTR	REVISIONS		
CM		00					DESCRIPTION	DATE	APPD
						5	REVISED PER EC 063B-0597-02	25-OCT-02	KW DC

- 2 0.0008 MIN GOLD INSIDE RECEPTACLE IN LOCALIZED PLATE AREA, OVER 0.0008 MIN NICKEL.
3. EITHER CAVITY WILL ACCEPT RECEPTACLE 350628,640392 OR PIN 350629,640391.
- 4 REELED ON PLASTIC REELS.

-	-
.660	16.76
.375	9.53
.330	8.38
.200	5.08
.145	3.68
.130	3.30
.115	2.92
.110	2.79
.105	2.67
.095	2.41
.090	2.29
.085	2.16
.084	2.13
.082	2.08
.081	2.06
.079	2.01
.075	1.91
.050	1.27
.040	1.02
.025	0.63
.008	0.20
.005	0.13
.000030	0.0008
IN	MM
CONVERSION TABLE	



4	PRE-TIN	0.20 BRASS	1.27-2.79	24-18	350628-8
	2	0.20 PH.BRZ.	1.27-2.79	24-18	350628-6
	2	0.20 BRASS	1.27-2.79	24-18	350628-5
	PRE-TIN	0.20 PH.BRZ.	1.27-2.79	24-18	350628-2
	PRE-TIN	0.20 BRASS	1.27-2.79	24-18	350628-1
	FINISH	MATERIAL	INSULATION DIAMETER	WIRE RANGE	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON :		DR 9-30-91 K. SALMON	AMP INCORPORATED Harrisburg, Pa. 17105		
2 PLC DEC ± -		CHK 9-30-91 R. SWING			
3 PLC DEC ± 0.13		APPD 10-1-91 C. CASH	.062 SOCKET COMMERCIAL PIN & SOCKET		
ANGLES ± 0°30'		APPD 10-1-91 C. CASH			
MATERIAL		PRODUCT SPEC -	DRAWING NO 350628		
SEE TABLE		APPLICATION SPEC -			
FINISH		WEIGHT -	SIZE D	CAGE CODE 00779	SHEET 1 OF 1
SEE TABLE			SCALE 5:1		

