


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER*	WEIGHT lbs/100 pcs (g)/100 pcs	USE WITH ANY OF THESE CABLE TIES
CSH-	1.52 (690)	S,H



NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- CABLE TIE CROSS-SECTION CODE
S-STANDARD
H-HEAVY
- MATERIAL -20 PIGMENTED BLACK
-0 WEATHER RESISTANT BLACK

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G00239ES_PB_CSH_02.PRT

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

CSH CABLE SPACER

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY CGSM

MAT'L:

SCALE FULL

DATE 1/23/97

NYLON 6/6

DRAWING NO.

GB0239ES

DWG
A
SIZE

2	06/18/01	LGG		UPDATED FOR WEB (ADDED "REF")	GB0239ES	2							
1	10-20-97	JAD		REVISED GEOMETRY TO REFLECT CORRECT GEOMETRICAL CONFIGURATION	GB0239ES	1							
R	1/23/97	CGSM		INITIAL RELEASE	GB0239ES	R							
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP					