


NEW

MCBs DX³ 10000 - 16 kA

thermal magnetic circuit breakers from 1 A to 125 A (continued)



4 091 11



4 092 03



4 087 71



Auxiliaries and accessories

p. 66



Dimensions **see e-catalogue**
Technical characteristics **p. 68**

Conform to IEC 60898-1

Breaking capacity

10000 - IEC 60898-1 - 400 V~

16 kA - IEC 60947-2 - 400 V~

Can be equipped with DX³ auxiliaries and accessories (p. 66)

Pack	Cat.Nos	MCBs DX ³ 10000 - 16 kA - C curve	
	C curve	Single pole 230/400 V~	
		Nominal rating In (A)	Number of modules
1	4 091 07	1	1
1	4 091 08	2	1
1	4 091 09	3	1
1	4 091 11	6	1
10	4 091 12	10	1
1	4 091 13	13	1
10	4 091 14	16	1
1	4 091 15	20	1
1	4 091 16	25	1
1	4 091 17	32	1
1	4 091 18	40	1
1	4 091 19	50	1
1	4 091 20	63	1
1	4 085 99	80	1.5
1	4 086 00	100	1.5
1	4 086 01	125	1.5
	C curve	2-pole 230/400 V~	
		Nominal rating In (A)	Number of modules
1	4 091 95	1	2
1	4 091 96	2	2
1	4 091 97	3	2
1	4 091 99	6	2
1	4 092 00	10	2
1	4 092 01	13	2
1	4 092 02	16	2
1	4 092 03	20	2
1	4 092 04	25	2
1	4 092 05	32	2
1	4 092 06	40	2
1	4 092 07	50	2
1	4 092 08	63	2
1	4 086 40	80	3
1	4 086 41	100	3
1	4 086 42	125	3
	C curve	3-pole 400 V~	
		Nominal rating In (A)	Number of modules
1	4 092 47	1	3
1	4 092 48	2	3
1	4 092 49	3	3
1	4 092 51	6	3
1	4 092 52	10	3
1	4 092 53	13	3
1	4 092 54	16	3
1	4 092 55	20	3
1	4 092 56	25	3
1	4 092 57	32	3
1	4 092 58	40	3
1	4 092 59	50	3
1	4 092 60	63	3
1	4 086 62	80	4.5
1	4 086 63	100	4.5
1	4 086 64	125	4.5

Pack	Cat.Nos	MCBs DX ³ 10000 - 16 kA - C curve (continued)	
	C curve	4-pole 400 V~	
		Nominal rating In (A)	Number of modules
1	4 093 29	1	4
1	4 093 30	2	4
1	4 093 31	3	4
1	4 093 33	6	4
1	4 093 34	10	4
1	4 093 35	13	4
1	4 093 36	16	4
1	4 093 37	20	4
1	4 093 38	25	4
1	4 093 39	32	4
1	4 093 40	40	4
1	4 093 41	50	4
1	4 093 42	63	4
1	4 087 03	80	6
1	4 087 04	100	6
1	4 087 05	125	6

Pack	Cat.Nos	MCBs DX ³ 10000 - 16 kA - D curve	
	D curve	3-pole 400 V~	
		Nominal rating In (A)	Number of modules
1	4 087 69	80	4.5
1	4 087 70	100	4.5
1	4 087 71	125	4.5



For detailed dimensions,
see e-catalogue