



Product: [8418](#)

Ruggedized, flexible microphone cable, 8 Conductor 20 AWG, TC

Product Description

8 x 20 AWG stranded (26x34) high-conductivity TC conductors, rubber insulation, cotton wrap, rayon braid, TC braid shield (85% coverage), EPDM rubber jacket.

Technical Specifications

Product Overview

Suitable Applications:	Deployable, Portable Microphone for studio or live performance, Audio
------------------------	-----------------------------------------------------------------------

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	Nominal Diameter	No. of Conductors
Conductor(s)	20	26x34	High Conductivity Tinned Copper	0.037 in	8

Conductor Count: 8

Insulation

Element	Material	Nominal Diameter	Nominal Wall Thickness
Conductor(s)	EPDM - Ethylene Propylene Diene Monomer	0.083 in	0.023 in

Color Chart

Number	Color
1	Black
2	White
3	Brown
4	Green
5	Red
6	Yellow
7	Orange
8	Blue

Outer Shield Material

Type	Material	Coverage [%]
Braid	Rayon	
Braid	TC - Tinned Copper	85 %

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Separator Material
EPDM - Ethylene Propylene Diene Monomer	0.381 in	0.037 in	Cotton Serve

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR
10.2 Ohm/1000ft	10.2 Ohm/1000ft	2.4 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
30 pF/ft	55 pF/ft

Inductance

Nominal Inductance
0.18 μ H/ft

Impedance

Nominal Characteristic Impedance
52 Ohm

Current

Max. Recommended Current [A]
2.8 Amps per conductor @ 25°C

Voltage

Non-UL Voltage Rating
600 V

Temperature Range

Non-UL Temp Rating:	60°C
Operating Temp Range:	-50°C to +90°C

Mechanical Characteristics

Bulk Cable Weight:	100 lbs/1000ft
Max Recommended Pulling Tension:	116 lbs
Min Bend Radius/Minor Axis:	3.8 in

Standards

CPR Euroclass:	Fca
----------------	-----

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
8418 010100	Black	Reel	100 ft	612825206491
8418 010250	Black	Reel	250 ft	612825355281

Footnote: C - CRATE REEL PUT-UP.

History

Update and Revision:	Revision Number: 0.301 Revision Date: 05-19-2020
----------------------	--------------------------------------------------

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.