

Toroidal Cores T60D thru T80

COLOR CODE

- 2 Red/Clear
- 8 Yellow/Red
- 14 Black/Red
- 18 Green/Red
- 19 Red/Green
- 26 Yellow/White
- 30 Green/Gray
- 34 Gray/Blue
- 35 Yellow/Gray
- 38 Gray/Black
- 40 Green/Yellow
- 45 Black/Black
- 52 Green/Blue

TYPICAL PART NO.

T 106 - 26 /

OD in 100th inches
 Micrometals Mix No.
 Letter Indicates Alternate Height
 Code Area For Other Characteristics

					MAGNETIC DIMENSIONS		
MICROMETALS Part No.	A _L nH/N ²	OD in/mm	ID in/mm	Ht in/mm	ℓ cm	A cm ²	V cm ³
T60-26D	97.0	.600/15.2	.336/8.53	.470/11.9	3.74	.374	1.400
T60-52D	94.0						
T68-2	5.7	.690/17.5	.370/9.40	.190/4.83	4.23	.179	.759
T68-8/90	19.5						
T68-14	7.0						
T68-18	29.0						
T68-19	29.0						
T68-26	43.5						
T68-38	45.0						
T68-40	35.0						
T68-45	53.0						
T68-52	40.0						
T68-2A	7.0	.690/17.5	.370/9.40	.250/6.35	4.23	.242	1.03
T68-8A/90	26.0						
T68-14A	9.5						
T68-18A	39.5						
T68-19A	39.5						
T68-26A	58.0						
T68-38A	61.0						
T68-40A	47.0						
T68-45A	71.0						
T68-52A	54.0						
T68-2D	11.4	.690/17.5	.370/9.40	.375/9.53	4.23	.358	1.52
T68-14D	14.2						
T68-26D	87.0						
T68-40D	70.0						
T68-52D	80.0						
T69-45	120.0	.690/17.5	.336/8.53	.367/9.32	4.09	.394	1.61
T72-2	12.8	.720/18.3	.280/7.11	.260/6.60	4.01	.349	1.40
T72-8/90	36.0						
T72-18	60.0						
T72-26	90.0						
T72-40	71.0						
T72-52	82.0						
T80-2	5.5	.795/20.2	.495/12.6	.250/6.35	5.14	.231	1.19
T80-8/90	18.0						
T80-14	7.4						
T80-18	31.0						
T80-19	31.0						
T80-26	46.0						
T80-38	48.0						
T80-40	39.5						
T80-45	56.0						
T80-52	42.0						