


PACKAGE DIMENSIONS

SO8N/N-TP, SO14N, SO16N, SO16W, SO20W, SO24W, SO28W




Release A1, Page 1/4

SO8N



[mm]		
	Min.	Max.
A	4.80	4.98
B	1.27 BSC	
C	0.35	0.49
D	0.53 REF	
E	3.81	3.99
F	5.80	6.20
G	0.10	0.25
H	1.10	1.65
I	1.35	1.75
J	0.19	0.25
K	45 DEG	
L	0.41	1.27
M	0 DEG	8 DEG

SO8N-TP



[mm]		
	Min.	Max.
A	4.80	4.98
B	1.27 BSC	
C	0.35	0.49
D	0.53 REF	
E	3.81	3.99
F	5.80	6.20
G	0.10	0.25
H	1.10	1.65
I	1.35	1.75
J	0.19	0.25
K	45 DEG	
L	0.41	1.27
M	0 DEG	8 DEG
P	2.29	3.1
Q	2.29	2.4


PACKAGE DIMENSIONS

SO8N/N-TP, SO14N, SO16N, SO16W, SO20W, SO24W, SO28W




Release A1, Page 2/4

SO14N



[mm]		
	Min.	Max.
A	8.55	8.75
B	1.27 BSC	
C	0.35	0.49
D	0.51 REF	
E	3.81	3.99
F	5.80	6.20
G	0.10	0.25
H	1.10	1.65
I	1.35	1.75
J	0.19	0.25
K	45 DEG	
L	0.41	1.27
M	0 DEG	8 DEG

SO16N



[mm]		
	Min.	Max.
A	9.80	9.98
B	1.27 BSC	
C	0.35	0.49
D	0.51 REF	
E	3.81	3.99
F	5.80	6.20
G	0.10	0.25
H	1.10	1.65
I	1.35	1.75
J	0.19	0.25
K	45 DEG	
L	0.38	1.27
M	0 DEG	8 DEG


PACKAGE DIMENSIONS

SO8N/N-TP, SO14N, SO16N, SO16W, SO20W, SO24W, SO28W




Release A1, Page 3/4

SO16W



[mm]		
	Min.	Max.
A	10.11	10.31
B	1.27 BSC	
C	0.36	0.46
D	0.66 REF	
E	7.40	7.60
F	10.11	10.51
G	0.10	0.30
H	2.34	
I	2.44	2.64
J	0.23	0.32
K	45 DEG	
L	0.51	1.01
M	0 DEG	8 DEG

SO20W



[mm]		
	Min.	Max.
A	12.65	12.85
B	1.27 BSC	
C	0.36	0.46
D	0.66	
E	7.40	7.60
F	10.11	10.51
G	0.10	0.30
H	2.34	
I	2.44	2.64
J	0.23	0.32
K	45 DEG	
L	0.51	1.01
M	0 DEG	8 DEG


PACKAGE DIMENSIONS

SO8N/N-TP, SO14N, SO16N, SO16W, SO20W, SO24W, SO28W




Release A1, Page 4/4

SO24W



[mm]		
	Min.	Max.
A	15.20	15.40
B	1.27 BSC	
C	0.36	0.46
D	0.66 REF	
E	7.40	7.60
F	10.11	10.51
G	0.10	0.30
H	2.24	2.44
I	2.44	2.64
J	0.23	0.32
K	45 DEG	
L	0.51	1.01
M	0 DEG	8 DEG

SO28W



[mm]		
	Min.	Max.
A	17.73	17.93
B	1.27 BSC	
C	0.36	0.46
D	1.27 BSC	
E	7.40	7.60
F	10.11	10.51
G	0.10	0.30
H	2.34	
I	2.44	2.64
J	0.23	0.32
K	45 DEG	
L	0.51	1.01
M	0 DEG	8 DEG

For additional information on component handling, preconditioning and soldering conditions, refer to the relevant iC-Haus customer information files, available separately.