




SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

- NOTES:
1. Rating:300V 20A(UL) ;
 2. Insulation Withstanding Voltage:AC2000V/MIN
 3. Insulation Resistance: $\geq 500M\Omega$ or more at DC500V
 4. Temperature Range: $-33^{\circ}C/+105^{\circ}C$
 5. Screw Torque Vlaue:4.5 lbf-in(UL)
 6. Suitable Electric Wire: 12-20AWG
 8. Housing: Nylon PA66
 9. Screw M3, Stell, Zinc Plated
 10. Standard Color: Natural

RoHS Compliant

DIM	P	2	3	4	5	6	7	8	9	10	11	12
L		16.6	26.6	36.6	46.6	56.6	66.6	76.6	86.6	96.6	106.6	116.6
TOL (±)		0.08	0.12	0.16	0.20	0.24	0.28	0.32	0.36	0.40	0.44	0.48

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

ON-SHORE TECHNOLOGY, INC.					
TITLE	ES1000 Series - 10.0mm Euro Strip, Wire guard, flat base				
PART NO.	ES1000/XXDSFB	DCX - number of poles per row	DWG NO.	ES1000/XXDSFB.DWG	
APPROVED	CHECKED	DESIGNED	DRAWN	5020	Tolerance
KSZ 2007.08.01	KSZ 2007.08.01	KSZ 2007.08.01	KSZ 2007.08.01		UNIT: mm SCALE: NONE REV: A
SHEET: 01/01				Tolerance .X ±015 .XX ±0.075 .XXX ±0.05	