

PRODUCT BRIEF

KEY FEATURES

- ▶ Very low power consumption (uncooled pump)
- ▶ Micro 45x70x12 mm form factor
- ▶ Up to 16 dBm output power
- ▶ Fast power transient suppression for stable output power
- ▶ Can support G.657 low bend radius fiber pigtails
- ▶ Pre-amplifier or booster configuration

APPLICATIONS

- ▶ Pre-amp or Booster for 40 Gb/s and 100 Gb/s transponder line cards
- ▶ Very long reach 10 Gb/s applications
- ▶ Submarine networks
- ▶ Military and industrial applications requiring small size and low power consumption
- ▶ Single channel networks

OVERVIEW

Finisar's Single Channel Micro EDFA is a cost-effective micro processor-controlled module for amplifying single channels in the C-band. The amplifier is provided in a micro 45x70x12 mm package, and exhibits low power consumption allowing it to be easily integrated onto space and power constrained transponder line cards. The EDFA can be configured as either pre-amplifier or booster.

In order to support 40 Gb/s and 100 Gb/s applications, the amplifier provides excellent broadband noise performance. Fast transient suppression circuitry is also provided, allowing the amplifier output power to be kept constant when there are fast changes in input power.



Single Channel Micro EDFA

KEY OPTICAL SPECIFICATIONS

Parameter	Specifications			Remarks
	Min.	Max.	Units	
Wavelength Range	1528.77	1567.13	nm	
Input Power Range	-10	5	dBm	
Output Power Range	0	16	dBm	
Operational Gain	5	26	dB	
Noise Figure		6.5 11	dB dB	At -10 dBm input with 26dB signal gain At 5 dBm input with 5 dB signal gain
Transient Overshoot / Undershoot	-0.5	0.5	dB	Rise / fall time > 1msec, Input power change < 6 dB, Signal output power (APC) = +16dBm
Power consumption		2.5	W	Over case temp range to EOL
Power Supply	2.97	3.63	V	
Operating Case Temperature	0	70	°C	
Storage Temperature Range	-40	85	°C	
Dimensions (WxHxD)	45x70x12		mm	
Laser safety	Class 1M*			

* Class 1M products are not hazardous under normal circumstances, but may pose an eye hazard when the laser output is viewed with certain optical instruments (for example eye loupes, magnifiers and microscopes) within a distance of 100 mm

Finisar®

1389 Moffett Park Drive
Sunnyvale, CA 94089-1133
www.finisar.com

Phone: +1-408-548-1000
Sales: +1-408-541-5690
Email: sales@finisar.com

© 2014 Finisar Corporation. All rights reserved. Finisar is a registered trademark of Finisar Corporation.
Features and specifications are subject to change without notice. 05/14



Visit Our Website

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Finisar:](#)

[50-11-0236-01R](#)