


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART, CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISONS		DOC. NO.	SPC-F005	Effective:	7/8/02	DCP No:	1398	
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRD	DATE
1343	A	RELEASED	HO	11/25/02	JWM	12/2/02	DJC	12/5/02

Overall Length 9 Inches



SPECIFICATION:

- WIRE STRIPPER FROM 10 ~ 22 AWG.
- CRIMPING 10 ~ 22 AWG INSULATED TERMINALS.
- CRIMPING 10 ~ 22 AWG NON-INSULATED TERMINALS.
- BOLT CUTTER FOR 10-24, 6-32, 8-32, 10-32, 4-40.
- WIRE CUTTER.
- MADE OF HEAT - TREATED AND HARDENED STEEL.

DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWING TITLE: CRIMPING AND STRIPPING TOOL

DRAWN BY: HISHAM ODISH

DATE: 11/25/02

SCALE: NTS

CHECKED BY: JEFF MCVICKER

DATE: 12/2/02

SIZE: A

DWG. NO.: SPC11307

APPROVED BY: DANIEL CAREY

DATE: 12/5/02

SCALE: NTS

U.O.M.: INCHES

DRAWN BY: HISHAM ODISH

DATE: 11/25/02

SIZE: A

DWG. NO.: SPC11307

CHECKED BY: JEFF MCVICKER

DATE: 12/2/02

SCALE: NTS

U.O.M.: INCHES

APPROVED BY: DANIEL CAREY

DATE: 12/5/02

SCALE: NTS

U.O.M.: INCHES

ELECTRONIC FILE: 34C7550.DWG

REV: A

SHEET: 1 OF 1