

Heyco® Blade-Ground Pin-Blade Series: BGB and BGMT

Blade-Pin-Blade/Blade-Tab-Pin Strip Sequences:

One shot, one operator, one die terminating!

NEMA 1-15P & 5-15P – .058" Mold Line Thickness

For mating Female Cord Connectors, see page 8-54.

For Male Ground Pins, see pages 8-45 & 8-46.

For Full Thickness Male/Female Combination Terminals, see pages 8-59 & 8-60.

PART DATA			PART NO.		APPLICATION TOOLING*				
Blade Profile	AWG Range	Material	Non-polarized	Polarized	Die**	Feeds	Tool Pack	Crimp Punch	Anvil

BGB Series – Blade-Ground Pin-Blade

Flat	18-14	Brass Post-Ni	5790	-	5790UXX5	Left to Right	B280L/B281L	C453	C327
			5794	-	5794UXX5				
7-Shape	18-14	Brass Tin-Pl	5792	-	5792UXX5	Right to Left	B280R/B281R		
		Brass	5796	-	5796UXX5				
			5793	-	5793UXX5				

alternate tooling for above BGB'S:

	18						B282L/B283L	C798	C327
	16						B284L/B285L	C799	
	14						B286L/B287L	C800	


BGMT Series – Blade-Male Tab-Ground Pin

Flat	18-14	Brass	5797	-	Consult Heyco	Left to Right	Consult Heyco		
------	-------	-------	-------------	---	---------------	---------------	---------------	--	--


7-Shape Blades feature a retention ledge to maintain position during overmolding (mold stop).

* Use the Heyco Universal Applicator Die (indicated by "U" in the Die Part No.), page 8-63.

** "XX" represents Wire Gauge. Please specify Wire Gauge when ordering.



BGB Series



BGMT Series

Materials	Alloy 260 Brass (70% Cu, 30% Zn. Higher Cu content resists dezincification) Tin-Pl = Brass, Tin plated before or after stamping Post-Ni = Brass, Nickel plated after stamping
Certifications	Recognized Component under UL File E164169 Certified by the Canadian Standards Association File 91824
Standards	NEMA 1-15P & NEMA 5-15P

Quick Specs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[7341](#)