





338919-1 Product Details

[Share](#) [Print](#) [Email](#)

338919-1

TE Internal Number: 338919-1

 Active

 [View 3D PDF](#)

2mm Centerline Futurebus+ Connectors

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Module Type = Signal
- 30 Signal Positions
- Connector
- Connector Assembly
- Cable Application

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Z-PACK 2mm FB+ UNSHIELDED CABLE CONNECTOR 30 POS. KIT \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing](#) (DXF, Version C)
- [3D Model](#) (IGES, Version C)
- [3D Model](#) (STEP, Version C)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- Connector Type = Connector Assembly
- Wire Size (mm² [AWG]) = 0.25-0.40² [30-26]

Mechanical Attachment:

- [Module Type](#) = Signal

Electrical Characteristics:

- Voltage Rating (VAC) = 30

Body Features:

- [Number of Signal Positions](#) = 30
- [Number of Rows](#) = 5
- Cable Diameter (Max.) (mm [in]) = 7.50 [0.295]
- Centerline, Matrix (mm [in]) = 2.00 x 2.00 [.079 x .079]

Contact Features:

- Contact Type = Socket
- Contact Base Material = Phosphor Bronze
- Contact Plating, Mating Area, Material = Gold (30)

Housing Features:

- Connector Style = Receptacle
- Housing Material = Liquid Crystal Polymer (LCP)

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Applies To = Cable

Operation/Application:

- Application = Cable

Other:

- Brand = AMP

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

