



ESD-115-TT-05

SS, SD, ESD, ESS, HSS SERIES

PRECISION MACHINED SOCKET STRIPS

TS, TD, HTS, BBS,
BBD, BBL, BDL, BHS

For complete specifications see www.samtec.com?SS, www.samtec.com?ESS, www.samtec.com?SD, www.samtec.com?ESD or www.samtec.com?HSS

Lead-Free Solderable:
Wave only

For complete scope
of recognitions see
www.samtec.com/quality



TYPE STRIP	1	NO. PINS PER ROW	PLATING OPTION	LEAD STYLE	OPTION	OTHER OPTION
			-S = 10 μ" (0.25 μm) Gold contact, Tin shell (Styles 2 & 22 only)		-L = Locking Socket Add -L suffix for locking lead socket in end positions. Requires Style -2 or -22 and .035" ± .003 DIA board hole.	-N = Non Flush N/A Style -5A
			-T = 30 μ" (0.76 μm) Gold contact, Tin shell		 Requires -T Plating Option	
			-G = 30 μ" (0.76 μm) Gold contact, 10 μ" (0.25 μm) Gold shell			
			-TT = Tin contact and shell (Styles 1, 2, 4, and 05 except LIF N/A)			
LIF= Low Insertion Force						
SS = Standard Single Row Socket		HSS = High Temp Single Row Socket			ALSO AVAILABLE (MOQ Required) • Locking lead option on ESS and ESD series	
ESS = Elevated Single Row Socket Styles -5A & -05 socket heads not countersunk.						

ALSO AVAILABLE
(MOQ Required)

- Locking lead option on ESS and ESD series

For complete scope
of recognitions see
www.samtec.com/quality



SD
= Standard Double Row Socket

ESD
= Elevated Double Row Socket

**Style -5A not available.
Styles -5A & -05 socket
heads not countersunk.**

Technical drawings showing dimensions for SD and ESD socket types. The top drawing shows the top view with dimensions: (2.54) .100 x No. of Positions, (2.54) .100, and (2.54) .100 TYP. The bottom drawing shows the side view with dimensions: (2.54) .100, (5.08) .200, and (2.54) .100. The drawings illustrate the standard double row socket (SD) and the elevated double row socket (ESD) configurations.

Note:
Some lengths, styles and options are non-standard, non-returnable.

-1A, -1B or -1C

For LIF specify -21A, -21B or -21C
(SS, HSS, SD)

LEAD STYLE	Y
-1A or -21A	(9.14) .360
-1B or -21B	(12.95) .510
-1C or -21C	(6.60) .260

-2, -22*, -5A, or -38*

*For LIF specify -22 or -38 (SS, HSS, SD)

LEAD STYLE	X DIA	Y	Z
-2 or -22	(0.51) .020	(3.18) .125	(7.62) .300
-38	(0.51) .020	(4.57) .180	(8.89) .350
-5A	(0.89) .035	(12.95) .510	(17.86) .703

Locking lead available. See OPTION.

Diagram illustrating the dimensions of the lead style:

- A**: Total length of the lead style.
- B**: Length of the rectangular section.
- C**: Length of the tapered section.
- Rectangular section dimensions: (0.76) length, 0.030 diameter.
- Tapered section dimensions: (0.64) length, 0.025 SQ diameter.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.