





THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT - By -		ALL RIGHTS RESERVED.	
DESCRIPTION	MATERIAL	FINISH	
MODULE ASSEMBLY	D.A.P. PER MIL-M14 TYPE SDG-F	COLOR: GREEN	
GROMMET	FLOURSILICONE RUBBER 70/30 BLEND	COLOR: GREEN	
CONTACT SOCKET	BERYLLIUM COPPER ASTM-B194	GOLD PLATE PER MIL-G-45204	
RETAINING CLIP	BERYLLIUM COPPER ASTM-B194 OR STAINLESS STEEL PER QQ-S-766	NONE	
RESISTOR	RLR07C2201JS	NONE	
SEALING PLUGS QTY 2	F.E.P. PER MIL-P-19468	COLOR: RED	
PIN CONTACT QTY = 4 P/N M39029/1-101	COPPER ALLOY PER MIL-C-39029	GOLD PLATE PER MIL-G-45204	

LOC	DIST	REVISIONS				
DF	A0	P	LTR	DESCRIPTION	DATE	DWN
		D		REVISED PER ECO-12-010820	25JUN12	PY



SCHEMATIC DIAGRAM
(2) 2200 OHM, 1/4 WATT, ±5%
RLR07C2201JS



1 MARK MODULE ASSEMBLY WITH "AMP", TE PART NO.,
AND DATE CODE .060 MIN CHARS PER 115-10002-2

591871-1
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	16AUG99	TE Connectivity		
		CHK	8-20-99			
		APVD	8-20-99	NAME		
		PRODUCT SPEC				
		APPLICATION SPEC		MODULE FEED-BACK ASSEMBLY SIZE 20 TJ WITH TWO RCR07G222JS RESISTORS		
		WEIGHT	-	SIZE	CAGE CODE	DRAWING NO
				A2	00779	C=591871
		CUSTOMER DRAWING		SCALE	4:1	SHEET 1 of 1