






FCIconnect.com

Copyright FCI

PRODUCT NUMBER


SEE NOTE 1




mat'l. code NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC			
ltr	ecn	no	dr	date		tolerances unless otherwise specified				title			
C	V13313	MRC		12/19/91		angles	linear	.XX ±.01/.3		4 ROW R/A HEADER SOLDER TO BOARD, 1 GP			
D	V23813	MRC		1/07/93				.XXX ±.005/.13					
E	V40228	PDP		1/11/94				.XXXX ±.0020/.051					
				0°±2'				scale 1:1					
F	V50270	SAR		3/10/95		dr	D. SHEAFFER	6/05/91		dwg no			
G	V90523	HTB		3/01/99		enfr	S. CLARK	6/05/91		sheet 1 of 2 size			
H	V00262	JWS		1/26/00		chr	S. CLARK	6/05/91		50123			
J	M06-0255	AEA		7/06/06		appd	S. CLARK	6/05/91		A3			
										type Product Customer Drawing			
sheet	revision	J	J										
index	sheet	1	2										

form: A3


PRODUCT NUMBER	DIM	LENGTH FORMULAS
SEE NOTE 1	DIM "A"	.100/2.54 x NO. OF COLUMNS + 1.05/26.7
	DIM "B"	.100/2.54 x NO. OF COLUMNS + .750/19.05
	DIM "C"	.100/2.54 x NO. OF COLUMNS DIVIDED BY 2 - .100/2.54



SECTION U-U



SECTION W-W



SECTION X-X


NOTES:

- ① PRODUCT NUMBERING CODE:
 50123 - X YYY Z
 X = TAIL LENGTH (NOTE 5)
 YYY = NO. OF POSITIONS (NOTE 2)
 Z = PLATING (NOTE 4)
 BASE NUMBER

PRODUCT NUMBERING CODE FOR
 SELECT LOAD PART NUMBERS:

- 50123 - XXYYY
 XX = SEQUENCE NUMBER
 ALWAYS 'XX'
 YYY = BASE NUMBER

- ② THIS PRODUCT IS CONFIGURED IN SIZES OF 20 THRU 122 COLUMNS IN INCREMENTS OF TWO.
 i.e.: 20,22,24,26,.....118,120,122.
- ③ HOUSING MATERIAL: GLASS AND MINERAL FILLED HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER UL94V-0. COLOR: BLACK.
 PIN MATERIAL: PHOS. BRONZE
- ④ PLATING OPTIONS:
 1 = 30u"/.76u GOLD
 3 = 50u"/1.27u GOLD
 5 = 30u"/.76u GXT
- ⑤ TAIL LENGTH OPTIONS:
 H = .180/4.57
 J = .120/3.05
- ⑥ MANUFACTURE'S NAME, P/N, AND LOT CODE TO APPEAR ON THIS SURFACE PER BUS-12-108.
7. FOR DOCUMENTATION MENU, SEE SPEC. BUS-01-057.



RECOMMENDED PCB LAYOUT
 (ALL HOLES LOCATED ON .100/2.54 GRID
 UNLESS OTHERWISE SPECIFIED)

mat'l. code				surface		tolerance	projection	product family	
-				ISO 1302		ISO 406 ISO 1101	ISO 1101	HPC	
ltr	ecn	no	dr	date	tolerances unless otherwise specified			title	
J					angles	linear	.XX ±.01/.3 .XXX ±.005/.13 .XXXX ±.0020/.051	4 ROW R/A HEADER SOLDER TO BOARD, 1 GP	
				dr	D. SHEAFFER	6/05/91	FCI	dwg no	
				enr	S. CLARK	6/05/91		sheet 2 of 2	
				chr	S. CLARK	6/05/91		size	
				appd	S. CLARK	6/05/91		A3	
sheet	revision						type		Product Customer Drawing
index	sheet								