

Surface Mount Ultrafast Rectifier


DO-214AC (SMA)

FEATURES

- Low profile package
- Ideal for automated placement
- Glass passivated chip junction
- Ultrafast reverse recovery time
- Low switching losses, high efficiency
- High forward surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Solder dip 260 °C, 40 s
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC


RoHS
COMPLIANT

TYPICAL APPLICATIONS

For use in high frequency rectification and freewheeling application in switching mode converters and inverters for consumer, computer, automotive and telecommunication.

MECHANICAL DATA

Case: DO-214AC (SMA)

Epoxy meets UL 94V-0 flammability rating

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD22-B102

E3 suffix for consumer grade, meets JESD 201 class 1A whisker test, HE3 suffix for high reliability grade (AEC Q101 qualified), meets JESD 201 class 2 whisker test

Polarity: Color band denotes cathode end

PRIMARY CHARACTERISTICS

$I_{F(AV)}$	1.0 A
V_{RRM}	50 V to 1000 V
I_{FSM}	30 A
t_{rr}	50 ns, 75 ns
V_F	1.0 V, 1.7 V
$T_J \text{ max.}$	150 °C

MAXIMUM RATINGS ($T_A = 25\text{ °C}$ unless otherwise noted)

PARAMETER	SYMBOL	US1A	US1B	US1D	US1G	US1J	US1K	US1M	UNIT
Device marking code		UA	UB	UD	UG	UJ	UK	UM	
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current at $T_L = 110\text{ °C}$	$I_{F(AV)}$	1.0							A
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I_{FSM}	30							A
Operating and storage temperature range	T_J, T_{STG}	- 55 to + 150							°C

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)											
PARAMETER	TEST CONDITIONS		SYMBOL	US1A	US1B	US1D	US1G	US1J	US1K	US1M	UNIT
Maximum instantaneous forward voltage ⁽¹⁾	1.0 A		V _F	1.0				1.7			V
Maximum DC reverse current at rated DC blocking voltage		T _A = 25 °C T _A = 100 °C	I _R	10 50							μA
Maximum reverse recovery time	I _F = 0.5 A, I _R = 1.0 A, I _{rr} = 0.25 A		t _{rr}	50				75			ns
Typical junction capacitance	4.0 V, 1 MHz		C _J	15				10			pF

Note:(1) Pulse test: 300 μs pulse width, 1 % duty cycle

THERMAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)										
PARAMETER	SYMBOL		US1A	US1B	US1D	US1G	US1J	US1K	US1M	UNIT
Maximum thermal resistance ⁽¹⁾	$R_{\theta JA}$ $R_{\theta JL}$		75 27							$^{\circ}\text{C/W}$

Note:

(1) P.C.B. mounted on 0.2 x 0.2" (5.0 x 5.0 mm) copper pad area

ORDERING INFORMATION (Example)				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
US1J-E3/61T	0.064	61T	1800	7" diameter plastic tape and reel
US1J-E3/5AT	0.064	5AT	7500	13" diameter plastic tape and reel
US1JHE3/61T ⁽¹⁾	0.064	61T	1800	7" diameter plastic tape and reel
US1JHE3/5AT ⁽¹⁾	0.064	5AT	7500	13" diameter plastic tape and reel

Note:

(1) Automotive grade AEC Q101 qualified


RATINGS AND CHARACTERISTICS CURVES($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

Figure 1. Forward Current Derating Curve




Figure 2. Maximum Non-Repetitive Peak Forward Surge Current




Figure 3. Typical Instantaneous Forward Characteristics




Figure 6. Typical Reverse Leakage Characteristics




Figure 4. Typical Reverse Leakage Characteristics




Figure 7. Typical Junction Capacitance




Figure 5. Typical Instantaneous Forward Characteristics






Figure 8. Typical Transient Thermal Impedance

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

DO-214AC (SMA)



Mounting Pad Layout





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[US1B/1T](#) [US1B-E3/1T](#) [US1G/1T](#) [US1G-E3/1T](#) [US1J/1T](#) [US1J-E3/1T](#) [US1M/1T](#) [US1M-E3/1T](#) [US1A/13T](#)
[US1A/5AT](#) [US1A/61T](#) [US1A/63T](#) [US1A-E3/2GT](#) [US1A-E3/5AT](#) [US1A-E3/63T](#) [US1AHE3/2GT](#) [US1AHE3/5AT](#)
[US1AHE3/61T](#) [US1AHE3/63T](#) [US1B/2FT](#) [US1B/2GT](#) [US1B/51T](#) [US1B/5AT](#) [US1B/61T](#) [US1B/63T](#) [US1B-E3/2GT](#)
[US1B-E3/51T](#) [US1B-E3/5AT](#) [US1B-E3/63T](#) [US1BHE3/2GT](#) [US1BHE3/5AT](#) [US1BHE3/61T](#) [US1BHE3/63T](#)
[US1D/13T](#) [US1D/2FT](#) [US1D/2GT](#) [US1D/5AT](#) [US1D/61T](#) [US1D/63T](#) [US1D-E3/11T](#) [US1D-E3/2GT](#) [US1D-E3/5AT](#)
[US1D-E3/63T](#) [US1DHE3/2GT](#) [US1DHE3/5AT](#) [US1DHE3/61T](#) [US1DHE3/63T](#) [US1G/11T](#) [US1G/13T](#) [US1G/2FT](#)
[US1G/2GT](#) [US1G/51T](#) [US1G/5AT](#) [US1G/61T](#) [US1G/63T](#) [US1G-E3/11T](#) [US1G-E3/2GT](#) [US1G-E3/51T](#) [US1G-](#)
[E3/5AT](#) [US1G-E3/63T](#) [US1GHE3/2GT](#) [US1GHE3/5AT](#) [US1GHE3/61T](#) [US1GHE3/63T](#) [US1J/11T](#) [US1J/13T](#)
[US1J/2FT](#) [US1J/2GT](#) [US1J/51T](#) [US1J/5AT](#) [US1J/61T](#) [US1J/63T](#) [US1J-E3/11T](#) [US1J-E3/2GT](#) [US1J-E3/51T](#)
[US1J-E3/5AT](#) [US1J-E3/63T](#) [US1JHE3/2GT](#) [US1JHE3/5AT](#) [US1JHE3/61T](#) [US1JHE3/63T](#) [US1K/11T](#) [US1K/51T](#)
[US1K/5AT](#) [US1K/61T](#) [US1K-E3/5AT](#) [US1KHE3/5AT](#) [US1KHE3/61T](#) [US1M/13T](#) [US1M/2FT](#) [US1M/2GT](#) [US1M/51T](#)
[US1M/5AT](#) [US1M/61T](#) [US1M/63T](#) [US1M-E3/11T](#) [US1M-E3/2GT](#) [US1M-E3/51T](#) [US1M-E3/5AT](#) [US1M-E3/63T](#)