


- Operational Areas
- Microphones.
 - Wiring of mixing desks.
 - Wiring of patchpanels.
 - Balanced and unbalanced audio lines.
 - Musical instrument digital interface.
 - Intercom cables.

Technical Specification	
Conductor	
Resistance	<=110 Ohm/km
Shielding	
Resistance	<=20 Ohm/km
Capacitance	Cond/Cond: 160nF/km Cond/Shield: 220nF/km
Test Voltage	Cond/Cond: 500 Veff Cond/Shield: 2000 Veff

Dimensions



- | | |
|-------------------------------|--|
| 1 - JACKET | PVC, Ø5.4mm ±0.30mm
Black, red, grey, blue, mint, yellow |
| 2 - SHIELD NO.1 | Bare copper wires, (0.10mm) |
| 3 - SHIELD NO.2 | Bare copper wires, (0.10mm) |
| 4 - PVC SEPERATION | Ø3.10mm ±0.15mm, white, tube |
| 5 - INSULATION
(CONDUCTOR) | PVC, Ø0.12mm ±0.05mm, wrapped twisted pair,
colours are white and brown |
| 6 - CONDUCTOR | Bare copper wire, 48x0.07mm (0.18mm) |

Ordering Data	
Reels at	100m
Weight/reel	4.40 kg
Weight/metre	0.037 kg
Colours	Black, Red, Grey, Blue, Mint, Yellow

Deltron No	Type	Deltron No	Type
439-0140	BLACK	439-0240	BLUE
439-0540	RED	439-0440	MINT
439-0940	GREY	439-0740	YELLOW

CONVERTED FROM PS0007 ISS2 (25.11.93) IN JAN 2003