

M/A-COM GaAs Broadband SPDT Switch

DC - 6.0 GHz

V1

MASWSS0070

MASWSS0070

Features

- 802.11a + b/g Dual Band Applications
- Broadband Performance: DC - 6.0 GHz
- Low Insertion Loss: 0.75 dB at 6.0 GHz
- High Isolation: 25 dB Typical
- Low Cost 3 mm FQFP-N 12 Lead Package
- Fast Switching Speed: 0.5 μ m GaAs PHEMT Process

Description

M/A-COM's MASWSS0070 is a broadband GaAs PHEMT MMIC SPDT switch in a low cost 3 mm FQFP-N 12 lead package (JEDEC). The MASWSS0070 is ideally suited for applications where very small size and low cost are required.

Typical applications are for WLAN IEEE 802.11a and 802.11b/g PC cards and access points. Designed for high power, this SPDT switch maintains high linearity up to 6.0 GHz.


The MASWSS0070 is fabricated using a 0.5 micron gate length GaAs PHEMT process. The process features full passivation for performance and reliability.

Ordering Information ¹

Part Number	Package
MASWSS0070	FQFP-N 12-lead Plastic Package
MASWSS0070TR	7 inch, 1000 piece reel
MASWSS0070TR-3000	13 inch, 3000 piece reel
MASWSS0070SMB	Sample Test Board (Includes 5 Samples)

1. Reference Application Note M513 for reel size information.

Functional Schematic



Pin Configuration

PIN No.	PIN Name	Description
1	V _{C1}	Control 1
2	RF1	RF Port
3	GND	Ground
4	GND	Ground
5	GND	Ground
6	GND	Ground
7	GND	Ground
8	RF2	RF Port
9	V _{C2}	Control 2
10	GND	Ground
11	RFC	RF Port
12	GND	Ground

M/A-COM Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.

Visit www.macom.com for additional data sheets and product information.

tyco / Electronics

M/A-COM

■ North America: Tel. (800) 366-2266
 ■ Asia/Pacific: Tel. +81-44-844-8296, Fax +81-44-844-8298
 ■ Europe: Tel. +44 (1908) 574 200, Fax +44 (1908) 574 300

Electrical Specifications: $T_A = 25^\circ\text{C}$, $Z_0 = 50\ \Omega$, $V_C = 0\ \text{V} / 3\ \text{V}$, 8 pF Capacitor^{2,3}

Parameter	Test Conditions	Units	Min.	Typ.	Max.
Insertion Loss ³	2 - 3 GHz	dB		0.55	0.9
	3 - 4 GHz	dB		0.55	0.9
	4 - 5 GHz	dB		0.65	1.0
	5 - 6 GHz	dB		0.75	1.1
Isolation	2 - 6 GHz	dB	22	25	
Return Loss	DC - 6 GHz	dB		20	
IIP2	Two Tone, +5 dBm/Tone, 5 MHz Spacing, > 50 MHz $V_C = 0.0\ \text{V}/3\ \text{V}$ @ 2.4 GHz $V_C = 0.0\ \text{V}/3\ \text{V}$ @ 5.8 GHz $V_C = 0.0\ \text{V}/5\ \text{V}$ @ 2.4 GHz $V_C = 0.0\ \text{V}/5\ \text{V}$ @ 5.8 GHz	dBm		90	
		dBm		84	
		dBm		91	
		dBm		85	
IIP3	Two Tone, +5 dBm/Tone, 5 MHz Spacing, > 50 MHz $V_C = 0.0\ \text{V}/3\ \text{V}$ @ 2.4 GHz $V_C = 0.0\ \text{V}/3\ \text{V}$ @ 5.8 GHz $V_C = 0.0\ \text{V}/5\ \text{V}$ @ 2.4 GHz $V_C = 0.0\ \text{V}/5\ \text{V}$ @ 5.8 GHz	dBm		46	
		dBm		40	
		dBm		47	
		dBm		41	
Input P-1dB	$V_C = 0.0\ \text{V}/3\ \text{V}$ @ 2.4 GHz $V_C = 0.0\ \text{V}/3\ \text{V}$ @ 5.8 GHz $V_C = 0.0\ \text{V}/5\ \text{V}$ @ 2.4 GHz $V_C = 0.0\ \text{V}/5\ \text{V}$ @ 5.8 GHz	dBm		30	
		dBm		29	
		dBm		31	
		dBm		31	
T-rise, T-fall	10% to 90% RF and 90% to 10% RF	nS		13	
Ton, Toff	50 - 350 MHz	nS		35	
Transients	$V_C = 5\ \text{V}$, square wave, in band	mV		14	
Control Current	$ V_C = 3\ \text{V}$	μA		10	25

2. External DC blocking capacitors are required on all RF ports.

3. Insertion loss can be optimized by varying the DC blocking capacitor value.

Absolute Maximum Ratings⁴

Parameter	Absolute Maximum
Max Input Power @ 3V Control	+32 dBm
Max Input Power @ 5V Control	+34 dBm
Operating Voltage	+8.5 volts
Operating Temperature	-40 °C to +85 °C
Storage Temperature	-65 °C to +150 °C

4. Exceeding any one or combination of these limits may cause permanent damage.

Qualification

Qualified to M/A-COM Specification Rel 201, Process Flow -2.


Handling Procedures

The following precautions should be observed to avoid damage:

Static Sensitivity


Gallium Arsenide Integrated Circuits are sensitive to electrostatic discharge (ESD) and can be damaged by static electricity. Proper ESD control techniques should be used when handling these devices.

3 mm FQFP-N 12 Lead




- NOTES: 1. REFERENCE JEDEC MO-220, VAR. VEED-1 FOR ADDITIONAL DIMENSIONAL AND TOLERANCE INFORMATION.
2. REFERENCE S2083 APPLICATION NOTE FOR PCB FOOTPRINT INFORMATION.
3. ALL DIMENSIONS SHOWN AS INCHES/MILL

Evaluation Board



Application Schematic

Truth Table ⁵

Control V1	Control V2	RFC- RF1	RFC- RF2
1	0	On	Off
0	1	Off	On

5. 1 = +2.9 V to +5 V, 0 = 0 V $\pm$ 0.2 V.

Application #1: Optimized for 802.11a

Qty	Description
3	Capacitor, 3.0 pF, 0402, SMT, 5% (C1-C3)

Application #2: Optimized for 802.11b/g


Qty	Description
3	Capacitor, 8.0 pF, 0402, SMT, 5% (C1-C3)

M/A-COM Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.


Visit www.macom.com for additional data sheets and product information.

Typical Performance Curves with 0/3 V Control, 8 pF Capacitors


Insertion Loss vs. Frequency



Isolation vs. Frequency



Return Loss vs. Frequency



M/A-COM Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.

Visit www.macom.com for additional data sheets and product information.

■ **North America:** Tel. (800) 366-2266
 ■ **Asia/Pacific:** Tel. +81-44-844-8296, Fax +81-44-844-8298
 ■ **Europe:** Tel. +44 (1908) 574 200, Fax +44 (1908) 574 300

S-Parameters

Insertion

Temp: Freq (GHz)	+25 C S11 (dB)	+25 C S21 (dB)	+25 C S22 (dB)	-35C S11 (dB)	-35 C S21 (dB)	-35 C S22 (dB)	+85 C S11 (dB)	+85 C S21 (dB)	+85 C S22 (dB)
1.00	-9.730	-0.936	-9.783	-9.709	-0.926	-9.770	-9.655	-1.000	-9.709
1.20	-11.319	-0.809	-11.403	-11.344	-0.775	-11.405	-11.294	-0.855	-11.363
1.40	-12.940	-0.690	-13.036	-13.033	-0.657	-13.137	-12.952	-0.743	-13.075
1.60	-14.517	-0.631	-14.651	-14.729	-0.587	-14.813	-14.609	-0.669	-14.764
1.80	-16.169	-0.583	-16.399	-16.423	-0.544	-16.608	-16.228	-0.639	-16.540
2.00	-17.831	-0.525	-18.244	-18.196	-0.486	-18.523	-17.646	-0.572	-18.224
2.20	-19.579	-0.508	-20.116	-20.082	-0.467	-20.566	-19.158	-0.558	-19.850
2.40	-21.563	-0.494	-22.472	-22.211	-0.459	-23.055	-20.823	-0.552	-22.042
2.60	-23.491	-0.508	-25.390	-24.358	-0.452	-26.033	-22.550	-0.556	-24.690
2.80	-25.655	-0.482	-29.225	-26.841	-0.450	-29.970	-24.322	-0.546	-28.310
3.00	-27.131	-0.506	-31.582	-28.525	-0.455	-32.320	-25.571	-0.567	-32.018
3.20	-28.233	-0.524	-37.545	-29.183	-0.485	-36.357	-26.446	-0.576	-46.959
3.40	-26.167	-0.480	-35.105	-26.499	-0.447	-32.010	-24.801	-0.549	-34.090
3.60	-24.982	-0.487	-29.647	-25.001	-0.452	-28.053	-23.687	-0.545	-28.422
3.80	-23.481	-0.433	-26.075	-23.277	-0.421	-25.022	-22.337	-0.482	-24.848
4.00	-23.068	-0.499	-24.325	-22.887	-0.465	-23.786	-22.247	-0.581	-23.499
4.20	-22.827	-0.545	-23.247	-22.751	-0.500	-22.993	-22.554	-0.606	-23.039
4.40	-23.576	-0.556	-23.157	-23.852	-0.517	-23.322	-23.734	-0.629	-23.589
4.60	-24.319	-0.565	-23.677	-25.195	-0.513	-24.168	-24.969	-0.635	-24.313
4.80	-25.425	-0.616	-24.410	-26.756	-0.556	-25.329	-26.764	-0.679	-25.821
5.00	-28.654	-0.629	-27.373	-31.190	-0.592	-29.149	-31.236	-0.716	-30.464
5.20	-33.904	-0.657	-33.320	-39.824	-0.608	-37.045	-38.072	-0.747	-39.195
5.40	-37.711	-0.713	-31.161	-36.879	-0.636	-30.283	-35.463	-0.794	-32.217
5.60	-30.135	-0.689	-27.491	-28.743	-0.639	-26.470	-27.844	-0.770	-27.194
5.80	-24.684	-0.694	-23.740	-23.996	-0.639	-23.193	-23.153	-0.795	-22.876
6.00	-21.882	-0.722	-20.517	-21.396	-0.625	-20.171	-20.312	-0.812	-19.567

M/A-COM Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.

Visit www.macom.com for additional data sheets and product information.

■ North America: Tel. (800) 366-2266

■ Asia/Pacific: Tel. +81-44-844-8296, Fax +81-44-844-8298

■ Europe: Tel. +44 (1908) 574 200, Fax +44 (1908) 574 300

S-Parameters (continued)

Isolation

Temp:	+25 C	+25 C	+25 C	-35 C	-35 C	-35 C	+85 C	+85 C	+85 C
Freq (GHz)	S11 (dB)	S21 (dB)	S22 (dB)	S11 (dB)	S21 (dB)	S22 (dB)	S11 (dB)	S21 (dB)	S22 (dB)
1.00	-9.618	-30.729	-0.540	-9.637	-30.782	-0.501	-9.560	-30.592	-0.607
1.20	-11.302	-29.739	-0.691	-11.385	-29.824	-0.633	-11.294	-29.626	-0.778
1.40	-13.046	-29.152	-0.826	-13.061	-29.218	-0.763	-13.059	-29.016	-0.962
1.60	-14.280	-28.617	-0.963	-14.398	-28.632	-0.879	-14.332	-28.398	-1.112
1.80	-16.501	-28.177	-1.083	-16.813	-28.224	-0.983	-16.636	-28.091	-1.248
2.00	-18.331	-28.113	-1.187	-18.679	-28.160	-1.075	-18.210	-28.009	-1.382
2.20	-19.492	-28.078	-1.268	-19.859	-28.077	-1.124	-19.021	-27.943	-1.446
2.40	-21.777	-28.065	-1.318	-22.571	-28.074	-1.183	-20.995	-27.930	-1.530
2.60	-22.653	-28.277	-1.386	-23.881	-28.324	-1.235	-21.948	-28.106	-1.605
2.80	-24.000	-28.571	-1.433	-25.063	-28.660	-1.277	-22.980	-28.409	-1.658
3.00	-25.864	-28.827	-1.480	-26.650	-28.916	-1.336	-24.406	-28.573	-1.735
3.20	-29.935	-29.510	-1.521	-31.809	-29.604	-1.348	-27.784	-29.200	-1.768
3.40	-26.921	-29.681	-1.542	-28.337	-29.909	-1.358	-25.601	-29.286	-1.786
3.60	-24.732	-29.860	-1.528	-24.789	-30.078	-1.346	-23.568	-29.467	-1.789
3.80	-23.580	-30.033	-1.481	-22.901	-30.267	-1.318	-22.493	-29.588	-1.737
4.00	-23.581	-30.309	-1.500	-23.240	-30.549	-1.320	-22.471	-29.723	-1.747
4.20	-20.116	-30.200	-1.458	-20.375	-30.524	-1.288	-20.062	-29.649	-1.696
4.40	-20.961	-29.994	-1.426	-21.243	-30.357	-1.270	-21.402	-29.390	-1.659
4.60	-24.644	-29.396	-1.394	-25.127	-29.760	-1.228	-24.744	-28.796	-1.623
4.80	-21.845	-28.768	-1.374	-22.958	-29.052	-1.209	-22.518	-28.144	-1.594
5.00	-27.006	-28.028	-1.387	-29.786	-28.275	-1.239	-29.669	-27.479	-1.589
5.20	-37.311	-27.028	-1.365	-33.629	-27.243	-1.209	-31.803	-26.428	-1.588
5.40	-27.670	-25.778	-1.375	-27.531	-26.003	-1.220	-26.783	-25.435	-1.590
5.60	-29.533	-24.785	-1.415	-26.927	-24.994	-1.288	-26.695	-24.421	-1.607
5.80	-22.688	-23.812	-1.409	-21.365	-23.868	-1.288	-20.791	-23.541	-1.596
6.00	-21.271	-23.038	-1.426	-21.038	-23.137	-1.296	-19.761	-22.750	-1.620

M/A-COM Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.

Visit www.macom.com for additional data sheets and product information.

■ North America: Tel. (800) 366-2266

■ Asia/Pacific: Tel. +81-44-844-8296, Fax +81-44-844-8298

■ Europe: Tel. +44 (1908) 574 200, Fax +44 (1908) 574 300