




THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO CONNECT POSITRONIC. IT IS THE PROPERTY OF CONNECT POSITRONIC. THE DATA ON THIS DRAWING IS TO BE RELIABLE. SINCE THE TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE, THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION. CONNECT POSITRONIC ASSUMES NO LIABILITY FOR ANY RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.

SK10737

DATE	REV	REVISION RECORD	APP	DR	CK
5-21-09	NC	ECO 31054	RCW	BS	COLB
3-19-10	A	ECO 32267	COLB	BE	COLB



NOTES:

1. MATERIALS AND FINISHES:

INSULATOR: GLASS FILLED POLYESTER PER ASTM D5927, UL 94V-0, COLOR: BLUE.

SIGNAL CONTACTS: PRECISION MACHINED HIGH TENSILE COPPER ALLOY WITH BERYLLIUM

COPPER CLIP: 0.000050 [1.27µ] GOLD OVER NICKEL PLATE.

POWER CONTACTS: HIGH CONDUCTIVITY COPPER ALLOY, GOLD FLASH OVER NICKEL PLATE.


SHELLS: STAINLESS STEEL, PASSIVATED.

MOUNTING SPACERS: STEEL, ZINC PLATE WITH CHROMATE SEAL.

2. DETAILED PRODUCT, ELECTRICAL, AND MECHANICAL INFORMATION IS AVAILABLE IN THE LATEST STANDARD DENSITY COMBO-D PRODUCT PUBLICATION.

VISIT CONNECTPOSITRONIC.COM/PRODUCTS/1/STANDARDENSITYCOMBO-D OR CONNECTPOSITRONIC.COM.

3. DIMENSIONS ARE IN INCHES [MILLIMETERS].



POSITRONIC INDUSTRIES INC.
www.connectpositronic.com

DECIMAL TOL.	SCALE	DRAWN BY	APPROVED BY
± 0.015 [0.38]	N.T.S.	B SHELLBUDY	R WILLIAMS

DATE	DRAWING NUMBER	REV.
5-21-09	SK10737	A