
POSISTOR® for Circuit Protection



muRata

Innovator in Electronics

Murata Manufacturing Co., Ltd.

CONTENTS

 $\label{eq:posistor} {\sf POSISTOR}^{\scriptsize \$} \mbox{ and "POSISTOR" in this catalog are the trademarks of Murata Manufacturing Co., Ltd.}$

Part Numbering 2
Basic Characteristics of POSISTOR® 4
Selection Guide 6
Application Matrix 7
1 for Overcurrent Protection Chip Type — 8
Chip Type Specifications and Test Methods
for Overcurrent Protection Narrow Current Band 30V Series — 14
for Overcurrent Protection Narrow Current Band 51/60V Series — 17
for Overcurrent Protection Narrow Current Band 140V Series 22
for Overcurrent Protection 24/30/32V Series 25
6 for Overcurrent Protection 56/80V Series 32
7 for Overcurrent Protection 125/140V Series — 38
8 for Overcurrent Protection 250/265V Series 45
PTGL Series Narrow Current Band Specifications and Test Methods 54
PTGL Series Specifications and Test Methods — 56
9 for Overheat Sensing Chip Type — 57
Chip Type (Ref. Only)
Chip Tight Tolerance Type (Ref. Only) 63
Chip Type Specifications and Test Methods ————————————————————————————————————
Chip Tight Tolerance Type Specifications and Test Methods ————————————————————————————————————
10 for Overheat Sensing Lead Type — 66
● for Temperature Sensor Lead Type Specifications and Test Methods — 70
PRG/PRF Series Package — 75
Lead Type PTGL Series Package — 76

•

O

7

ဂ

Part Numbering

PTC Thermistors (POSISTOR®) for Circuit Protection

(Part Number) PR G 18 BB 470 M B1 RB

Product ID

Product ID	
PR	PTC Thermistors Chip Type

2 Series

Code	Series
G	for Overcurrent Protection

3Dimensions (LXW)

Code	Dimensions (LXW)
18	1.60×0.80mm
21	2.00×1.25mm

4Temperature Characteristics

Code	Temperature Characteristics
ВВ	Curie Point 100°C
ВС	Curie Point 90°C

6 Resistance

Expressed by three figures. The unit is ohm (Ω) . The first and second figures are significant digits, and the third figure expresses the number of zeros which follow the two figures. If there is a decimal point, it is expressed by the capital letter " \mathbf{R} ". In this case, all figures are significant digits.

Ex.)	Code	Resistance
	470	47Ω
	471	470Ω

6Resistance Tolerance

Code	Resistance Tolerance
М	±20%
Q	Special Tolerance

Individual Specifications

Code	Individual Specifications
B1	Structure, others

8 Packaging

Code	Packaging
RA	Plastic Taping (4mm Pitch) (4000pcs.)
RB	Paper Taping (4mm Pitch) (4000pcs.)
RK	Plastic Taping (4mm Pitch) (3000pcs.)

PTC Thermistors (POSISTOR®) for Overheat Sensing Chip Type

(Part Number) PR F 18 BB 471 Q B1 RB

Product ID

Product ID	
PR	PTC Thermistors Chip Type

2 Series

Code	Series
F	for Overheat Sensing

3Dimensions (LXW)

Code	Dimensions (LXW)
18	1.60×0.80mm
21	2.00×1.25mm

4Temperature Characteristics

Code	Temperature Characteristics
AR	Curie Point 120°C
AS	Curie Point 130°C
ВА	Curie Point 110°C
ВВ	Curie Point 100°C
ВС	Curie Point 90°C
BD	Curie Point 80°C
BE	Curie Point 70°C
BF	Curie Point 60°C
BG	Curie Point 50°C

6 Resistance

Expressed by three figures. The unit is ohm (Ω) . The first and second figures are significant digits, and the third figure expresses the number of zeros which follow the two figures. If there is a decimal point, it is expressed by the capital letter " \mathbf{R} ". In this case, all figures are significant digits.

Ex.)	Code	Resistance
	471	470Ω

6 Resistance Tolerance

Code	Resistance Tolerance	Sensing Temp. Tolerance
Q	Special Tolerance	±5°C
R	Special Tolerance	±3°C

Individual Specifications

Code	Individual Specifications
B1	Standard Type

8 Packaging

Code	Packaging
RA	Plastic Taping (4mm Pitch)
RB	Paper Taping (4mm Pitch)



PTC Thermistors (POSISTOR®) for Circuit Protection / for Overheat Sensing Lead Type

(Part Number) PT GL 07 AR 220 M 3P51 A0

Product ID

Product ID	
PT	PTC Thermistors

2Series

Code	Series
FL	for Overheat Sensing Lead Type
FM	for Overheat Sensing with Lug-terminal
GL	for Circuit Protection Lead Type

3Dimensions

Code	Dimensions
04	Nominal Body Diameter 4mm Series
05	Nominal Body Diameter 5mm Series
07	Nominal Body Diameter 7mm Series
09	Nominal Body Diameter 9mm Series
10	Nominal Body Diameter 10mm Series
12	Nominal Body Diameter 12mm Series
13	Nominal Body Diameter 13mm Series
14	Nominal Body Diameter 14mm Series
16	Nominal Body Diameter 16mm Series
18	Nominal Body Diameter 18mm Series

4Temperature Characteristics

Code	Temperature Characteristics
AS	Curie Point 130°C
AR	Curie Point 120°C
ВА	Curie Point 110°C
ВВ	Curie Point 100°C
ВС	Curie Point 90°C
BD	Curie Point 80°C
BE	Curie Point 70°C
BF	Curie Point 60°C
BG	Curie Point 50°C
ВН	Curie Point 40°C

6 Resistance

Expressed by three figures. The unit is ohm (Ω) . The first and second figures are significant digits, and the third figure expresses the number of zeros which follow the two figures. If there is a decimal point, it is expressed by the capital letter " \mathbf{R} ". In this case, all figures are significant digits.

x.)	Code	Resistance
	R22	0.22Ω
	2R2	2.2Ω
	220	22Ω

6Resistance Tolerance

Code	Resistance Tolerance
Н	±25%
K	±10%
М	±20%
N	±30%
Q	Special Tolerance

Individual Specifications

Code	Individual Specifications
3P51	Lead Type, others

Packaging

Code	Packaging
A0	Ammo Pack
В0	Bulk




Basic Characteristics of POSISTOR®


■Basic Characteristics

POSISTOR® has three main characteristics.


1. Resistance-Temperature Characteristic
Although there is a negligible difference between the normal and "Curie-point" temperature, POSISTOR® shows almost constant resistance-temperature characteristics. Yet they have resistance-temperature characteristics that cause resistance to sharply increase when the temperature exceeds the Curie-point.



2. Current-Voltage Characteristic (Static Characteristic)
This shows the relation between applied voltage when voltage applied to POSISTOR® causes balancing of inner heating and outer thermal dissipation and stabilized current. This has both a maximum point of current and constant output power.



3. Current-Time Characteristic (Dynamic Characteristic)
This shows the relation between current and time before inner heating and outer thermal dissipation arrive at equilibrium state. This features having large initial current and abruptly continuous attenuating portion.



Basic Characteristics of POSISTOR®

Technical Terms

1. Protective Threshold Current

The maximum current value is called the "Protective Threshold Current" for Voltage vs. Current characteristics (static).

When smaller than the protective threshold current flows in POSISTOR®, it reaches its stability (as shown in figure of right) at the intersection (A) of the load curve (a) and voltage-current characteristics of POSISTOR®(c). And POSISTOR® works as normal fixed resistor.


However, when larger than protective threshold current flows, it stabilizes at the intersection (B) with the load curve (b).

[Load Curve of Circuit and Voltage-current Characteristics of POSISTOR®] a Load curve in normal state (normal current) b Load curve in abnormal state (abnormal current) c Voltage-current characteristics of POSISTOR® b Voltage (log) E Voltage (log)

2. Protective Threshold Current Range


Protective threshold current varies depending on the ambient temperature, resistance value, temperature characteristics and shape (Figure of right) The maximum value of trip current and the minimum value of the non-operating current are in the range of ambient temperature -10 to +60°C.

That is, when a current is smaller than the non-operating current, POSISTOR® works only as a fixed resistor. When larger than the trip current flows, however, POSISTOR® protects the circuit from overload.




3. Operating Time

A period starting from the voltage input to the moment current itself sharply attenuates is called "Operating Time". Conventionally, operation time (to) is determined to be the period until inrush current (lo) decreases to a level one half the original inrush current (lo/2).



Selection Guide

Please confirm the parameters according to the following questions. The best selection is the product that is satisfied with three parameters.



 $\label{eq:ptgl12AR100M6C01B0} \textbf{ptgl12AR100M6C01B0} \ \text{is the best selection in this case}.$



Application Matrix

Series	Over Currer	t Protection	Overheat Sensing				
Application	PTGL Series	PRG Series	PTFL Series PTFM Series	PRF Series			
Color TV	•	•					
CRT Display	•	•					
VCR	•	•	•	•			
Audio	•	•	•	•			
Speaker	•						
Refrigerator	•	•	•	•			
Vacuum Cleaner	•	•					
Air Conditioner	•	•		•			
FAX	•	•	•	•			
Personal Computer	•	•		•			
USB HUB	•						
PDA		•		•			
Lighting Equipment	•	•	•	•			
STB	•	•	•	•			
DSL	•	•	•	•			
Exchanger	•	•					
Transceiver	•	•	•	•			
Security System	•	•	•	•			
Vending Machine	•	•	•	•			
Automobile	•	•	•	•			
Car Audio	•	•	•	•			
Car Navigation	•						
Small DC Motor	•	•	•	•			
Fan Motor	•	•	•	•			
Battery Pack		•		•			
Power Supply	•	•	•	•			
AC Adaptor	•		•	•			
Small Transformer	•	•	•	•			



POSISTOR® for Circuit Protection



for Overcurrent Protection Chip Type

Overcurrent Protection device with resettable function suitable for current limiting resistor.


This product is chip type PTC thermistor for overcurrent protection which is suitable for the following

- •Countermeasure for short circuit testing
- •Current limiting resistor

■ Features

- Rapid operation to protects the circuit in an overcurrent condition abnormality such as a short circuit
 - By removing the overcurrent condition, these products automatically return to the initial condition and can be used repeatedly
- 2. Suitable for countermeasure to short circuit test in safety standard
- Stable resistance after operation due to ceramic PTC
- 4. Similar size (0603 size) is possible due to the large capacity for electric power.
- Possible to use these products as current limiting resistors with overcurrent protection functions
- 6. SMD type is helpful for miniaturizing circuits because of its small size and light weight
- 7. Lead is not contained in the terminations






Part Number	Max. Voltage (V)	Non-operating Current (at +60°C)(mA)	Trip Current (at -10°C) (mA)	Max. Current (mA)	Resistance (at 25°C) (ohm)	Curie Point (°C)
PRG18BB471MB1RB	24	7	25	60	470 ±20%	100 (BB)
PRG18BB221MB1RB	G18BB221MB1RB 24		35	130	220 ±20%	100 (BB)
PRG18BB101MB1RB	G18BB101MB1RB 24		55	300	100 ±20%	100 (BB)
PRG18BB470MB1RB	24	20	75	630	47 ±20%	100 (BB)
PRG18BB330MB1RB	24	25	85	900	33 ±20%	100 (BB)
PRG21BB220MB1RK	20	30	110	1100	22 ±20%	100 (BB)
PRG21BB150MB1RK	RG21BB150MB1RK 20		140	1600	15 ±20%	100 (BB)
PRG21BC0R2MM1RA	6	500	2000	10000	0.2 ±20%	90 (BC)




■ Standard Land Pattern Dimensions





(in mm)


Part Number	Soldering	Dimensions (mm)							
	Methods	Chip (LXW)	a	b	С				
PRG18	Reflow Soldering	1.6×0.8	0.6-0.8	0.6-0.7	0.6-0.8				
PRG21	Reflow Soldering	2.0×1.25	1.0-1.2	0.5-0.7	1.0-1.2				


■ Protective Threshold Current Range
















Continued from the preceding page.


■ Protective Threshold Current Range







■ Operating Time (Typical Curve)











PRG18BB101MB1RB



PRG18BB470MB1RB




Continued on the following page.




■ Operating Time (Typical Curve)


PRG18BB330MB1RB




PRG21BB220MB1RK



PRG21BB150MB1RK



PRG21BC0R2MM1RA



Chip Type Specifications and Test Methods

■ 24/20V Series

No.	Item	Rating Value	Method of Examination					
1	Operating Temp.	-10 to 60°C	Temperature range with maximum voltage applied to PTC.					
2	Resistance Value (at 25°C)	The resistance value should be within the specified tolerance.	After applying maximum operating voltage for 3 mins. and leaving for 2 hrs. in 25°C, measured by applying voltage of less than 1.5Vdc (by a direct current of less than 10mA).					
3	Withstanding Voltage	Without damage	We apply 120% of the maximum operating voltage to PTC by rising gradually for 180±5 secs. at 25°C. (A protective resistor is to be connected in series, and the inrush current through PTC must be limited below maximum rated value.)					
4	Adhesive Strength	There is no exfoliation sign of electrode.	EIAJ ET-7403 term 9 Soldered PTC to PCB and add the force of 5.0N in the direction as shown below. PTC Glass Epoxy PCB F=5.0N					
5	Vibrationability	Normal appearance Resistance change: not to exceed ±20% (*)	JIS C 5102 term 8.2 Soldered PTC to PCB Vibration: A 10-55-10Hz (1 min.) Width: 1.5mm Vibrate for 2 hrs. in each of 3 mutually perpendicular planes for a total of 6 hrs.					
6	Solderability	Min. 75% electrode is covered with new solder. Resistance change: not to exceed ±20% (*)	JIS C 5102 term 8.4 Solder: Sn 63%/Pb 37% (or 60/40%) Solder temp: 230±5°C Soaking time: 3±0.5 s. Soaking position: Until a whole electrode is soaked					
7	Solder-heatability	Normal appearance Resistance change: not to exceed ±20% (*)	Solder: Sn 63%/Pb 37% (or 60/40%) Flux: Solder paste containing less than 0.2wt% of chlorine. Preheating: 150±5°C 3mins. Peak temp.: 260±5°C 10±5 s. (reflow) PCB: Glass Epoxy PCB (JIS C 6484)					
8	Temperature Cycling Normal appearance Resistance change: not to exceed ±20% (*)		JIS C 5102 term 9.3 Times: 5 cycles Step Temp. (°C) Time (min.) 1 -20 +0, -3 30 2 Room temp. 10-15 3 +85 +3, -0 30 4 Room temp. 10-15					
9	Humidity Test	Normal appearance Resistance change: not to exceed ±20% (*)	JIS C 5102 term 9.5 40±2°C, 90-95%RH leave for 500±4 hrs.					
10	Resistance change: not to exceed ±20% (*) High Temperature Normal appearance Resistance change: not to exceed ±20% (*) JIS C 5102 term 9.10							

^(*) Measure resistance after the test by applying voltage of less than 1.5Vdc by a direct current of less than 10mA after product is left at 25±2°C for 2 hours.

Above mentioned soldering in "4. Adhesive Strength" and "5. Vibrationability" is done under the following conditions at our site.

- •Glass-Epoxy PC board
- •Recommendable land dimension
- •Recommendable solder paste
- •Recommendable solder profile

Above conditions are mentioned in Notice.



Chip Type Specifications and Test Methods

■ 6V Series

No.	Item	Rating Value	Method of Examination				
1	Operating Temp.	-10 to 60°C	Temperature range with maximum voltage applied to PTC.				
2	Resistance Value (at 25°C)	The resistance value should be within the specified tolerance.	After leaving for 24 hrs. or more in 25°C, it measures by 4 wire measuring methods using the direct-current terminal current of 10mA or less (0.1 or less Vdcs).				
3	Withstanding Voltage	Without damage	We apply 120% of the maxi. operating voltage to PTC by rising gradually for 180±5 secs. at 25°C. (A protective resistor is to be connected in series, and the inrush current through PTC must be limited below max. rated value.)				
			EIAJ ET-7403 term 9 Soldered PTC to PCB and add the force of 5.0N in the direction as shown below.				
4	Adhesive Strength	There is no exfoliation sign of electrode.	PTC F Glass Epoxy PCB F=5.0N				
5	Vibrationability	Normal appearance Resistance change: not exceed ±20% (*)	JIS C 5102 term 8.2 Soldered PTC to PCB Vibration: A 10-55-10Hz (1 min.) Width: 1.5mm Vibrate for 2 hrs. in each of 3 mutually perpendicular plane for a total of 6 hrs.				
6	Solderability	Min. 75% electrode is covered with new solder. Resistance change: not exceed ±20% (*)	JIS C 5102 term 8.4 Solder: Sn 63%/Pb 37% (or 60/40%) Solder temp: 230±5°C Soaking time: 3±0.5 secs. Soaking position: Until a whole electrode is soaked.				
7	Solder-heatability	Normal appearance Resistance change: not exceed ±20% (*)	Solder: Sn 63%/Pb 37% (or 60/40%) Flax: Solder paste containing less than 0.2wt% of chlorine. Preheating: 150±5°C 3mins. Peak temp.: 260±5°C 10±5 secs. (reflow) PCB: Glass Epoxy PCB (JIS C 6484)				
8	High Temperature Test		60±3°C leaves for 1000±10 hrs.				
9	Low Temperature Test		-10±3°C leaves for 1000±10 hrs.				
10	Humidity Test		60±2°C, 90-95%RH leaves for 500±4 hrs.				
		Normal appearance	JIS C 5102 term 9.3 Times: 5 cycles Step Temp. (°C) Time (min.)				
11	Temperature Cycling	Resistance change: not exceed ±20% (*)	1 -20 +0, -3 30				
			2 Room temp. 10-15				
			3 +85 +3, -0 30 4 Room temp. 10-15				
12	High Temperature Load Test		60±3°C (in air), PTC is applied max. operating voltage for 1.5 hrs. on and 0.5 hrs. off. This cycle is repeated for 500±4 hrs.				

^(*) The resistance measurement after the test.

After leaving for 24 hours, or more in 25±2°C, it measures by 4 wire measuring methods using the direct-current terminal current of 10mA or less (0.1 or less Vdcs).

Above mentioned soldering in "4. Adhesive Strength" and "5. Vibrationability" is done under the following conditions at our site.

- •Glass-Epoxy PC board
- •Recommendable land dimension
- •Recommendable solder paste
- •Recommendable solder profile

Above conditions are mentioned in Notice.



POSISTOR® for Circuit Protection




for Overcurrent Protection Narrow Current Band 30V Series


This product is leaded type PTC thermistor for overcurrent protection which is suitable for the current limiting resistor.

■ Features

- 1. Small fluctuation in the circuit due to resistance tolerance +/-10%
- 2. Narrow current range (less than twice) between operating and non-operating current at -10 to 60 degree C.
- 3. Quick operating time due to small size compared with conventional products.
- 4. Best suited to meet the requirements for power supply and motor protector. Error-free operations are assured by rush current.
- 5. Circuit is protected until current is turned off.
- 6. Restores the original low resistance value automatically once the overload is removed.
- 7. Non-contact design leads to long life and no noise. Durable and strong against mechanical vibration and shock because it is a solid element.
- 8. Lead (Pb) is not contained in the terminations.









Part Number	Max. Voltage (V)	Non-operating Current (at +60°C)(mA)	Trip Current (at -10°C) (mA)	Max. Current (A)	Resistance (at 25°C) (ohm)	Curie Point (°C)	Body Diameter (D) (mm)	Thickness (T) (mm)	Height (H) (mm)	Lead Space (F) (mm)	Lead Diameter (phi d)(mm)
PTGL04AS100K2N51B0	30	122	240	1.5	10 ±10%	130 (AS)	4.5	3.5	9.5	5.0	0.5
PTGL04AS100K2B51B0	30	167	330	2.0	10 ±10%	130 (AS)	4.5	3.5	9.5	5.0	0.6
PTGL05AS3R9K2B51B0	30	269	530	3.5	3.9 ±10%	130 (AS)	5.5	3.5	10.5	5.0	0.6
PTGL07AS2R7K2B51B0	30	336	663	4.5	2.7 ±10%	130 (AS)	7.3	3.5	12.3	5.0	0.6
PTGL07AS1R8K2B51B0	30	420	829	5.0	1.8 ±10%	130 (AS)	7.3	3.5	12.3	5.0	0.6
PTGL09AS1R2K2B51B0	30	556	1097	6.0	1.2 ±10%	130 (AS)	9.3	3.5	14.3	5.0	0.6
PTGL12AS0R8K2B51B0	30	685	1352	7.0	0.8 ±10%	130 (AS)	11.5	3.5	16.5	5.0	0.6

Maximum Current shows typical capacities of the transformer which can be used.

■ Protective Threshold Current Range



PTGL04AS100K2B51B0



Continued on the following page.






³⁰V Series are recognized by UL


Taping type is also available.

■ Protective Threshold Current Range


PTGL05AS3R9K2B51B0




PTGL07AS2R7K2B51B0




PTGL07AS1R8K2B51B0



PTGL09AS1R2K2B51B0




PTGL12AS0R8K2B51B0




■ Operating Time (Typical Curve)

PTGL04AS100K2N51B0




PTGL04AS100K2B51B0




■ Operating Time (Typical Curve)


PTGL05AS3R9K2B51B0




PTGL07AS2R7K2B51B0




PTGL07AS1R8K2B51B0



PTGL09AS1R2K2B51B0



PTGL12AS0R8K2B51B0



POSISTOR® for Circuit Protection




for Overcurrent Protection Narrow Current Band 51/60V Series


This product is leaded type PTC thermistor for overcurrent protection which is suitable for the current limiting resistor.

■ Features

- 1. Small fluctuation in the circuit due to resistance tolerance +/-10%
- Narrow current range (less than twice) between operating and non-operating current at -10 to 60 degree C.
- 3. Quick operating time due to small size compared with conventional products.
- Best suited to meet the requirements for power supply and motor protector. Error-free operations are assured by rush current.
- 5. Circuit is protected until current is turned off.
- 6. Restores the original low resistance value automatically once the overload is removed.
- Non-contact design leads to long life and no noise.
 Durable and strong against mechanical vibration and shock because it is a solid element.
- 8. Lead (Pb) is not contained in the terminations.








Part Number	Max. Voltage (V)	Non-operating Current (at +60°C)(mA)	Trip Current (at -10°C) (mA)	Max. Current (A)	Resistance (at 25°C) (ohm)	Curie Point (°C)	Temperature Range (°C)	Body Diameter (D) (mm)	Thickness (T) (mm)	Height (H) (mm)	Lead Space (F) (mm)	Lead Diameter (phi d)(mm)
PTGL04AS100K3B51B0	51	168	332	1.0	10 ±10%	130 (AS)	-30 to 85	4.5	4.5	9.5	5.0	0.6
PTGL05AS6R8K3B51B0	51	197	388	1.5	6.8 ±10%	130 (AS)	-30 to 85	5.5	5.5	10.5	5.0	0.6
PTGL07AS3R3K3B51B0	51	307	606	3.0	3.3 ±10%	130 (AS)	-30 to 85	7.3	7.3	12.3	5.0	0.6
PTGL09AS2R2K3B51B0	51	412	814	4.0	2.2 ±10%	130 (AS)	-30 to 85	9.3	9.3	14.3	5.0	0.6
PTGL12AS1R2K3B51B0	51	592	1168	5.0	1.2 ±10%	130 (AS)	-30 to 85	11.5	11.5	16.5	5.0	0.6
PTGL04AS220K4N51B0	60	88	175	1.0	22 ±10%	130 (AS)	-30 to 85	4.5	4.5	9.5	5.0	0.5
PTGL04AS220K4B51B0	60	115	226	1.0	22 ±10%	130 (AS)	-30 to 85	4.5	4.5	9.5	5.0	0.6
PTGL05AS100K4B51B0	60	170	335	1.5	10 ±10%	130 (AS)	-30 to 85	5.5	5.5	10.5	5.0	0.6
PTGL07AS5R6K4N51B0	60	186	368	2.2	5.6 ±10%	130 (AS)	-30 to 85	7.3	7.3	12.3	5.0	0.5
PTGL07AS5R6K4B51B0	60	229	452	3.0	5.6 ±10%	130 (AS)	-30 to 85	7.3	7.3	12.3	5.0	0.6
PTGL09AS3R3K4B51B0	60	333	656	4.0	3.3 ±10%	130 (AS)	-30 to 85	9.3	9.3	14.3	5.0	0.6
PTGL12AS2R2K4B51B0	60	439	867	5.0	2.2 ±10%	130 (AS)	-30 to 85	11.5	11.5	16.5	5.0	0.6

Maximum Current shows typical capacities of the transformer which can be used.


51/60V Series are recognized by UL.

Taping type is also available.


■ Protective Threshold Current Range (51V Series)




PTGL05AS6R8K3B51B0




PTGL07AS3R3K3B51B0



PTGL09AS2R2K3B51B0




PTGL12AS1R2K3B51B0





■ Protective Threshold Current Range (60V Series)

PTGL04AS220K4N51B0




PTGL04AS220K4B51B0







■ Protective Threshold Current Range (60V Series)



PTGL07AS5R6K4N51B0 Trip current Trip current Non operating current


20 40 Ambient Temperature (°C)








20 40 Ambient Temperature (°C)




■ Operating Time 51V Series (Typical Curve)

PTGL04AS100K3B51B0




PTGL05AS6R8K3B51B0




■ Operating Time 51V Series (Typical Curve)


PTGL07AS3R3K3B51B0




PTGL09AS2R2K3B51B0




PTGL12AS1R2K3B51B0




■ Operating Time 60V Series (Typical Curve) PTGL04AS220K4N51B0




PTGL04AS220K4B51B0



PTGL05AS100K4B51B0



PTGL07AS5R6K4N51B0






■ Operating Time 60V Series (Typical Curve)


PTGL07AS5R6K4B51B0

Note Please read rating and \(\tilde{\text{DCAUTION}}\) (for storage, operating, rating, soldering, mounting and handling) in this PDF catalog to prevent smoking and/or burning, etc.


This catalog has only typical specifications. Therefore, you are requested to approve our product specifications or to transact the approval sheet for product specifications before ordering



PTGL09AS3R3K4B51B0



PTGL12AS2R2K4B51B0



POSISTOR® for Circuit Protection




for Overcurrent Protection Narrow Current Band 140V Series

This product is leaded type PTC thermistor for overcurrent protection which is suitable for the current limiting resistor.

■ Features


- 1. Small fluctuation in the circuit due to resistance tolerance +/-10%
- 2. Narrow current range (less than twice) between operating and non-operating current at -10 to 60 degree C.
- 3. Quick operating time due to small size compared with conventional products.
- 4. Best suited to meet the requirements for power supply and motor protector. Error-free operations are assured by rush current.
- 5. Circuit is protected until current is turned off.
- 6. Restores the original low resistance value automatically once the overload is removed.
- 7. Non-contact design leads to long life and no noise. Durable and strong against mechanical vibration and shock because it is a solid element.
- 8. Lead (Pb) is not contained in the terminations.



Part Number	Max. Voltage (V)	Non-operating Current (at +60°C)(mA)	Trip Current (at -10°C) (mA)	Max. Current (A)	Resistance (at 25°C) (ohm)	Curie Point (°C)	Temperature Range (°C)	Body Diameter (D) (mm)	Thickness (T) (mm)	Height (H) (mm)	Lead Space (F) (mm)	Lead Diameter (phi d)(mm)
PTGL04AS560K6B51B0	140	74	147	0.5	56 ±10%	130 (AS)	-30 to 85	5.5	5.5	10.5	5.0	0.6
PTGL05AS270K6B51B0	140	106	209	1.0	27 ±10%	130 (AS)	-30 to 85	5.5	5.5	10.5	5.0	0.6
PTGL07AS150K6B51B0	140	148	292	1.5	15 ±10%	130 (AS)	-30 to 85	7.3	7.3	12.3	5.0	0.6
PTGL09AS120K6B51B0	140	192	380	2.0	12 ±10%	130 (AS)	-30 to 85	9.3	9.3	14.3	5.0	0.6
PTGL09AS7R6K6B51B0	140	227	447	2.2	7.6 ±10%	130 (AS)	-30 to 85	9.3	9.3	14.3	5.0	0.6
PTGL12AS4R7K6B51B0	140	310	613	3.5	4.7 ±10%	130 (AS)	-30 to 85	11.5	11.5	16.5	5.0	0.6

Maximum Current shows typical capacities of the transformer which can be used.


■ Protective Threshold Current Range



Ambient Temperature (°C)

PTGL04AS560K6B51B0

PTGL05AS270K6B51B0



Continued on the following page.






¹⁴⁰V Series are recognized by UL.

Taping type is also available.


Continued from the preceding page.

■ Protective Threshold Current Range


PTGL07AS150K6B51B0




PTGL09AS120K6B51B0



PTGL09AS7R6K6B51B0




PTGL12AS4R7K6B51B0




■ Operating Time (Typical Curve)


PTGL04AS560K6B51B0




PTGL05AS270K6B51B0



PTGL07AS150K6B51B0




PTGL09AS120K6B51B0




Continued from the preceding page.

■ Operating Time (Typical Curve)

PTGL09AS7R6K6B51B0



PTGL12AS4R7K6B51B0



POSISTOR® for Circuit Protection




for Overcurrent Protection 24/30/32V Series

Safety resistor "POSISTOR" is most suited to meet the requirements of the safety standard short-circuit tests such as IEC, VDE, BS, UL, CSA etc. all over the world.

■ Features

- Best suited to meet the requirements of the shortcircuit test. Quick response compared with current fuse and resistor and error-free operation are assured.
- 2. Small size does not need a large space. Capable of being mounted to any place because replacement is not required.
- 3. Actuates by excessive current during the short-circuit test to restrain abnormal heat generation in other circuit components and printed boards. This state will be maintained until the abnormal state is removed or power is turned off to reset the "POSISTOR" to the original state. Surface temperature of "POSISTOR" is kept low, below a certain value, during the actuation.
- Non-contact design leads to long life and no noise.
 Durable and strong against mechanical vibration and shock because it is a solid element.



Part Number	Max. Voltage (V)	Non-operating Current (at +60°C)(mA)	Trip Current (at -10°C) (mA)	Max. Current (A)	Resistance (at 25°C) (ohm)	Curie Point (°C)	Body Diameter (D) (mm)	Thickness (T) (mm)	Lead Space (F) (mm)	Lead Diameter (phi d)(mm)
PTGL07BD100N2B51B0	24	80	320	2.0	10 ±30%	80 (BD)	7.4	4.0	5.0	0.6
PTGL07BD6R8N2B51B0	24	90	370	2.0	6.8 ±30%	80 (BD)	7.4	4.0	5.0	0.6
PTGL09BD4R7N2B51B0	24	120	500	2.0	4.7 ±30%	80 (BD)	9.5	4.0	5.0	0.6
PTGL09BD3R3N2B51B0	24	140	580	2.0	3.3 ±30%	80 (BD)	9.5	4.0	5.0	0.6
PTGL09BD2R2N2B51B0	24	180	710	2.0	2.2 ±30%	80 (BD)	9.5	4.0	5.0	0.6
PTGL04AR130H2B51B0	30	145	400	0.7	13 ±25%	120 (AR)	5.5	4.0	5.0	0.6
PTGL07AR4R6H2B51B0	30	250	700	2.0	4.6 ±25%	120 (AR)	7.4	4.0	5.0	0.6
PTGL09AR1R8H2B51B0	30	410	1120	3.0	1.8 ±25%	120 (AR)	9.5	4.0	5.0	0.6
PTGL12AR1R2H2B51B0	30	520	1420	4.3	1.2 ±25%	120 (AR)	12.0	4.0	5.0	0.6
PTGL13AR0R8H2B71B0	30	680	1900	5.5	0.8 ±25%	120 (AR)	13.5	4.0	7.5	0.6
PTGL07BD470N3B51B0	32	30	140	1.5	47 ±30%	80 (BD)	7.4	4.0	5.0	0.6
PTGL07BD330N3B51B0	32	40	170	1.5	33 ±30%	80 (BD)	7.4	4.0	5.0	0.6
PTGL07BD220N3B51B0	32	45	200	1.5	22 ±30%	80 (BD)	7.4	4.0	5.0	0.6
PTGL07BD150N3B51B0	32	60	240	1.5	15 ±30%	80 (BD)	7.4	4.0	5.0	0.6


Maximum Current shows typical capacities of the transformer which can be used.


24/30/32V Series are recognized by UL


PTGL_51B0 series are available in taping type.





■ Protective Threshold Current Range (24V Series)














■ Protective Threshold Current Range (30V Series)










■ Protective Threshold Current Range (30V Series)










■ Protective Threshold Current Range (32V Series)











■ Operating Time 24V Series (Typical Curve)


PTGL07BD100N2B51B0




PTGL07BD6R8N2B51B0




PTGL09BD4R7N2B51B0




PTGL09BD3R3N2B51B0




PTGL09BD2R2N2B51B0




■ Operating Time 30V Series (Typical Curve)







PTGL07AR4R6H2B51B0




PTGL09AR1R8H2B51B0



PTGL12AR1R2H2B51B0




PTGL13AR0R8H2B71B0




■ Operating Time 32V Series (Typical Curve)


PTGL07BD470N3B51B0




PTGL07BD330N3B51B0



PTGL07BD220N3B51B0




PTGL07BD150N3B51B0




■ Application Circuit 24/32V Series

(1) Short-Circuit Test of Transistor



(2) Short-Circuit Test of Diode




Continued on the following page.




■ Application Circuit 24/32V Series


(3) Short-Circuit Test of IC




(4) Short-Circuit Test of Electrolytic Capacitor




(5) Lock Test of Motor




■ Application Circuit 30V Series




(2) Transformer Protection Circuit 1)



(3) Transformer Protection Circuit 2)



(4) Fluorescent Lamp Protection Circuit





POSISTOR® for Circuit Protection



for Overcurrent Protection 56/80V Series

"POSISTOR" is a circuit protector whose resistance value in normal operation is very low and in abnormal situations like overcurrent or overheating, will be increased to restrain overcurrent. "POSISTOR" can be used for overcurrent protection against current fuse or temperature fuse, due to its ability to return to its initial condition when overcurrent is removed.





(in mm)

■ Features

- Best suited to meet the requirements for power supply and motor protector. Error-free operations are assured by rush current.
- 2. Circuit is protected until current is turned off.
- 3. Restores the original low resistance value automatically once the overload is removed.
- 4. Non-contact design leads to long life and no noise. Durable and strong against mechanical vibration and shock because it is a solid element.

■ Applications

- DC cooling fan motors in office equipment, e.g., computers, facsimiles, floppy disk drives and power units.
- 2. DC drive motors in VTRs and cassette tape recorders. Power transformers (at secondary winding)


Part Number	Max. Voltage (V)	Non-operating Current (at +60°C)(mA)	Trip Current (at -10°C) (mA)	Max. Current (A)	Resistance (at 25°C) (ohm)	Curie Point (°C)	Body Diameter (D) (mm)	Thickness (T) (mm)	Lead Space (F) (mm)	Lead Diameter (phi d)(mm)
PTGL07AR220M3P51B0	56	90	240	1.0	22 ±20%	120 (AR)	7.4	4.0	5.0	0.6
PTGL07AR8R2M3P51B0	56	130	350	1.0	8.2 ±20%	120 (AR)	7.4	4.0	5.0	0.6
PTGL09AR150M3B51B0	56	150	400	1.2	15 ±20%	120 (AR)	9.5	4.0	5.0	0.6
PTGL10AR3R9M3P51B0	56	210	550	2.0	3.9 ±20%	120 (AR)	10.5	4.0	5.0	0.6
PTGL09AR4R7M3B51B0	56	270	700	2.0	4.7 ±20%	120 (AR)	9.5	4.0	5.0	0.6
PTGL10AR3R9M3B51B0	56	300	800	2.0	3.9 ±20%	120 (AR)	10.5	4.0	5.0	0.6
PTGL14AR3R3M3B71B0	56	380	980	2.5	3.3 ±20%	120 (AR)	14.5	4.0	7.5	0.6
PTGL05AR550H4P51B0	80	50	135	0.7	55 ±25%	120 (AR)	5.5	4.5	5.0	0.6
PTGL07AR250H4B51B0	80	110	300	1.0	25 ±25%	120 (AR)	7.4	4.5	5.0	0.6
PTGL09AR9R4H4B51B0	80	190	530	3.0	9.4 ±25%	120 (AR)	9.5	4.5	5.0	0.6
PTGL12AR5R6H4B71B0	80	270	760	4.3	5.6 ±25%	120 (AR)	12.0	4.5	7.5	0.6
PTGL13AR3R7H4B71B0	80	310	860	5.5	3.7 ±25%	120 (AR)	13.5	4.5	7.5	0.6


 $\label{thm:maximum} \mbox{ Maximum Current shows typical capacities of the transformer which can be used.}$


Please contact us for UL recognized products.


PTGL_51B0 series are available in taping type.


■ Protective Threshold Current Range (56V Series)






















■ Protective Threshold Current Range (80V Series)













■ Operating Time 56V Series (Typical Curve)


PTGL07AR220M3P51B0




PTGL07AR8R2M3P51B0




PTGL09AR150M3B51B0




PTGL10AR3R9M3P51B0



PTGL09AR4R7M3B51B0




PTGL10AR3R9M3B51B0






■ Operating Time 56V Series (Typical Curve)

PTGL14AR3R3M3B71B0




■ Operating Time 80V Series (Typical Curve)


PTGL05AR550H4P51B0




PTGL07AR250H4B51B0



PTGL09AR9R4H4B51B0




PTGL12AR5R6H4B71B0




■ Operating Time 80V Series (Typical Curve)

PTGL13AR3R7H4B71B0




■ Application Circuit 56V Series


DC Motor Protection Circuit



■ Application Circuit 80V Series



(2) Transistor Protection Circuit



POSISTOR® for Circuit Protection



for Overcurrent Protection 125/140V Series

"POSISTOR" is a circuit protector whose resistance value in normal operation is very low and in abnormal situations like overcurrent or overheating, will be increased to restrain overcurrent. "POSISTOR" can be used for overcurrent protection against current fuse or temperature fuse, due to its ability to return to its initial condition when overcurrent is removed.

■ Features

- Best suited to meet the requirements for power supply and motor protector. Error-free operations are assured by rush current.
- 2. Circuit is protected until current is turned off.
- Restores the original low resistance value automatically once the overload is removed.
- 4. Non-contact design leads to long life and no noise. Durable and strong against mechanical vibration and shock because it is a solid element.


■ Applications

Circuit Protection:

- 1. Transformers
- 2. Transistors
- 3. Fluorescent Lamps




125V Series





140V Series




Part Number	Max. Voltage (V)	Non-operating Current (at +60°C)(mA)	Trip Current (at -10°C) (mA)	Max. Current (A)	Resistance (at 25°C) (ohm)	Curie Point (°C)	Body Diameter (D) (mm)	Thickness (T) (mm)	Lead Space (F) (mm)	Lead Diameter (phi d)(mm)
PTGL05AR181M7P52B0	125	30	75	0.3	180 ±20%	120 (AR)	6.0	5.0	5.0	0.6
PTGL07AR750M7B52B0	125	65	165	0.3	75 ±20%	120 (AR)	8.0	6.0	5.0	0.6
PTGL09AR470M6B52B0	125	90	230	0.5	47 ±20%	120 (AR)	10.0	5.5	5.0	0.6
PTGL09AR220M6B52B0	125	135	340	0.8	22 ±20%	120 (AR)	10.0	5.5	5.0	0.6
PTGL12AR150M6B72B0	125	175	440	1.0	15 ±20%	120 (AR)	12.5	5.5	7.5	0.6
PTGL14AR100M6B72B0	125	220	550	1.2	10 ±20%	120 (AR)	15.0	5.5	7.5	0.6
PTGL18AR6R8M6B72B0	125	300	750	1.4	6.8 ±20%	120 (AR)	18.5	5.5	7.5	0.6
PTGL18AR4R7M6B72B0	125	360	900	1.7	4.7 ±20%	120 (AR)	18.5	5.5	7.5	0.6
PTGL18AR3R3M6B72B0	125	420	1050	2.0	3.3 ±20%	120 (AR)	18.5	5.5	7.5	0.6
PTGL07AR330M6A51B0	140	100	230	0.5	33 ±20%	120 (AR)	7.4	6.0	5.0	0.5
PTGL09AR220M6C61B0	140	140	330	1.0	22 ±20%	120 (AR)	9.6	6.0	6.5	0.65
PTGL10AR150M6C61B0	140	170	400	1.0	15 ±20%	120 (AR)	11.6	6.0	6.5	0.65
PTGL12AR100M6C01B0	140	220	510	1.0	10 ±20%	120 (AR)	13.0	6.0	10.0	0.65
PTGL13AR6R8M6C01B0	140	290	670	1.0	6.8 ±20%	120 (AR)	14.0	6.0	10.0	0.65
PTGL16AR5R6M6C01B0	140	340	780	2.0	5.6 ±20%	120 (AR)	17.0	6.0	10.0	0.65


Maximum Current shows typical capacities of the transformer which can be used.


Please contact us for UL recognized products.


PTGL_52B0 series are available in taping type.


■ Protective Threshold Current Range (125V Series)

























Continued from the preceding page.


■ Protective Threshold Current Range (125V Series)





■ Protective Threshold Current Range (140V Series)


















■ Operating Time 125V Series (Typical Curve)


PTGL05AR181M7P52B0




PTGL07AR750M7B52B0




PTGL09AR470M6B52B0




PTGL09AR220M6B52B0



PTGL12AR150M6B72B0




PTGL14AR100M6B72B0




■ Operating Time 125V Series (Typical Curve)


PTGL18AR6R8M6B72B0



PTGL18AR4R7M6B72B0




PTGL18AR3R3M6B72B0




■ Operating Time 140V Series (Typical Curve)

PTGL07AR330M6A51B0




PTGL09AR220M6C61B0




■ Operating Time 140V Series (Typical Curve)


PTGL10AR150M6C61B0




PTGL12AR100M6C01B0



PTGL13AR6R8M6C01B0




PTGL16AR5R6M6C01B0




■ Application Circuit 125V Series


(1) Transformer Protection Circuit 1)




(2) Transformer Protection Circuit 2)








(4) Fluorescent Lamp Protection Circuit




■ Application Circuit 140V Series

(1) Transformer Protection Circuit 1)



(2) Transformer Protection Circuit 2)



POSISTOR® for Circuit Protection





for Overcurrent Protection 250/265V Series

"POSISTOR" is a circuit protector whose resistance value in normal operation is very low and in abnormal situations like overcurrent or overheating, will be increased to restrain overcurrent. "POSISTOR" can be used for overcurrent protection against current fuse or temperature fuse, due to its ability to return to its initial condition when overcurrent is removed.

■ Features


- 1. Best suited to meet the requirements for power supply and motor protector. Error-free operations are assured by rush current.
- 2. Circuit is protected until current is turned off.
- 3. Restores the original low resistance value automatically once the overload is removed.
- 4. Non-contact design leads to long life and no noise. Durable and strong against mechanical vibration and shock because it is a solid element.







(PTGL 2B0)



Part Number	Max. Voltage (V)	Non-operating Current (at +60°C)(mA)	Trip Current (at -10°C) (mA)	Max. Current (A)	Resistance (at 25°C) (ohm)	Curie Point (°C)	Body Diameter (D) (mm)	Thickness (T) (mm)	Lead Space (F) (mm)	Lead Diameter (phi d)(mm)
PTGL07BB220N0B52A0	250	90	300	0.5	22 ±30%	100 (BB)	8.0	6.0	5.0	0.6
PTGL10BB120N0P52A0	250	90	300	0.6	12 ±30%	100 (BB)	11.0	6.0	5.0	0.6
PTGL09AR390N0B52A0	250	100	280	0.6	39 ±30%	120 (AR)	10.0	6.0	5.0	0.6
PTGL05AR151H8P52B0	265	28	78	0.2	150 ±25%	120 (AR)	6.0	6.0	5.0	0.6
PTGL05AR181M9N51B0	265	29	70	0.3	180 ±20%	120 (AR)	6.5	6.5	5.0	0.5
PTGL05AR121M9N51B0	265	35	85	0.3	120 ±20%	120 (AR)	6.5	6.5	5.0	0.5
PTGL07AR820M9A51B0	265	60	150	0.5	82 ±20%	120 (AR)	8.2	6.5	5.0	0.5
PTGL07AR700H8B52B0	265	66	185	0.4	70 ±25%	120 (AR)	8.0	6.0	5.0	0.6
PTGL07AR650H8B52B0	265	68	190	1.0	65 ±25%	120 (AR)	8.0	6.0	5.0	0.6
PTGL07AR450H8B52B0	265	80	220	1.0	45 ±25%	120 (AR)	8.0	6.0	5.0	0.6
PTGL07AR560M9A51B0	265	80	190	0.8	56 ±20%	120 (AR)	8.2	6.5	5.0	0.5
PTGI 094R390M9C61R0	265	100	240	1 2	39 +20%	120 (AR)	10.0	6.5	6.5	0.65

Continued from the preceding page.


Part Number	Max. Voltage (V)	Non-operating Current (at +60°C)(mA)	Trip Current (at -10°C) (mA)	Max. Current (A)	Resistance (at 25°C) (ohm)	Curie Point (°C)	Body Diameter (D) (mm)	Thickness (T) (mm)	Lead Space (F) (mm)	Lead Diameter (phi d)(mm)
PTGL09AR250H8B52B0	265	118	330	1.0	25 ±25%	120 (AR)	10.0	6.0	5.0	0.6
PTGL12AR270M9C01B0	265	150	360	1.5	27 ±20%	120 (AR)	14.0	6.5	10.0	0.65
PTGL12AR150H8B72B0	265	165	460	1.5	15 ±25%	120 (AR)	12.5	6.0	7.5	0.6
PTGL14AR180M9C01B0	265	180	440	1.8	18 ±20%	120 (AR)	15.7	6.5	10.0	0.65
PTGL13AR100H8B72B0	265	200	560	2.2	10 ±25%	120 (AR)	14.0	6.0	7.5	0.6
PTGL18AR6R0H8B72B0	265	300	830	4.1	6.0 ±25%	120 (AR)	18.5	6.0	7.5	0.6


Maximum Current shows typical capacities of the transformer which can be used.


Please contact us for UL recognized products.

PTGL_5*B0 series are available in taping type.


■ Protective Threshold Current Range (250V Series)









■ Protective Threshold Current Range (265V Series)











■ Protective Threshold Current Range (265V Series)
























Continued from the preceding page.


■ Protective Threshold Current Range (265V Series)














■ Operating Time 250V Series (Typical Curve)






PTGL10BB120N0P52A0




PTGL09AR390N0B52A0




■ Operating Time 265V Series (Typical Curve)

PTGL05AR151H8P52B0




PTGL05AR181M9N51B0




Continued from the preceding page.

■ Operating Time 265V Series (Typical Curve)


PTGL05AR121M9N51B0




PTGL07AR820M9A51B0




PTGL07AR700H8B52B0




PTGL07AR650H8B52B0



PTGL07AR450H8B52B0




PTGL07AR560M9A51B0




■ Operating Time 265V Series (Typical Curve)


PTGL09AR390M9C61B0




PTGL09AR250H8B52B0




PTGL12AR270M9C01B0




PTGL12AR150H8B72B0



PTGL14AR180M9C01B0




PTGL13AR100H8B72B0




Continued from the preceding page.

■ Operating Time 265V Series (Typical Curve)


PTGL18AR6R0H8B72B0




■ Application Circuit 250V Series




(2) Transformer Protection Circuit 1)




(3) Transformer Protection Circuit 2)



(4) Fluorescent Lamp Protection Circuit









■ Application Circuit 250V Series

(5) Short-Circuit Test of IC




■ Application Circuit 265V Series

(1) Transformer Protection Circuit 1)



(2) Transformer Protection Circuit 2)



PTGL Series Narrow Current Band Specifications and Test Methods

No.	Item	Rating Value	Method of Examination
1	Operating Temperature	-30 to +85°C	The temperature range with maximum voltage applied to the POSISTOR®.
2	Storage Temperature	-40 to +125°C	The temperature range with zero voltage.
3	Resistance Value (at 25°C)	Satisfies ratings	Resistance value is measured by applying voltage under 1.0Vdc (by a direct current of less than 10mA) at 25°C. (But it must be measured after maximum voltage is applied for 180 seconds and then is left for 2 hours at 25°C.)
4	Withstanding Voltage	No problem	We apply AC voltage 120% that of the maximum voltage to POSISTOR® by raising voltage gradually for 180±5 seconds at 25°C. (A protective resistor is to be connected in series, and the inrush current through POSISTOR® must be limited below maximum rated value.)
5	Protective Threshold Current	Satisfies ratings (Trip Current, Non-operating Current)	Maximum current measured in this examination. Voltage is applied to POSISTOR® in 3 minutes step by step on still air based on "Protective Threshold Current Test Conditions" shown in next page. Stable current is measured at each step.
6	Tensile Strength of Lead Wire Terminal	No damage	The load is gradually applied to each terminal of POSISTOR® until the force of the following table in the axial direction with fixing POSISTOR®'s body itself and this load is kept for 10 seconds.
	Wile Terrimia		Lead Diameter Force
			<u>Ø0.60mm max.</u> 4.90N Ø0.65mm min. 9.80N
7	Bending Strength of Lead Wire Terminal	Lead wire does not come off	POSISTOR® is held so that it is perpendicular to the lead wire with the following lead hanging in the axial direction of the lead wire. The lead wire is slowly bent toward 90° and returned. Then it is slowly bent in the opposite direction and returned to original state. Lead Diameter Force
			ø0.60mm max. 2.45N
			<u></u> Ø0.65mm min. 4.90N
8	Solderability	Solder is applied around the lead wire covering 3/4 or more of the circumference without gap in the axial direction.	The Lead wire of POSISTOR® is soaked in a Isopropyl Alcohol (JIS K 8839) solution (about 25wt%) of colophony (JIS K 5902) for 5-10 sec. Each lead wire is soaked in Molten solder (JIS Z 3282 H60A) at 235±5°C from the bottom to a point of 2.0-2.5mm for 2±0.5 seconds.
9	Terminal Durability of Soldering	ΔR/R25≦±15%	The lead wire of POSISTOR® is soaked in Molten solder (JIS Z 3282 H60A) at $350\pm10^{\circ}$ C from the bottom to a point of 2.0-2.5mm for 3.5 ± 0.5 seconds. After the device is left at room temperature (25°C) for 24 \pm 4 hours, the resistance is then measured.
10	Humidity Test	ΔR/R25≦±20%	POSISTOR® is set in an environmental chamber at 60±2°C and 90-95% humidity for 500±4 hours. After the device is left at room temperature (25°C) for one hour, the resistance measurement is then performed.
11	Load Test at High Temperature	ΔR/R25≦±20%	POSISTOR® is set in an environmental chamber at 85±3°C with maximum voltage applied for 500±4 hours. After the device is left at room temperature (25°C) for one hour, the resistance measurement is performed. (A protective resistor is to be connected in series and the inrush current through POSISTOR® must be limited below maximum rated value.)
12	Load Cycle Test at Room Temperature	ΔR/R25≦±20%	POSISTOR® is set in a room temperature at 25±2°C with maximum voltage applied for 1 minute and then is left without voltage applied for 5 minutes. This cycle is repeated for 100 cycles, and after the device is left at room temperature (25°C) for one hour, the resistance measurement is performed. (A protective resistor is to be connected in series and the inrush current through POSISTOR® must be limited below maximum rated value.)





PTGL Series Narrow Current Band Specifications and Test Methods


Continued from the preceding page.

■ Protective Threshold Current Test Conditions

1. Substrate


Materials: Phenol Size: 50x50xt1.6mm

Land Pattern: Cu land without through hole




2. Measurement condition

Solder POSISTOR® on the substrate, then put the cover (150mm cubed) surround POSISTOR® to prevent flow of wind.



3. Measurement circuit





PTGL Series Specifications and Test Methods

Item	Rating Value	Method of Examination			
Continuous Operating Temperature	-10 to +60 °C	The temperature range with maximum voltage applied to the POSISTOR®.			
Resistance Value (at 25°C)	Satisfies ratings	Resistance value is measured by applying voltage under 1.5Vdc (by a direct current of less than 10mA) at 25°C. (But it must be measured after maximum voltage is applied for 180 seconds and then is left for 2 hours at 25°C.) As for 16V series, measurement probe should be connected on the lead wire at the point within 2mm from the below side of the forming. Resistance should be measured 4 wing method.			
Withstanding Voltage	No problem	We apply AC voltage 120% that of the maximum voltage to POSISTOR® by raising voltage gradually for 180±5 seconds at 25°C. (A protective resistor is to be connected in series, and the inrush current through POSISTOR® must be limited below max. rated value.)			
Tensile Strength of Lead Wire Terminal	No damage	The load is gradually applied to each terminal of POSISTO until the force of the following table in the axial direction wit fixing POSISTOR® s body itself and this load is being kept 10 seconds. Lead Diameter Force Ø0.60mm max. 4.90N Ø0.65mm min. 9.80N			
Bending Strength of Lead Wire Terminal	Lead wire does not come off	POSISTOR® is held so that it is perpendicular to the lead wire with the following lead hanging in the axial direction of the lead wire. The lead wire is slowly bent toward 90° and returned. Then it is slowly bent in the opposite direction and returned to original state. Lead Diameter Force Ø0.60mm max. 2.45N Ø0.65mm min. 4.90N			
Solderability	Solder is applied around the lead wire covering 3/4 or more of the circumference without gap in the axial direction.	The Lead wire of POSISTOR® is soaked in a Isopropyl alcohol (JIS K 8839) or ethanol (JIS K 8101) solution (about 25wt%) of colophony (JIS K 5902) for 5 to 10 sec. And, each lead wire is soaked in Molten solder (JIS Z 3282 H60A) at 235±5°C from the bottom to a point of 2.0 to 2.5mm for 2±0.5 sec.			
Terminal Durability of Soldering	ΔR/R25≦±15%	The lead wire of POSISTOR® is soaked in Molten solder (JIS Z 3282 H60A) at 350±10°C from the bottom to a point of 2.0 to 2.5mm for 3.5±0.5 sec. And, after the device is being left at room temperature (25°C) for 24±4 hours, the resistance is measured.			
Humidity Test	ΔR/R25≦±20%	POSISTOR® is set in an environmental chamber at 40±2°C and 90 to 95% humidity for 500±4 hours. And after the device is being left at room temperature (25°C) for one hour, the resistance measurement is performed.			
Load Cycle Test at High Temperature	ΔR/R25≦±20%	POSISTOR® is set in an environmental chamber at 60±3°C with maximum voltage applied for 1.5 hours and then is left without voltage applied for 0.5 hours. This cycle is repeatedfor 1000±10 hours, and after the device is left at room temperature (25°C) for one hour, the resistance measurement is performed. (A protective resistor is to be connected in series and the inrush current through POSISTOR® must be limited below max. rated value.)			



7

POSISTOR® for Circuit Protection



for Overheat Sensing Chip Type


Chip Type 0603 (1608) Size

This chip PTC Thermistor is reflow soldering SMD type for overheat sensing for power transistors, power diodes and power ICs in hybrid circuits.

■ Features

- 1. SMD type is helpful for miniaturizing circuits because of its small size and light weight.
- 2. Excellent thermal response due to small size
- 3. Solid-state construction provides excellent mechanical vibration and impact resistance.
- 4. Contactless operation provides noiseless operation.
- 5. Lead is not contained in the terminations.





Part Number		Dimen	sions (mm)	
Part Number	L	W	T	е	g
PRF18_RB	1.6±0.15	0.8±0.15	0.8±0.15	0.1 to 0.6	-
PRF21_RA	2.0±0.2	1.25±0.2	0.9±0.2	0.2 min.	0.5 min.

Part Number	Sensing Temperature (at 4.7k ohm) (°C)	Maximum Voltage (V)	Resistance (at 25°C) (ohm)	Temperature Range (°C)
PRF18BG471QB1RB	65 ±5°C	32	470 ±50%	-20 to 80
PRF18BF471QB1RB	75 ±5°C	32	470 ±50%	-20 to 90
PRF18BE471QB1RB	85 ±5°C	32	470 ±50%	-20 to 100
PRF18BD471QB1RB	95 ±5°C	32	470 ±50%	-20 to 110
PRF18BC471QB1RB	105 ±5°C	32	470 ±50%	-20 to 120
PRF18BB471QB1RB	115 ±5°C	32	470 ±50%	-20 to 130
PRF18BA471QB1RB	125 ±5°C	32	470 ±50%	-20 to 140
PRF18AR471QB1RB	135 ±5°C	32	470 ±50%	-20 to 150
PRF18AS471QB1RB	145 ±5°C	32	470 ±50%	-20 to 160

This product is applied to reflow soldering. Please consult us for flow soldering usage.


Chip Tight Tolerance Type 0603 (1608) Size

PRF18_RB1RB series is an improvement on sensing accuracy from existing PRF18_QB1RB series.

■ Features

- Sensing accuracy +/-3 deg.C which is highest of PTC Thermistor and the same level as NTC at sensing point.
- 2. Same resistance-temperature characteristics as PRF18_QB1RB series.
 - Easy to use higher accurate sensing type.
- 3. SMD type is helpful for miniaturizing circuits because of its small size and light weight.
- 4. Excellent thermal response due to small size
- Solid-state construction provides excellent mechanical vibration and impact resistance.
- 6. Contactless operation provides noiseless operation.
- 7. Lead is not contained in the terminations.





Part Number		Dimen:	sions (mm)	
Part Number	L	W	Т	е	g
PRF18_RB	1.6±0.15	0.8±0.15	0.8±0.15	0.1 to 0.6	-
PRF21_RA	2.0±0.2	1.25±0.2	0.9±0.2	0.2 min.	0.5 min.



Part Number	Sensing Temperature (at 4.7k ohm) (°C)	Maximum Voltage (V)	Resistance (at 25°C) (ohm)	Temperature Range (°C)
PRF18BE471RB1RB	85 ±3°C	32	470 ±50%	-20 to 100
PRF18BD471RB1RB	95 ±3°C	32	470 ±50%	-20 to 110
PRF18BC471RB1RB	105 ±3°C	32	470 ±50%	-20 to 120
PRF18BB471RB1RB	115 ±3°C	32	470 ±50%	-20 to 130


This product is applied to reflow soldering. Please consult us for flow soldering usage.

Chip Type 0805 (2012) Size

This chip PTC Thermistor is reflow soldering SMD type for overheat sensing for power transistors, power diodes and power ICs in hybrid circuits.

■ Features

- 1. SMD type is helpful for miniaturizing circuits because of its small size and light weight.
- 2. Excellent thermal response due to small size
- 3. Solid-state construction provides excellent mechanical vibration and impact resistance.
- 4. Contactless operation provides noiseless operation.
- 5. Lead is not contained in the terminations.




Part Number		Dimen:	sions (mm)	
Part Number	L	W	T	е	g
PRF18_RB	1.6±0.15	0.8±0.15	0.8±0.15	0.1 to 0.6	-
PRF21_RA	2.0±0.2	1.25±0.2	0.9±0.2	0.2 min.	0.5 min.

Part Number	Sensing Temperature (at 4.7k ohm) (°C)	Maximum Voltage (V)	Resistance (at 25°C) (ohm)	Temperature Range (°C)
PRF21BE471QB1RA	85 ±5°C	32	470 ±50%	-20 to 100
PRF21BD471QB1RA	95 ±5°C	32	470 ±50%	-20 to 110
PRF21BC471QB1RA	105 ±5°C	32	470 ±50%	-20 to 120
PRF21BB471QB1RA	115 ±5°C	32	470 ±50%	-20 to 130
PRF21BA471QB1RA	125 ±5°C	32	470 ±50%	-20 to 140
PRF21AR471QB1RA	135 ±5°C	32	470 ±50%	-20 to 150
PRF21AS471QB1RA	145 ±5°C	32	470 ±50%	-20 to 160

(in mm)


This product is applied to reflow soldering. Please consult us for flow soldering usage.

■ Standard Land Pattern Dimensions




Part Number	Soldering	Dimensions (mm)					
Part Number	Methods	Chip (LXW)	a	b	С		
PRF18	Flow Soldering	1.6×0.8	0.6-1.0	0.8-0.9	0.6-0.8		
	Reflow Soldering	1.6×0.8	0.6-0.8	0.6-0.7	0.6-0.8		
PRF21	Reflow Soldering	2.0X1.25	1.0-1.2	0.5-0.7	1.0-1.2		

■ Resistance-Temperature Characteristics (Typical)






■ Overheat Protection Circuit




■ Temperature Sensing Circuit




Chip Type (Ref. Only)

■ Resistance-Temperature Characteristics Range







PRF_BF471Q Type



PRF_BE471Q Type



PRF_BD471Q Type








Chip Type (Ref. Only)


Continued from the preceding page.

■ Resistance-Temperature Characteristics Range


PRF_BC471Q Type




PRF_BB471Q Type



PRF_BA471Q Type



PRF_AR471Q Type








Chip Type (Ref. Only)

Continued from the preceding page.

■ Resistance-Temperature Characteristics Range


PRF_AS471Q Type




Chip Tight Tolerance Type (Ref. Only)

■ Resistance-Temperature Characteristics Range


PRF18BE471RB1RB




PRF18BD471RB1RB



PRF18BC471RB1RB



PRF18BB471RB1RB





Chip Type Specifications and Test Methods

No.	Item	Rating Value	Method of Examination		
1	Resistance Value (at 25°C)	The resistance value should be within the specified tolerance.	After applying max. operating voltage for 3 mins. and leaving for 2 hrs. at 25°C, measured by applying voltage of less than 1.5Vdc (by a direct current of less than 10mA).		
2	Adhesive Strength	There is no sign of electrode exfoliation	EIAJ ET-7403 term 9 Solder PTC to PCB and add a force of 5.0N in the direction shown below. PTC Glass Epoxy PCB F=5.0N		
3	Vibrationability	Normal appearance Resistance change: not to exceed ±20% (*)	JIS C 5102 term 8.2 Soldered PTC to PCB Vibration: 10-55-10Hz (1 min.) Width: 1.5mm Vibrate for 2 hrs. in each of 3 mutually perpendicular planes for a total of 6 hrs.		
4	Solderability	Min. 75% electrode is covered with new solder. Resistance change: not to exceed ±20% (*)	JIS C 5102 term 8.4 Solder: Sn 63%/Pb 37% (or 60/40%) Solder temp: 230±5°C Soaking time: 3±0.5 sec. Soaking position: Until a whole electrode is soaked.		
5	Solder-heatability	Normal appearance Resistance change: not to exceed ±20% (*)	Solder: Sn 63%/Pb 37% (or 60/40%) Flux: Solder paste containing less than 0.2wt% of chlorine. Preheating: 150±5°C 3 mins. Peak temp.: 260±5°C 10±5 sec. (reflow) PCB: Glass Epoxy PCB (JIS C 6484)		
6	Temperature Cycling	Normal appearance Resistance change: not to exceed ±20% (*)	JIS C 5102 term 9.3 Times: 5 cycles Step Temp. (°C) Time (min.) 1 -20 +0, -3 30 2 Room temp. 10-15 3 +150 +3, -0 30 4 Room temp. 10-15		
7	Humidity Test	Normal appearance Resistance change: not to exceed ±20% (*)	JIS C 5102 term 9.5 40±2°C, 90-95%RH leave for 500±8 hrs.		
8	High Temperature Load Test	Normal appearance Resistance change: not to exceed ±20% (*)	JIS C 5102 term 9.10 85±5°C (in air), load max. operating voltage for 1000±12 hrs.		

^(*) Measurement resistance after the test by applying voltage of less than 1.5Vdc by a direct current of less than 10mA after product is left at 25±2°C for 2 hours.

Above mentioned soldering in "2. Adhesive Strength" and "3. Vibrationability" is done following condition at our side.

- •Glass-Epoxy PC board
- •Standard land dimension
- •Standard solder paste
- •Standard solder profile

Above conditions are mentioned in Notice.



Chip Tight Tolerance Type Specifications and Test Methods

No.	Item	Rating Value	Method of Examination		
1	Resistance Value (at 25°C)	The resistance value should be within the specified tolerance.	After applying max. operating voltage for 3 mins. and leaving for 2 hrs. at 25°C, measured by applying voltage of less than 1.5Vdc. (by a direct current of less than 10mA).		
2	Adhesive Strength	There is no sign of electrode exfoliation	EIAJ ET-7403 term 9 Solder PTC to PCB and add a force of 5.0N in the direction shown below. PTC Glass Epoxy PCB F=5.0N		
3	Vibrationability	Normal appearance Resistance change: not to exceed ±20% (*1)	JIS C 5102 term 8.2 Soldered PTC to PCB Vibration: 10-55-10Hz (1 min.) Width: 1.5mm Vibrate for 2 hrs. in each of 3 mutually perpendicular planes for a total of 6 hrs.		
4	Solderability	Min. 75% electrode is covered with new solder. Resistance change: not to exceed ±20% (*1)	JIS C 5102 term 8.4 Solder: Sn 63%/Pb 37% (or 60/40%) Solder temp: 230±5°C Soaking time: 3±0.5 sec. Soaking position: Until a whole electrode is soaked		
5	Solder-heatability	Normal appearance Resistance change: not to exceed ±20% (*1)	Solder: Sn 63%/Pb 37% (or 60/40%) Flux: Solder paste containing less than 0.2wt% of chlorine. Preheating: 150±5°C 3mins. Peak temp.: 260±5°C 10±5 sec. (reflow) PCB: Glass Epoxy PCB (JIS C 6484)		
6	Temperature Cycling	Normal appearance Resistance change: not to exceed ±20% (*1, 2)	JIS C 5102 term 9.3 Times: 5 cycles Step Temp. (°C) Time (min.) 1 -20 +0, -3 30 2 Room temp. 10-15 3 +150 +3, -0 30 4 Room temp. 10-15		
7	Humidity Test	Normal appearance Resistance change: not to exceed ±20% (*1, 2)	JIS C 5102 term 9.5 40±2°C, 90-95%RH leave for 500±8 hrs.		
8	High Temperature Load Test	Normal appearance Resistance change: not to exceed ±20% (*1, 2)	JIS C 5102 term 9.10 85±5°C (in air), load max. operating voltage for 1000±12 hrs.		

^(*1) Measurement resistance after the test by applying voltage of less than 1.5Vdc by a direct current of less than 10mA after product is left at 25±2°C for 2 hours. (*2) Sensing temp. change: not to exceed ±1°C

Above mentioned soldering in "2. Adhesive Strength" and "3. Vibrationability" is done following condition at our side.

- •Glass-Epoxy PC board
- •Standard land dimension
- •Standard solder paste
- Standard solder profile

Above conditions are mentioned in Notice.



POSISTOR® for Circuit Protection





for Overheat Sensing Lead Type

PTFM type has been developed for protecting power transistors, stereo main amplifiers, etc. from overheating, and also for sensing the temperature of other components which may be overheated. The "POSISTOR" offers an excellent temperature sensing ability, exhibiting a steep change in electrical resistivity near the temperature setting. PTFL type is suitable for use as an air temperature sensor.

■ Features

- 1. PTFM type is a screw-fixing type and PTFL type is a lead type, therefore mounting is easy.
- 2. Compact and light design as well as excellent thermal response.
- 3. Solid-state construction withstands mechanical vibration and impact sufficiently.
- 4. Contactless operation provides a prolonged service life, yet permits noiseless operation.
- The operating point of "POSISTOR" is set on the steepest point along the resistance-temperature characteristic curve, thus performing the overheat protective operation securely.
- 6. PTFM type and PTFL type have the same temperature characteristic, providing a selection depending on the mounting method.






Part Number	Max. Voltage (V)	Curie Point (°C)	Sensing Temp. (TS) (°C)	Resistance Value at 25°C (max.) (ohm)	Resistance Value (at Sensing Temp10°C) (max.) (ohm)	Resistance Value (at Sensing Temp. TS°C) (min.) (ohm)
PTF□04BH471Q2N34B0	16	40 (BH)	60	100	330	470
PTF□04BG471Q2N34B0	16	50 (BG)	70	100	330	470
PTF□04BF471Q2N34B0	16	60 (BF)	80	100	330	470
PTF□04BE471Q2N34B0	16	70 (BE)	90	100	330	470
PTF□04BD471Q2N34B0	16	80 (BD)	100	100	330	470
PTF□04BC471Q2N34B0	16	90 (BC)	110	100	330	470
PTF□04BB471Q2N34B0	16	100 (BB)	120	100	330	470
PTF□04BH222Q2N34B0	16	40 (BH)	60	330	1.5k	2.2k
PTF□04BG222Q2N34B0	16	50 (BG)	70	330	1.5k	2.2k
PTF□04BF222Q2N34B0	16	60 (BF)	80	330	1.5k	2.2k
PTF□04BE222Q2N34B0	16	70 (BE)	90	330	1.5k	2.2k
PTF□04BD222Q2N34B0	16	80 (BD)	100	330	1.5k	2.2k
PTF□04BC222Q2N34B0	16	90 (BC)	110	330	1.5k	2.2k
PTF□04BB222Q2N34B0	16	100 (BB)	120	330	1.5k	2.2k


A blank is filled with type codes. (L: Lead type, M: with Lug-terminal) $\,$

■ Resistance-Temperature Characteristics




■ Example of Thermal Response Time

Operating Time of POSISTOR®




Relation between resistance change and time after POSISTOR® PTFM04BE222Q2N34B0 is installed on the part heated at a constant temperature of 90°C (3mm thick alminum sheet) is shown in the figure below.


■ Overheat Protection Circuit




■ Overheat Sensing Circuit



■ Resistance-Temperature Characteristics Range (Ref. Only)







Continued on the following page.





10


■ Resistance-Temperature Characteristics Range (Ref. Only)
















68


10


Continued from the preceding page.


■ Resistance-Temperature Characteristics Range (Ref. Only)














for Temperature Sensor Lead Type Specifications and Test Methods

No.	Item	Rating Value	Method of Examination		
1	Resistance Value	Satisfies specification	Resistance value is measured by applying voltage under 1.5Vdc (by a direct current of less than 10mA) in a silicone oil vessel.		
2	Withstanding Voltage	No problem	We apply AC voltage 120% that of the maximum voltage to POSISTOR® by raising voltage gradually for 180±5 seconds at 25°C. (A protective resistor is to be connected in series, and the inrush current through POSISTOR® must be limited below max rated value.)		
3	Tensile Strength of Lead Wire Terminal	No damage	The load is gradually applied to each terminal of POSISTOR® until the force of the following table in the axial-direction with fixing POSISTOR®'s body itself and this load is kept for 10 seconds. Series Force PTFL 4.90N PTFM 9.80N		
4	Bending Strength of Lead Wire Terminal	Lead wire does not come off	POSISTOR® is held so that it is perpendicular to the lead wire with the following load hanging in the axial direction of the lead wire. The lead wire is slowly bent toward 90° and returned; then it is slowly bent in the opposite direction and returned to original state. (Above mentioned procedure is done slowly with one cycle.) Series Force PTFL 2.45N PTFM 4.90N		
5	Solderability	Solder is applied around the lead wire covering 3/4 or more of the circumference without gap in the axial-direction.	The lead wire of POSISTOR® is soaked in a Isopropyl Alcohol (JIS K 8839) or ethanol (JIS K 8101) solution (about 25wt%) of colophony (JIS K 5902) for 5-10 sec. And, each lead wire is soaked in molten solder (JIS Z 3282 H60A) at 235±5°C from the bottom to a point of 2.0-2.5mm for 2±0.5 sec.		
6	Terminal Durability of Soldering	ΔR/R25≦±15%	The lead wire of POSISTOR® is soaked in molten solder (JIS Z 3282 H60A) at 350±10°C from the bottom to a point of 2.0-2.5 mm for 3.5±0.5 sec. And, after the device is left at room temperature (25°C) for 24±4 hours, the resistance is measured.		
7	Humidity Test	ΔR/R25≦±20%	POSISTOR® is set in an environmental chamber at 40±2°C and 90-95% humidity for 500±4 hours. And after the device is left at room temperature (25°C) for one hour, the resistance measurement is performed.		
8	Load Cycle Test at High Temperature	POSISTOR® is set in an environmental chamber a maximum voltage applied for 1.5 hours and then is voltage applied for 0.5 hours. This cycle is repeated for 1000±10 hours, and after left at room temperature (25°C) for one hour, the remeasurement is performed. (A protective resistor is to be connected in series at current through POSISTOR® must be limited below value.)			

∴Caution/Notice

■ ① Caution (Storage and Operating Condition)

This product is designed for application in an ordinary environment (normal room temperature, humidity and atmospheric pressure). Do not use under the following conditions because all these factors can deteriorate the characteristics or cause product failure and burn-out.

 Corrosive gas or deoxidizing gas (Chlorine gas, Hydrogen sulfide gas, Ammonia gas, Sulfuric acid gas, Nitric oxide gas, etc.)

■ **(**Caution (Other)

Be sure to provide an appropriate fail-safe function on your product to prevent secondary damage that may be caused by the abnormal function or the failure of our product.

■ Notice (Storage and Operating Condition)

To keep solderability of product from declining, following storage condition is recommended.

- Storage condition:
 Temperature -10 to +40 degree C
 Humidity less than 75%RH (not dewing condition)
- Storage term:
 Use this product within 6 months after delivery by first-in and first-out stocking system.

■ Notice (Soldering and Mounting)

PTGL Series

When the lead of this product is soldered, pay attention as follows to avoid the decline of element characteristics or break-down of the element.

- 1. Use Rosin type flux or non-activated flux
- Do not dip the body into flux. (flux should be coated to lead wire only for soldering.)
- 3. Be sure that preheating does not melt the soldering of this product.
- Notice (Soldering and Mounting)

PTFL/PTFM Series

- 1. PTFM type is to be screwed beside the Power-Transistor on the radiative plate.
- 2. If PTFL type is adhered on the portion to detect temperature with some adhesive, please do not use the Ciano Acclilate family one.
- Please bend the lead wire far from the root of the body and do not apply force to the lead wire of the product.

- 2. Volatile or flammable gas
- 3. Dusty conditions
- 4. Under high or low pressure
- 5. Wet or humid conditions
- 6. Places with salt water, oils, chemical liquids or organic solvents
- 7. Strong vibrations
- 8. Other places where similar hazardous conditions

- Handling after unpacking:
 After unpacking, promptly reseal this product or store it in a sealed container with a drying agent.
- Storage place:
 Do not store this product in corrosive gas (sulfuric acid, chlorine, etc.) or in direct sunlight.

- When the lead of this product is soldered, pay attention as follows to avoid the decline of element characteristics or break-down of the element.
- (1) Use Rosin type flux or non-activated flux.
- (2) Do not dip the body into flux. (Flux should be coated to lead wire only for soldering.)
- (3) Be sure that preheating does not melt the soldering of this product.



⚠Caution/Notice

■ Notice (Soldering and Mounting) PRG/PRF Series

1. Solder and Flux

(1) Solder Paste

Use solder paste Sn:Pb=63:37wt%.

For your reference, we are using

63Sn/37Pb RMA9086 90-3-M18,

manufactured by Alpha Metals Japan Ltd.

96.5Sn/3.0Ag/0.5Cu M705-221BM5-42-11,

manufactured by Senju Metal Industry Co., LTD for any Internal tests of this product.

(2) Flux

Use rosin-based flux. Do not use strong acidic flux (with halide content exceeding 0.2wt%).

2. Cleaning Conditions and Drying

To remove the flux after soldering, observe the following points in order to avoid deterioration of the characteristics or any change to the external electrodes quality.

(1) Cleaning Conditions

Solvent	Dipping Cleaning	Ultrasonic Cleaning
2-propanol	Less than 5 min. at room temp. or Less than 2 min. at 40°C max.	Less than 1 min. 20W/L Frequency of several 10kHz to 100kHz.

A sufficient cleaning should be applied to remove flux completely.

(2) Drying


After cleaning, promptly dry this product.

3. Soldering Conditions

In your mounting process, observe the following points in order to avoid deterioration of the characteristics or destruction of this product. The mounting quality of this product may also be affected by the mounting conditions, shown in the points below.

This product is for only reflow soldering. Flow soldering should not be allowed.

- (1) Printing Conditions of Solder Paste
 - (a) Standard thickness of solder paste printing should be from 0.15 to 0.20 mm.
 - (b) After soldering, the solder fillet should be a height from 0.2 mm to the thickness of this product (see the figure at right).
 - (c) Too much solder gives too strong mechanical stress to this product. Such stress may cause cracking or other mechanical damage. Also, it can destroy the electrical performance of this product.







∴Caution/Notice

Continued from the preceding page.


- (2) Allowable Soldering Temperature and Time
 - (a) Solder within the temperature and time combinations, indicated by the slanted lines in the right graphs.
 - (b) The excessive soldering conditions may cause dissolution of metallization or deterioration of solderwetting on the external electrode.
 - (c) In the event that soldering is repeated more than twice, the allowable reflow soldering time should be the accumulated soldering time.



- (3) Standard Temperature Profile for Soldering
- (a) Insufficient preheating may cause a crack on ceramic body. Difference between preheating temperature and maximum temperature in the profile should be 100℃.
- (b) Rapid cooling by dipping in solvent or by other means is not recommended.



specified mounting conditions.



∆Caution/Notice

■ Notice (Handling)

PTGL Series

- Do not apply an excessive force to the lead.
 Otherwise, it may cause the junction between lead and element to break, or may crack the element.
 Therefore, holding the element side lead wire is recommended when lead wire is bent or cut.
- This product does not have waterproof construction. Splashed water may cause failure mode such as decline of characteristics or current leak.
- area may be over 100 to 160 degree C. Be sure that surrounding parts and inserting material can withstand the temperature. If the surrounding part and material are kept under such condition, they may deteriorate or produce harmful gas (Chlorine gas, Hydrogen sulfide gas, Ammonia gas, Sulfuric acid gas, Nitric oxide gas, etc.). And such harmful gas may deteriorate the element.

3. When this product is operated, temperature of some

■ Notice (Handling)

PTFL/PTFM Series

- Do not apply an excessive force to the lead.
 Otherwise, it may cause the junction between lead and element to break, or may crack the element.
 Therefore, holding the element side lead wire is recommended when lead wire is bent or cut.
- This product does not have waterproof construction.Splashed water may cause failure mode such as decline of characteristics or current leak.

■ Notice (Handling)

PRG/PRF Series

- 1. When this product is operated, temperature of some area may be over 100 to 150 degree C. Be sure that surrounding parts and inserting material can withstand the temperature. If the surrounding part and material are kept under such condition, they may deteriorate or produce harmful gas (Chlorine gas, Hydrogen sulfide gas, Ammonia gas, Sulfuric acid gas, Nitric oxide gas, etc.). And such harmful gas may deteriorate the element.
- Do not assemble this product with air-sealing or resin casting. Such sealing may deteriorate element.




PRG/PRF Series Package


■ Minimum Quantity Guide

Part Number	Quantity (pcs.)			
Part Number	Paper Tape	Plastic Tape		
PR*18_RB	4000	-		
PR*21_RA	-	4000		
PR*21_RK	-	3000		


■ Tape Dimensions




PR*21_RA Series : Plastic Tape



PR*21_RK Series : Plastic Tape



■ Reel Dimensions



Lead Type PTGL Series Package

■ Minimum Order Quantity

1. Bulk: 100 pcs.

2. Taping

z. raping					
Series	Taping Part Number	Minimum Quantity (pcs.)			
36163	raping Fait Number	Ammo Pack			
Narrow	PTGL04AS100K2B51A0	1500			
Current Band 30V series	PTGL04AS100K2N51A0				
30V Series	PTGL05AS3R9K2B51A0				
	PTGL07AS1R8K2B51A0				
	PTGL07AS2R7K2B51A0				
	PTGL09AS1R2K2B51A0				
	PTGL12AS0R8K2B51A0				
Narrow	PTGL04AS100K3B51A0	1500			
Current Band	PTGL05AS6R8K3B51A0				
51V series	PTGL07AS3R3K3B51A0				
	PTGL09AS2R2K3B51A0				
	PTGL12AS1R2K3B51A0				
Narrow	PTGL04AS220K4B51A0	1500			
Current Band	PTGL04AS220K4N51A0				
60V series	PTGL05AS100K4B51A0				
	PTGL07AS5R6K4B51A0				
	PTGL07AS5R6K4N51A0				
	PTGL09AS3R3K4B51A0				
	PTGL12AS2R2K4B51A0				
Narrow	PTGL04AS560K6B51A0	1500			
Current Band	PTGL05AS270K6B51A0				
140V series	PTGL07AS150K6B51A0				
	PTGL09AS120K6B51A0				
	PTGL09AS7R6K6B51A0				
	PTGL12AS4R7K6B51A0				
	-				

	T : D .N .	Minimum Quantity (pcs.)
Series	Taping Part Number	Ammo Pack
24V series	PTGL07BD100N2B51A0	1500
	PTGL07BD6R8N2B51A0	
	PTGL09BD4R7N2B51A0	
	PTGL09BD3R3N2B51A0	
	PTGL09BD2R2N2B51A0	
30V series	PTGL04AR130H2B51A0	1500
	PTGL07AR4R6H2B51A0	
	PTGL09AR1R8H2B51A0	
32V series	PTGL07BD470N3B51A0	1500
	PTGL07BD330N3B51A0	
	PTGL07BD220N3B51A0	
	PTGL07BD150N3B51A0	
56V series	PTGL07AR220M3P51A0	1500
	PTGL07AR8R2M3P51A0	
	PTGL09AR150M3B51A0	
	PTGL10AR3R9M3P51A0	
	PTGL09AR4R7M3B51A0	
	PTGL10AR3R9M3B51A0	
80V series	PTGL05AR550H4P51A0	1500
	PTGL07AR250H4B51A0	
	PTGL09AR9R4H4B51A0	
125V series	PTGL05AR181M7P52A0	1000
	PTGL07AR750M7B52A0	
	PTGL09AR470M6B52A0	
	PTGL09AR220M6B52A0	
250V series	PTGL07BB220N0B52A0	1000
	PTGL09AR390N0B52A0	
	PTGL10BB120N0P52A0	
265V series	PTGL05AR151H8P52A0	1000
	PTGL07AR700H8B52A0	
	PTGL07AR650H8B52A0	
	PTGL07AR450H8B52A0	
	PTGL09AR250H8B52A0	






Lead Type PTGL Series Package

Continued from the preceding page.

■ 24-80V/Narrow Curent Band 30-140V Series Taping Dimensions



Item	Code	Dimensions (mm)	Note
Pitch of Component	Р	12.7	Tolerance is determined by ΔS .
Pitch of Sprocket Hole	Po	12.7±0.3	
Lead Spacing	F	5.0+0.8	
Length from Hole Center to Lead	P1	3.85±0.8	
Length from Hole Center to Component	P ₂	6.35±1.3	Deviation in the feeding direction
Body Diameter	D	Please see in Ratings	
Thickness	Т	Please see in Ratings	
Deviation along Tape, Left or Right	ΔS	±1.5	Including the inclination caused by lead bending.
Carrier Tape Width	W	18.0±0.5	
Position of Sprocket Hole	W1	9.0 ^{+0.5} _{-0.75}	Deviation of tape width.
Lead Distance between Reference and	H ₀	16.0±1.0	
Bottom Planes	H ₂	6.0 max.	
Overflow of Lead	I	+0.5 to -1.0	
Diameter of Sprocket Hole	D ₀	4.0±0.2	
Lead Diameter	d	Please see in Ratings	
Total Tana Thickness	t1	0.6±0.3	
Total Tape Thickness	t2	2.0 max.	
Deviation across Tape	Δh1, Δh2	1.5 max.	
Portion to cut in Case of Defect	L	11.0+0	
Hold Down Tape Width	Wo	11.0 min.	
Hold Down Tape Position	W2	4.0 max.	
Coating Extension on Lead	е	Up to the center of crimp	






Lead Type PTGL Series Package

Continued from the preceding page.

■ 125/250/265V Series Taping Dimensions



Item	Code	Dimensions (mm)	Note
Pitch of Component	Р	12.7	Tolerance is determined by ΔS.
Pitch of Sprocket Hole	Po	12.7±0.3	
Lead Spacing	F	5.0+0.8	
Length from Hole Center to Lead	P1	3.85±0.8	
Length from Hole Center to Component	P ₂	6.35±1.3	Deviation in the feeding direction
Body Diameter	D	Please see Ratings	
Thickness	Т	Please see Ratings	
Deviation along Tape, Left or Right	ΔS	±1.5	Including the inclination caused by lead bending.
Carrier Tape Width	W	18.0±0.5	
Position of Sprocket Hole	W1	9.0 ^{+0.5} _{-0.75}	Deviation of tape width.
Lead Distance between Reference and	Ho	16.0±1.0	
Bottom Planes	H ₂	6.0 max.	
Overflow of Lead	I	+0.5 to -1.0	
Diameter of Sprocket Hole	D ₀	4.0±0.2	
Lead Diameter	d	0.6±0.05	
Total Tana Thiaknasa	t1	0.6±0.3	
Total Tape Thickness	t2	2.0 max.	
Deviation across Tape	Δh1, Δh2	1.5 max.	
Portion to cut in Case of Defect	L	11.0+0	
Hold Down Tape Width	Wo	11.0 min.	
Hold Down Tape Position	W2	4.0 max.	
Coating Extension on Lead	е	Up to the center of crimp	

⚠ Note:

1. Export Control

(For customers outside Japan)

Murata products should not be used or sold for use in the development, production, stockpiling or utilization of any conventional weapons or mass-destructive weapons (nuclear weapons, chemical or biological weapons, or missiles), or any other weapons.

For products which are controlled items subject to the "Foreign Exchange and Foreign Trade Law" of Japan, the export license specified by the law is required for export.

- 2. Please contact our sales representatives or product engineers before using the products in this catalog for the applications listed below, which require especially high reliability for the prevention of defects which might directly damage to a third party's life, body or property, or when one of our products is intended for use in applications other than those specified in this catalog.
 - Aircraft equipment
 Undersea equipment
- ② Aerospace equipment④ Power plant equipment
- Medical equipment
- 6 Transportation equipment (vehicles, trains, ships, etc.)
- Traffic signal equipment
- (8) Disaster prevention / crime prevention equipment
- Data-processing equipment
- (1) Application of similar complexity and/or reliability requirements to the applications listed in the above
- 3. Product specifications in this catalog are as of November 2004. They are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. If there are any questions, please contact our sales representatives or product engineers.
- 4. Please read rating and ACAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
- 5. This catalog has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.
- 6. Please note that unless otherwise specified, we shall assume no responsibility whatsoever for any conflict or dispute that may occur in connection with the effect of our and/or a third party's intellectual property rights and other related rights in consideration of your use of our products and/or information described or contained in our catalogs. In this connection, no representation shall be made to the effect that any third parties are authorized to use the rights mentioned above under licenses without our consent.
- 7. No ozone depleting substances (ODS) under the Montreal Protocol are used in our manufacturing process.



http://www.murata.com/