


MICRO BOARD STACKER

(1.27 mm) .050" PITCH • DWM/HDWM SERIES



DWM/HDWM

Mates:

SMS, SLM, RSM

SPECIFICATIONS

Insulator Material:

Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over 50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 °C to +105 °C with Tin

-55 °C to +125 °C with Gold

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.15 mm) .006" max*

*(.004" stencil solution

may be available; contact



ipg@samtec.com)

ALSO AVAILABLE

Contact Samtec

Other Platings

DWM	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	OTHER OPTION																												
	01 thru 50	Specify LEAD STYLE from chart	-L = 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail -G = 10 μ" (0.25 μm) Gold on contact, Gold flash on tail	-S = Single Row -D = Double Row	- "XXX" = Stacker Height Example: -200 = (5.08 mm) .200"	- "XXX" = Polarized Position (Specify position of omitted pin)																												
<table><tr><th colspan="2">OAL</th></tr><tr><th>LEAD STYLE</th><th>THROUGH-HOLE</th></tr><tr><td>-01</td><td>(11.43) .450</td></tr><tr><td>-51</td><td>(10.41) .410</td></tr><tr><td>-52</td><td>(10.80) .425</td></tr><tr><td>-53</td><td>(12.83) .505</td></tr><tr><td>-54</td><td>(14.10) .555</td></tr><tr><td>-55</td><td>(15.49) .610</td></tr><tr><td>-56</td><td>(15.88) .625</td></tr><tr><td>-57</td><td>(16.51) .650</td></tr><tr><td>-58</td><td>(17.91) .705</td></tr><tr><td>-59</td><td>(19.18) .755</td></tr><tr><td>-60</td><td>(20.96) .825</td></tr><tr><td>-61</td><td>(26.67) 1.050</td></tr></table>							OAL		LEAD STYLE	THROUGH-HOLE	-01	(11.43) .450	-51	(10.41) .410	-52	(10.80) .425	-53	(12.83) .505	-54	(14.10) .555	-55	(15.49) .610	-56	(15.88) .625	-57	(16.51) .650	-58	(17.91) .705	-59	(19.18) .755	-60	(20.96) .825	-61	(26.67) 1.050
OAL																																		
LEAD STYLE	THROUGH-HOLE																																	
-01	(11.43) .450																																	
-51	(10.41) .410																																	
-52	(10.80) .425																																	
-53	(12.83) .505																																	
-54	(14.10) .555																																	
-55	(15.49) .610																																	
-56	(15.88) .625																																	
-57	(16.51) .650																																	
-58	(17.91) .705																																	
-59	(19.18) .755																																	
-60	(20.96) .825																																	
-61	(26.67) 1.050																																	

HDWM	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	OTHER OPTION																																										
FACE MOUNT	01 thru 50	Specify LEAD STYLE from chart	-L = 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail	-S = Single Row	- "XXX" = Stacker Height Example: -250 = (6.35 mm) .250"	- "XXX" = Polarized Position (Specify position of omitted pin)																																										
			-G = 10 μ" (0.25 μm) Gold on contact, Gold flash on tail	-D = Double Row		- SM = Surface Mount (02 thru 40 positions only)																																										
																																																
																																																
<table><tr><th colspan="3">OAL</th></tr><tr><th>LEAD STYLE</th><th>THROUGH-HOLE</th><th>SURFACE MOUNT</th></tr><tr><td>-01</td><td>(11.43) .450</td><td>(8.38) .330</td></tr><tr><td>-51</td><td>(10.41) .410</td><td>—</td></tr><tr><td>-52</td><td>(10.80) .425</td><td>—</td></tr><tr><td>-53</td><td>(12.83) .505</td><td>(9.78) .385</td></tr><tr><td>-54</td><td>(14.10) .555</td><td>(11.05) .435</td></tr><tr><td>-55</td><td>(15.49) .610</td><td>(12.45) .490</td></tr><tr><td>-56</td><td>(15.88) .625</td><td>(12.83) .505</td></tr><tr><td>-57</td><td>(16.51) .650</td><td>(13.46) .530</td></tr><tr><td>-58</td><td>(17.91) .705</td><td>(14.86) .585</td></tr><tr><td>-59</td><td>(19.18) .755</td><td>(15.62) .615</td></tr><tr><td>-60</td><td>(20.96) .825</td><td>—</td></tr><tr><td>-61</td><td>(26.67) 1.050</td><td>—</td></tr></table>							OAL			LEAD STYLE	THROUGH-HOLE	SURFACE MOUNT	-01	(11.43) .450	(8.38) .330	-51	(10.41) .410	—	-52	(10.80) .425	—	-53	(12.83) .505	(9.78) .385	-54	(14.10) .555	(11.05) .435	-55	(15.49) .610	(12.45) .490	-56	(15.88) .625	(12.83) .505	-57	(16.51) .650	(13.46) .530	-58	(17.91) .705	(14.86) .585	-59	(19.18) .755	(15.62) .615	-60	(20.96) .825	—	-61	(26.67) 1.050	—
OAL																																																
LEAD STYLE	THROUGH-HOLE	SURFACE MOUNT																																														
-01	(11.43) .450	(8.38) .330																																														
-51	(10.41) .410	—																																														
-52	(10.80) .425	—																																														
-53	(12.83) .505	(9.78) .385																																														
-54	(14.10) .555	(11.05) .435																																														
-55	(15.49) .610	(12.45) .490																																														
-56	(15.88) .625	(12.83) .505																																														
-57	(16.51) .650	(13.46) .530																																														
-58	(17.91) .705	(14.86) .585																																														
-59	(19.18) .755	(15.62) .615																																														
-60	(20.96) .825	—																																														
-61	(26.67) 1.050	—																																														

Notes:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

This Series is non-standard, non-returnable.

samtec.com?DWM or samtec.com?HDWM

F-226

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.