


## CONDUCTIVE BOXES + SMD-BOXES


- SMD COLLAPSIBLE BOXES
- SMD BOXES
- SMD CABINETS
- SMD SPOOL STANDS
- CONDUCTIVE CABINETS
- CONDUCTIVE BOXES
- CONDUCTIVE CASES




SMD boxes – non-conductive

|            |                                                                                     | Art. No.                   | Lid                                                                                   | Bottom part                                                                           | Inside dimensions | Characteristics |
|------------|-------------------------------------------------------------------------------------|----------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------|-----------------|
| <b>N 1</b> |    | <b>SMD-Box N 1-2-3-2-1</b> | transparent                                                                           |    | 16 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 1-2-3-4-1</b> | transparent                                                                           |    | 16 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 1-2-3-6-1</b> | transparent                                                                           |    | 16 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 1-2-3-7-1</b> | transparent                                                                           |    | 16 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 1-2-3-8-1</b> | transparent                                                                           |    | 16 x 12 x 15      | non-conductive  |
|            |    | <b>SMD-Box N 1-2-2-2-2</b> |    |    | 16 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 1-2-2-4-4</b> |    |    | 16 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 1-2-2-6-6</b> |    |    | 16 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 1-2-2-7-7</b> |    |    | 16 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 1-2-2-8-8</b> |    |    | 16 x 12 x 15      | non-conductive  |
| <b>N 2</b> |    | <b>SMD-Box N 2-2-3-2-1</b> | transparent                                                                           |    | 37 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 2-2-3-4-1</b> | transparent                                                                           |    | 37 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 2-2-3-6-1</b> | transparent                                                                           |    | 37 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 2-2-3-7-1</b> | transparent                                                                           |    | 37 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 2-2-3-8-1</b> | transparent                                                                           |    | 37 x 12 x 15      | non-conductive  |
|            |    | <b>SMD-Box N 2-2-2-2-2</b> |    |    | 37 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 2-2-2-4-4</b> |    |    | 37 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 2-2-2-6-6</b> |    |    | 37 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 2-2-2-7-7</b> |   |   | 37 x 12 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 2-2-2-8-8</b> |  |  | 37 x 12 x 15      | non-conductive  |
| <b>N 3</b> |  | <b>SMD-Box N 3-2-3-2-1</b> | transparent                                                                           |  | 41 x 37 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 3-2-3-4-1</b> | transparent                                                                           |  | 41 x 37 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 3-2-3-6-1</b> | transparent                                                                           |  | 41 x 37 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 3-2-3-7-1</b> | transparent                                                                           |  | 41 x 37 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 3-2-3-8-1</b> | transparent                                                                           |  | 41 x 37 x 15      | non-conductive  |
|            |  | <b>SMD-Box N 3-2-2-2-2</b> |  |  | 41 x 37 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 3-2-2-4-4</b> |  |  | 41 x 37 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 3-2-2-6-6</b> |  |  | 41 x 37 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 3-2-2-7-7</b> |  |  | 41 x 37 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 3-2-2-8-8</b> |  |  | 41 x 37 x 15      | non-conductive  |
| <b>N 4</b> |  | <b>SMD-Box N 4-2-3-2-1</b> | transparent                                                                           |  | 68 x 57 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 4-2-3-4-1</b> | transparent                                                                           |  | 68 x 57 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 4-2-3-6-1</b> | transparent                                                                           |  | 68 x 57 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 4-2-3-7-1</b> | transparent                                                                           |  | 68 x 57 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 4-2-3-8-1</b> | transparent                                                                           |  | 68 x 57 x 15      | non-conductive  |
|            |  | <b>SMD-Box N 4-2-2-2-2</b> |  |  | 68 x 57 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 4-2-2-4-4</b> |  |  | 68 x 57 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 4-2-2-6-6</b> |  |  | 68 x 57 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 4-2-2-7-7</b> |  |  | 68 x 57 x 15      | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 4-2-2-8-8</b> |  |  | 68 x 57 x 15      | non-conductive  |
| <b>N 5</b> |  | <b>SMD-Box N 5-2-3-2-1</b> | transparent                                                                           |  | 180 x 68 x 15     | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 5-2-3-4-1</b> | transparent                                                                           |  | 180 x 68 x 15     | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 5-2-3-6-1</b> | transparent                                                                           |  | 180 x 68 x 15     | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 5-2-3-7-1</b> | transparent                                                                           |  | 180 x 68 x 15     | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 5-2-3-8-1</b> | transparent                                                                           |  | 180 x 68 x 15     | non-conductive  |
|            |  | <b>SMD-Box N 5-2-2-2-2</b> |  |  | 180 x 68 x 15     | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 5-2-2-4-4</b> |  |  | 180 x 68 x 15     | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 5-2-2-6-6</b> |  |  | 180 x 68 x 15     | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 5-2-2-7-7</b> |  |  | 180 x 68 x 15     | non-conductive  |
|            |                                                                                     | <b>SMD-Box N 5-2-2-8-8</b> |  |  | 180 x 68 x 15     | non-conductive  |

## SMD boxes – conductive – dissipative


|     |                                                                                     | Art. No.                  | Lid          | Bottom part | Inside dimensions | Characteristics                                                                                                                                                             |
|-----|-------------------------------------------------------------------------------------|---------------------------|--------------|-------------|-------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| N 1 |    | SMD-Box N 1-6-6-10-10     | ●            | ●           | 16 x 12 x 15      |                                                                                          |
|     |                                                                                     | SMD-Box N 1-6-6-1 LS      | transparent* | ●           | 16 x 12 x 15      |                                                                                          |
|     |                                                                                     |                           |              |             |                   |                                                                                                                                                                             |
|     |    | SMD-Box N 1-11-6-4-1 LS   | transparent* | ●           | 16 x 12 x 15      |       |
|     |                                                                                     | SMD-Box N 1-11-6-6-1 LS   | transparent* | ●           | 16 x 12 x 15      |       |
|     |                                                                                     | SMD-Box N 1-11-6-8-1 LS   | transparent* | ●           | 16 x 12 x 15      |       |
|     |    | Diss-SMD-Box N1-11-11-4-4 | ●            | ●           | 16 x 12 x 15      |                                                                                          |
|     |                                                                                     | Diss-SMD-Box N1-11-11-6-6 | ●            | ●           | 16 x 12 x 15      |                                                                                          |
|     |                                                                                     | Diss-SMD-Box N1-11-11-8-8 | ●            | ●           | 16 x 12 x 15      |                                                                                          |
| N 2 |    | SMD-Box N 2-6-6-10-10     | ●            | ●           | 37 x 12 x 15      |                                                                                          |
|     |                                                                                     | SMD-Box N 2-6-6-10-1 LS   | transparent* | ●           | 37 x 12 x 15      |                                                                                          |
|     |                                                                                     |                           |              |             |                   |                                                                                                                                                                             |
|     |    | SMD-Box N 2-11-6-4-1 LS   | transparent* | ●           | 37 x 12 x 15      |       |
|     |                                                                                     | SMD-Box N 2-11-6-6-1 LS   | transparent* | ●           | 37 x 12 x 15      |       |
|     |                                                                                     | SMD-Box N 2-11-6-8-1 LS   | transparent* | ●           | 37 x 12 x 15      |       |
|     |    | Diss-SMD-Box N2-11-11-4-4 | ●            | ●           | 37 x 12 x 15      |                                                                                          |
|     |                                                                                     | Diss-SMD-Box N2-11-11-6-6 | ●            | ●           | 37 x 12 x 15      |                                                                                          |
|     |                                                                                     | Diss-SMD-Box N2-11-11-8-8 | ●            | ●           | 37 x 12 x 15      |                                                                                          |
| N 3 |  | SMD-Box N 3-6-6-10-10     | ●            | ●           | 41 x 37 x 15      |                                                                                        |
|     |                                                                                     | SMD-Box N 3-6-6-10-1 LS   | transparent* | ●           | 41 x 37 x 15      |                                                                                        |
|     |                                                                                     |                           |              |             |                   |                                                                                                                                                                             |
|     |  | SMD-Box N 3-11-6-4-1 LS   | transparent* | ●           | 41 x 37 x 15      |   |
|     |                                                                                     | SMD-Box N 3-11-6-6-1 LS   | transparent* | ●           | 41 x 37 x 15      |   |
|     |                                                                                     | SMD-Box N 3-11-6-8-1 LS   | transparent* | ●           | 41 x 37 x 15      |   |
|     |  | Diss-SMD-Box N3-11-11-4-4 | ●            | ●           | 41 x 37 x 15      |                                                                                        |
|     |                                                                                     | Diss-SMD-Box N3-11-11-6-6 | ●            | ●           | 41 x 37 x 15      |                                                                                        |
|     |                                                                                     | Diss-SMD-Box N3-11-11-8-8 | ●            | ●           | 41 x 37 x 15      |                                                                                        |
| N 4 |  | SMD-Box N 4-6-6-10-10     | ●            | ●           | 68 x 57 x 15      |                                                                                        |
|     |                                                                                     | SMD-Box N 4-6-6-10-1 LS   | transparent* | ●           | 68 x 57 x 15      |                                                                                        |
|     |                                                                                     |                           |              |             |                   |                                                                                                                                                                             |
|     |  | SMD-Box N 4-11-6-4-1 LS   | transparent* | ●           | 68 x 57 x 15      |   |
|     |                                                                                     | SMD-Box N 4-11-6-6-1 LS   | transparent* | ●           | 68 x 57 x 15      |   |
|     |                                                                                     | SMD-Box N 4-11-6-8-1 LS   | transparent* | ●           | 68 x 57 x 15      |   |
|     |  | Diss-SMD-Box N4-11-11-4-4 | ●            | ●           | 68 x 57 x 15      |                                                                                        |
|     |                                                                                     | Diss-SMD-Box N4-11-11-6-6 | ●            | ●           | 68 x 57 x 15      |                                                                                        |
|     |                                                                                     | Diss-SMD-Box N4-11-11-8-8 | ●            | ●           | 68 x 57 x 15      |                                                                                        |
| N 5 |  |                           |              |             |                   |                                                                                                                                                                             |
|     |                                                                                     | SMD-Box N 5-6-6-10-10     | ●            | ●           | 180 x 68 x 15     |                                                                                        |
|     |                                                                                     | SMD-Box N 5-6-6-10-1 LS   | transparent* | ●           | 180 x 68 x 15     |                                                                                        |
|     |                                                                                     |                           |              |             |                   |                                                                                                                                                                             |
|     |                                                                                     |                           |              |             |                   |                                                                                                                                                                             |

## SMD CABINETS WITH CHIP CONTAINERS



Art. No. **144 SMD-Boxen N1**  
fitting exactly into **A 1-4/16-6-10**

Inside Dimensions 340 x 250 x 22



Art. No. SMD cabinet **A 1-4 Bunt 144**

Cabinet with 3 drawers incl.


3 x 144 = 432 pcs



Art. No. SMD cabinet **A 1-4 ESD 144**

Cabinet with 3 drawers incl.

3 x 144 = 432 pcs



Art. No. **72 SMD-Boxen N2**  
fitting exactly into **A 1-4/16-6-10**


Inside Dimensions 340 x 250 x 22



Art. No. SMD cabinet **A 1-4 Bunt 72**

Cabinet with 3 drawers incl.


3 x 72 = 216 pcs



Art. No. SMD cabinet **A 1-4 ESD 72**


Cabinet with 3 drawers incl.

3 x 72 = 216 pcs



Art. No. **36 SMD-Boxen N3**  
fitting exactly into **A 1-4/16-6-10**


Inside Dimensions 340 x 250 x 22



Art. No. SMD cabinet **A 1-4 Bunt 36**

Cabinet with 3 drawers incl.


3 x 36 = 108 pcs



Art. No. SMD cabinet **A 1-4 ESD 36**


Cabinet with 3 drawers incl.

3 x 36 = 108 pcs



Art. No. **16 SMD-Boxen N4**  
fitting exactly into **A 1-4/16-6-10**


Inside Dimensions 340 x 250 x 22



Art. No. SMD cabinet **A 1-4 Bunt 16**

Cabinet with 3 drawers incl.


3 x 16 = 48 pcs




Art. No. SMD cabinet **A 1-4 ESD 16**

Cabinet with 3 drawers incl.


3 x 16 = 48 pcs




Art. No. **A 1-4/4 Bunt MIX**  
 Multicoloured cabinet (not ESD) with 4 drawers  
 various SMD collapsible boxes per drawer, sizes N1-N4  
 (cf. page 60)



Art. No. **A 1-4/4 ESD MIX**  
 Conductive cabinet with 4 drawers  
 various SMD collapsible boxes per drawer, sizes N1-N4  
 (cf. page 75)



Art. No. **144 SMD-Boxen N1** **72 SMD-Boxen N2**



**36 SMD-Boxen N3** **16 SMD-Boxen N4**



Art. No. **SMD-Rollboy Single N1**  
 Art. No. **SMD-Rollboy Single N2**  
 Art. No. **SMD-Rollboy Single N3**  
 Art. No. **SMD-Rollboy Single N4**  
 Art. No. **SMD-Rollboy Single Mix** (on request)



Art. No. **SMD-EGB-Rollboy Single N1**  
 Art. No. **SMD-EGB-Rollboy Single N2**  
 Art. No. **SMD-EGB-Rollboy Single N3**  
 Art. No. **SMD-EGB-Rollboy Single N4**  
 Art. No. **SMD-EGB-Rollboy Single Mix** (on request)

## SMD SPOOL RACK



Art. No. **V 11-4** (not conductive)  
with 25 variable partitions and  
continuous identification rail  
(for spools up to 250 mm Ø)

Basic dimensions 450 x 240

Colours



Art. No. **V 11-7**  
with 25 variable partitions and  
continuous identification rail  
(for spools up to 330 mm Ø)

Basic dimensions 455 x 315

Colours



Art. No. **V 11-14**  
with 10 variable partitions and  
continuous identification rail  
(for spools up to 380 mm Ø)

Basic dimensions 455 x 360

Colours



Art. No. **V 11-4-6-10** (conductive)  
with 25 variable partitions and  
continuous identification rail  
(for spools up to 250 mm Ø)

Basic dimensions 450 x 240

Colours



Art. No. **V 11-7-6-10** (conductive)  
with 25 variable partitions and  
continuous identification rail  
(for spools up to 330 mm Ø)

Basic dimensions 455 x 315

Colours



Art. No. **V 11-14-6-10** (conductive)  
with 10 variable partitions and  
continuous identification rail  
(for spools up to 380 mm Ø)

Basic dimensions 455 x 360

Colours



Art. No. **V 11-8-6-10** (conductive)  
Spool stands for horizontal storage  
of SMD spools up to 180 mm Ø  
(First in/first out)

Outside dimensions 186 x 173 x 210

Inside dimensions 182 x 169 x 190



Art. No. **V 11-9-6-10** (conductive)  
Spool stands for horizontal storage  
of SMD spools up to 330 mm Ø  
(First in/first out)

Outside dimensions 339 x 319 x 210

Inside dimensions 335 x 315 x 190



Art. No. **V 11-15-6-10** (conductive)  
Spool stands for horizontal storage  
of SMD spools up to 380 mm Ø  
(First in/first out)

Outside dimensions 380 x 370 x 250

Inside dimensions 375 x 365 x 230

## SMD CABINETS WITH ROUND BOXES FOR CHIPS




Art. No. **V 11-5**  
SMD packing set with 32 cavities  
18 Ø x 12 mm with individual  
top cover (non-conductive)



Art. No. **A 1-3 SMD**  
for 6 pcs **V 11-5** (without top cover)


Art. No. **A 1-3 SMD NORMAL**  
non conductive




Art. No. SMD cabinet **A 1-1 SMD** Liastat  
6-fold cabinets with inserts and  
6 x 42 round boxes **V 1-12-6-10**  
27 Ø x 13




Art. No. SMD cabinet **A 1-1 SMD white**



Art. No. SMD cabinet **A 1-1 SMD yellow**



Art. No. SMD cabinet **A 1-1 SMD green**




Art. No. SMD cabinet **A 1-1 SMD red**



Art. No. SMD cabinet **A 1-1 SMD blue**



Art. No. SMD cabinet **A 1-1 SMD/5 bunt**



Art. No. **V 11-3**  
SMD packing set with 60 boxes  
and foam grid




Art. No. **V 11-1**  
SMD packing set with 130 boxes  
and foam grid

Art. No. **V 4-1**  
6 x 6 x 19 mm  
(non conductive)

Art. No. **V 4-1**  
6 x 6 x 19 mm  
(non conductive)



## SERIES A 1-1 DRAWER FORMAT

Art. No. **A 1-1 S** 6-fold Liastat

Drawer 261 x 238 x 20 (inside)


Characteristics conductive

Art. No. **SK 730-6-10**

Drawer 261 x 238 x 20 (inside)

Characteristics conductive


Note Please order inserts and identification labels separately

Art. No. **A 1-1 SMD** complete with round boxes

Drawer 261 x 238 x 20 (inside)


Characteristics conductive

Note Please order identification labels separately, further designs (clear boxes with conducting layer) see page 73

Art. No. **A 1-1/16-6-10** as stackable box

Inside dimensions 261 x 238 x 20

Characteristics conductive

Art. No. **A 1-1/16-6-10** bottom partArt. No. **+ A 1-1/4-6-10** lid  
as flat box

Inside dimensions 261 x 238 x 20

Characteristics conductive


Art. No. **A 1-1/16-6-10** bottom partArt. No. **+ A 1-1/4-6-10** lidArt. No. **+ TE ... W-6-10** insert

see below as assortment case


Inside dimensions 261 x 238 x 20

Characteristics conductive

## VACUM FORMED STANDARD DRAWER INSERTS Conductive version Liastat \*) black, inside dimension of compartments, inside depth 16 mm



## SERIES A 1-1 DRAWER FORMAT




|                 |                                                           |
|-----------------|-----------------------------------------------------------|
| Art. No.        | <b>A 1-4</b> 9-fold Liastat                               |
| Drawer          | 340 x 250 x 22 (inside)                                   |
| Characteristics | conductive                                                |
| Note            | Please order inserts and identification labels separately |




|                 |                                                                          |
|-----------------|--------------------------------------------------------------------------|
| Art. No.        | <b>SK 734-6-10</b>                                                       |
| Drawer          | 340 x 250 x 22 (inside)                                                  |
| Characteristics | conductive                                                               |
| Note            | Please order inserts and identification labels separately, lateral hinge |



|                 |                                                                                                     |
|-----------------|-----------------------------------------------------------------------------------------------------|
| Art. No.        | <b>A 1-4 Liacarry</b>                                                                               |
| Drawer          | 340 x 250 x 22 (inside)                                                                             |
| Characteristics | conductive                                                                                          |
| Note            | Inserts, identification labels and declaration form pockets to be ordered separately, lateral hinge |



|                   |                             |
|-------------------|-----------------------------|
| Art. No.          | <b>Drawer A 1-4/16-6-10</b> |
|                   | as stackable box            |
| Inside dimensions | 340 x 250 x 22              |
| Characteristics   | conductive                  |
| Note              |                             |




|                   |                                               |
|-------------------|-----------------------------------------------|
| Art. No.          | <b>A 1-4/6 ESD insert</b> spare parts cabinet |
| Inside dimensions | 340 x 250 x 22                                |
| Characteristics   | conductive /antistatic                        |
|                   | 3 drawers, insert with 42 subdivisions each   |
|                   | 2 drawers, insert with 25 subdivisions each   |
|                   | 1 drawer, insert with 16 subdivisions each    |




|                   |                                  |
|-------------------|----------------------------------|
| Art. No.          | <b>A 1-4/16-6-10</b> bottom part |
| Art. No.          | <b>+ A 1-2/4-6-10</b> lid        |
| Art. No.          | <b>+ TE ... 4-6-10</b> insert    |
|                   | see below as assortment cases    |
| Inside dimensions | 340 x 250 x 22                   |
| Characteristics   | conductive                       |

## VACUM FORMED STANDARD DRAWER INSERTS Inside dimensionsof compartments, conductive type Liastat \*) black



## SERIES A 1-2 DRAWER FORMAT

Art. No. **A 1-2 S 6-fold Liastat**

Drawer 340 x 250 x 40 (inside)

Characteristics conductive


Note Please order inserts and identification labels separately

Art. No. **SK 731-6-10**

Drawer 340 x 250 x 40 (inside)

Characteristics conductive

Note Please order inserts and identification labels separately, lateral hinge

Art. No. **A 1-2 Liacarry**




Drawer 340 x 250 x 40 (inside)

Characteristics conductive


Note Inserts, identification labels and declaration form pockets to be ordered separately, lateral hinge

## DETACHABLE DRAWER INSERTS, conductive type Liastat \*) black, standard type grey and white

|         | 24                  | 12                  | 6                  |
|---------|---------------------|---------------------|--------------------|
| grey    | <b>SE 24-2-2-9</b>  | <b>SE 12-2-2-9</b>  | <b>SE 6-2-2-9</b>  |
| white   | <b>SE 24-2-2-2</b>  | <b>SE 12-2-2-2</b>  | <b>SE 6-2-2-2</b>  |
| EGB     | <b>SE 24-2-6-10</b> | <b>SE 12-2-6-10</b> | <b>SE 6-2-6-10</b> |
| outside | 62 x 56 x 33 mm     | 112 x 62 x 33 mm    | 124 x 112 x 33 mm  |
| inside  | 59 x 53 x 31 mm     | 109 x 59 x 31 mm    | 121 x 109 x 31 mm  |

Special size **V 6-28/2**; 110 x 42 x 35 mm outside 18 pcs per box

Drawers **A 1-2/16-6-10** with lid, **A 1-2/4-6-10** as flat box or with inserts as assortment boxArt. No. **A 1-2/ESD selective cups Service cabinet**









with 2 drawers with 24, 2 drawers with

12 and 2 drawers with 6 selective cups each


Inside dimensions 340 x 250 x 40

Characteristics conductive /antistatic

## VACUM FORMED STANDARD DRAWER INSERTS Conductive version Liastat \*) black, inside dimension of compartments, inside depth 16 mm

|                                                                                     |                                                                                                                |                                                                                                                                                       |                                                                                                                |                                                                                                                                                         |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|
|  |  <p><b>TE 3 S-6-10</b></p>  |  <p><b>TE 6 S-6-10</b></p>                                         |  <p><b>TE 9 S-6-10</b></p>  |  <p><b>TE 12 S-6-10</b></p>                                        |
|                                                                                     |  <p><b>TE 16 S-6-10</b></p> |  <p><b>TE 22 S-6-10</b><br/>Compartments rounded at the bottom</p> |  <p><b>TE 25 S-6-10</b></p> |  <p><b>TE 30 S-6-10</b><br/>Compartments rounded at the bottom</p> |


## SERIES A 1-60 DRAWER FORMAT



|                 |                                                           |
|-----------------|-----------------------------------------------------------|
| Art. No.        | <b>A 1-60 4-fold Liastat</b>                              |
| Drawer          | 340 x 250 x 62 ( inside)                                  |
| Characteristics | conductive                                                |
| Note            | Please order inserts and identification labels separately |



|                 |                                                                          |
|-----------------|--------------------------------------------------------------------------|
| Art. No.        | <b>SK 732-6-10</b>                                                       |
| Drawer          | 340 x 250 x 62 ( inside)                                                 |
| Characteristics | conductive                                                               |
| Note            | Please order inserts and identification labels separately, lateral hinge |



|                 |                                                                                                     |
|-----------------|-----------------------------------------------------------------------------------------------------|
| Art. No.        | <b>A 1-60 Liacarry</b>                                                                              |
| Drawer          | 340 x 250 x 62 (inside)                                                                             |
| Characteristics | conductive                                                                                          |
| Note            | Inserts, identification labels and declaration form pockets to be ordered separately, lateral hinge |

## LOOSE DRAWER INSERTS CONDUCTIVE, standard version, white

|            | 58                   | 30                   | 15                   | 6                   |
|------------|----------------------|----------------------|----------------------|---------------------|
| white      | <b>SE 58-60-1-2</b>  | <b>SE 30-60-1-2</b>  | <b>SE 15-60-1-2</b>  | <b>SE 6-60-1-2</b>  |
| conductive | <b>SE 58-60-6-10</b> | <b>SE 30-60-6-10</b> | <b>SE 15-60-6-10</b> | <b>SE 6-60-6-10</b> |
| outside    | 59 x 23 x 60 mm      | 56 x 50 x 54 mm      | 113 x 50 x 54 mm     | 125 x 113 x 54 mm   |
| inside     | 54 x 18 x 58 mm      | 53 x 47 x 52 mm      | 109 x 47 x 52 mm     | 121 x 109 x 52 mm   |

## VACUM FORMED STANDARD DRAWER INSERTS Conductive version Liastat \*) black, inside height 53 mm

|  |                            |                            |                            |                            |                            |
|--|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|
|  | <p><b>TE 4-60-6-10</b></p> | <p><b>TE 6-60-6-10</b></p> | <p><b>TE 9-60-6-10</b></p> | <p><b>TE 12 K 6-10</b></p> | <p><b>TE 24 K 6-10</b></p> |
|--|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|

Dimensions in mm.

Dimensions subject to errors and corrections!

\* Material Liastat = conductive/antistatic material, black. Surface resistance according to fabrication criteria  $10^5$ – $10^8$  Ohm.

## EGB-ROLLBOYS + EGB-DRAWER CABINETS



Art. No. **EGB-Rollboy Single 4**  
with 18 drawers  
(cf. inside dimensions drawers page 75)  
Outside dimensions 318 x 365 x 806  
Note Please order inserts separately  
conductive pad on request



Art. No. **EGB-Rollboy Single 1**  
with 12 drawers  
(cf. inside dimensions drawers page 78)  
Outside dimensions 318 x 365 x 806  
Note Please order inserts separately  
conductive pad on request



Art. No. **EGB-Rollboy Single 2**  
with 8 drawers  
(cf. inside dimensions drawers page 79)  
Outside dimensions 318 x 365 x 806  
Note Please order inserts separately  
conductive pad on request



Art. No. **Spiral cable** extremely flexible  
2.4 m x 2 x 1 MOhm safety resistance  
Earth connection: 10 mm push-button



Art. No. **Wrist band** adjustable, flexible,  
interlaced, silver-plated synthetic fabrics,  
antiallergenic



Art. No. **EGB-Rollboy 4 with 36 drawers**  
with pad 585 x 365  
(cf. inside dimensions drawers page 75)  
Outside dimensions 585 x 365 x 806  
Note Please order inserts separately




Art. No. **EGB-Rollboy 1 with 24 drawers**  
with pad 585 x 365  
(cf. inside dimensions drawers page 78)  
Outside dimensions 585 x 365 x 806  
Note Please order inserts separately



Art. No. **EGB-Rollboy 2 with 16 drawers**  
with pad 585 x 365  
(cf. inside dimensions drawers page 79)  
Outside dimensions 585 x 365 x 806  
Note Please order inserts separately

## CONDUCTIVE BOXES + SUBDIVISIONS



Printed boards packings


|          |                 |                       |
|----------|-----------------|-----------------------|
| Art. No. | <b>V 11-20*</b> | 175 x 100 x 26 inside |
| Art. No. | <b>V 11-21*</b> | 175 x 100 x 47 inside |
| Art. No. | <b>V 11-22*</b> | 175 x 100 x 67 inside |
| Art. No. | <b>V 11-23*</b> | 220 x 100 x 26 inside |
| Art. No. | <b>V 11-24*</b> | 220 x 100 x 47 inside |
| Art. No. | <b>V 11-25*</b> | 220 x 100 x 67 inside |

Characteristics non-conductive, white bottom part, crystal clear lid

\*) conductive version i.e. bottom part conductive/antistatic, lid conductive, black, vapour-deposited

Order instructions e.g. **V 11 - 20 - 6 - 7 - 10 - 1**

conductive version



Art. No. **ET-1-6-10** Insert tray for Euro boxes

**EK 1-2/LWB** (400 x 300) stackable,

Inside dimensions 310 x 250 x 20



Art. No. **ET-3-6-10**

Insert tray for Euro boxes

**EK 3-4/LWB** stackable,

Inside dimensions 520 x 345 x 60

| EURO boxes (conductive) |                 |                 |            |                 |                 |            |
|-------------------------|-----------------|-----------------|------------|-----------------|-----------------|------------|
| Art. No.                | EK 1-6-10       | EK 2-6-10       | D 1-2-6-10 | EK 3-6-10       | EK 4-6-10       | D 3-4-6-10 |
| Outside dimensions      | 400 x 300 x 120 | 400 x 300 x 220 | Top cover  | 600 x 400 x 120 | 600 x 400 x 270 | Top cover  |



Pallets for small printed boards

Art. No. **TL 1** for 16 printed boards 105 x 50


Dimensions 350 x 225 x 30

Art. No. **TL 2** for 15 printed boards 100 x 40

Dimensions 350 x 250 x 30

Art. No. **TL 3** for 45 printed boards 50 x 30

Dimensions 350 x 250 x 23



Printed boards L-profile

Art. No. **LP 1**

Dimensions 200 x 274 x 93

Art. No. **LP 2**

Dimensions 350 x 263 x 125

25 slots for printed boards

Transport/storage Service workshop

Dimensions in mm.

Dimensions subject to errors and corrections!

## CONDUCTIVE BOXES + SUBDIVISIONS

Art. No. **A 4-1-6-10**

Base area 175 x 100

Top edge 250 x 125

Height inside 34 mm

Colours ●

Art. No. **A 4-2-6-10**

Base area 190 x 120

Height inside 50 mm

Colours ●

Note can be stacked nested, when turned even with content

Art. No. **A 4-3-6-10**

Base area 210 x 150

Top edge 260 x 200

Height inside 40 mm

Colours ●

Art. No. **A 4-4 N-6-10**

Outside dimensions 260 x 165

Height outside 45 mm

Colours ●

Art. No. **A 4-16-6-10**

Outside dimensions 240 x 210 x 82

Inside dimensions 208 x 178 x 79

Colours ●

Art. No. **EGB Papierkorb 14 l**


Outside dimensions 300 Ø x 320

Inside dimensions 255 Ø x 310


Colours ●

Note Volume approx. 14 l, conductive

Polypropylene with EGB warning symbol



ESD boxes (conductive/antistatic)

Art. No. **A 3-1/2-6-10** 282 x 130 x 70 insideArt. No. **A 3-1/4-6-10** Top coverArt. No. **A 3-1/11** RackArt. No. **A 3-1/10-6-10** Cross partitions optional


ESD boxes (conductive/antistatic)

Art. No. **A 3-3/2-6-10** 282 x 130 x 90 insideArt. No. **A 3-1/4-6-10** Top coverArt. No. **A 3-1/11** RackArt. No. **A 3-1/10-6-10** Cross partitions optional


## EGB PACKINGS FOR ELECTRONIC PARTS (LIASTAT\*)



|                        |                         |                         |                         |                         |
|------------------------|-------------------------|-------------------------|-------------------------|-------------------------|
| Art. No.               | <b>V 3-12-6-6-10-10</b> | <b>V 3-18-6-6-10-10</b> | <b>V 3-30-6-6-10-10</b> | <b>V 3-40-6-6-10-10</b> |
| Inside dimensions      | 50 x 30 x 16            | 57 x 36 x 17            | 73 x 42 x 17            | 80 x 50 x 27            |
| Art. No.               | <b>V 3-12/9-6-10</b>    | <b>V 3-18/9-6-10</b>    | <b>V 3-30/9-6-10</b>    | <b>V 3-40/9-6-10</b>    |
| Foam fit for insertion | 8 mm                    | 8 mm                    | 8 mm                    | 8 mm                    |
| Colours                | ●                       | ●                       | ●                       | ●                       |



|                    |                                                                                         |                                 |                                                                   |
|--------------------|-----------------------------------------------------------------------------------------|---------------------------------|-------------------------------------------------------------------|
| Art. No.           | <b>V 8-14 SCH + V-6-6-10-10</b>                                                         | <b>V 9-40 SCH + V-6-6-10-10</b> | <b>V 8-12 SCH + V-6-6-10-10</b>                                   |
| Outside dimensions | 295 x 175 x 20                                                                          | 295 x 175 x 20                  |                                                                   |
| Inside dimensions  | 292 x 160 x 16                                                                          | 73 x 42 x 17                    | 80 x 50 x 27                                                      |
| Colours            | ●                                                                                       | ●                               | ●                                                                 |
| Note               | various compartment inserts s. p. 29-30, conductive versions on request 54 compartments |                                 | various comp. inserts s. p. 28-29, conductive versions on request |



|                        |                        |                                                    |                         |
|------------------------|------------------------|----------------------------------------------------|-------------------------|
| Art. No.               | <b>V 8-8-6-6-10-10</b> | <b>V 8-9 SCH + V-6-6-10-10</b>                     | <b>V 8-15-6-6-10-10</b> |
| Inside dimensions      | 183 x 108 x 30         | 196 x 136 x 49 (Outside dimensions 203 x 152 x 53) | 220 x 130 x 35          |
| Art. No.               | <b>V 8-8/9-6-10</b>    |                                                    |                         |
| Foam fit for insertion | 8 mm                   |                                                    |                         |
| Colours                | ●                      | ●                                                  |                         |



|                            |                                                  |
|----------------------------|--------------------------------------------------|
| Stackable boxes, slip lid  |                                                  |
| EGB foam inlays on request |                                                  |
| Art. No.                   | <b>V 3-16-6-6-10-10</b> 55 x 55 x 25/16 inside   |
| Art. No.                   | <b>V 3-17-6-6-10-10</b> 55 x 55 x 35/26 inside   |
| Art. No.                   | <b>V 3-59-6-6-10-10</b> 115 x 55 x 35/26 inside  |
| Art. No.                   | <b>V 3-60-6-6-10-10</b> 115 x 55 x 55/46 inside  |
| Art. No.                   | <b>V 3-61-6-6-10-10</b> 115 x 115 x 55/46 inside |



|                            |                                             |
|----------------------------|---------------------------------------------|
| Stackable boxes, slip lid  |                                             |
| EGB foam inlays on request |                                             |
| Art. No.                   | <b>V 8-1-6-6-10-10</b> 75 x 50 x 33 inside  |
| Art. No.                   | <b>V 8-2-6-6-10-10</b> 75 x 50 x 45 inside  |
| Art. No.                   | <b>V 8-5-6-6-10-10</b> 106 x 75 x 46 inside |
| Art. No.                   | <b>V 8-7-6-6-10-10</b> 56 x 106 x 46 inside |



|                      |                                           |
|----------------------|-------------------------------------------|
| LiaStat hinged boxes |                                           |
| Art. No.             | <b>V 20-29-6-10</b> 130 x 80 x 14 inside  |
| Art. No.             | <b>V 20-30-6-10</b> 130 x 80 x 30 inside  |
| Art. No.             | <b>V 20-31-6-10</b> 130 x 80 x 50 inside  |
| Art. No.             | <b>V 20-32-6-10</b> 178 x 133 x 78 inside |
| Art. No.             | <b>V 20-33-6-10</b> 221 x 121 x 55 inside |

**CONDUCTIVE ROUND BOXES, COMPARTMENT BOXES, RECTANGULAR BOXES AND CASES** with foam inlays, soft or fit for insertion, on request



Liastat round boxes


Art. No. **V 1-11-6-6-10-10** 26 Ø x 17,5 slip lid

Art. No. **V 1-12-6-10** 26 Ø x 13 slip lid

Art. No. **V 2-101-6-6-10-10** 52 Ø x 40 screw cap

Art. No. **V 2-102-6-6-10-10** 52 Ø x 67 screw cap

Colours ●




Liastat compartment box

Art. No. **V 6-4-6-6-10-10**

6 comp. je 19 x 15 x 5 mm inside

Art. No. **V 6-5-6-6-10-10**

12 comp. je 25 x 10 x 10 mm inside



Liastat rectangular box

Art. No. **V 3-37-6-6-10-10**

Inside dimensions 75 x 75 x 27

Art. No. **V 3-54-6-6-10-10**

Inside dimensions 102 x 85 x 47

Note further sizes see pages 12-15 on request



| Art. No.          | <b>K 2005 ESD</b> | <b>K 2001 ESD</b> | <b>K 2004 ESD</b> | <b>K 2000 ESD</b> |
|-------------------|-------------------|-------------------|-------------------|-------------------|
| Inside dimensions | 170 x 130 x 37    | 240 x 170 x 42    | 270 x 185 x 76    | 340 x 250 x 53    |
| Colours           | ●                 | ●                 | ●                 | ●                 |
| Equipment         | ① ② ③ ④           | ① ② ③ ④ ⑤         | ① ② ③ ④           | ① ② ③ ④ ⑤ ⑥       |

**VACUUM FORMED INSERTS** Please specify art. no. separately!



Art. No. ① **Noppe**      ② **Raster**      ③ **TE 6**      ④ **TE 9**      ⑤ **TE 12**      ⑥ **TE 24**