


NAIS

**ANALOG OUTPUT TYPE
OPTICAL FIBER
PHOTOELECTRIC
SENSOR**

UZF36

NEW ANALOG OUTPUT TYPE FOR DIVERSE APPLICATIONS



Analog Voltage Output


Incorporated with the analog voltage output (1 to 5V).

Various Uses

The analog process with various kinds of fiber heads offers unique application solutions such as a height evaluation, or a gap detection.


Slim

Space-effective as it is only 10mm .394inch thick.



Automatic Crosstalk Prevention Function

Two sets of fibers can be mounted close together or face to face.



Saturation Indicator

Saturation indicator lights up when the output reaches 5V, thereby its sensitivity is easily adjusted without using a tester.


The incident beam indicator brightens up in proportion to the amount of incident beam (output voltage).



APPLICATIONS


Comparing traveling objects in height

With the array fiber, columns are classified in height.




Detecting gap to boards

No sensitivity setting is required even as products are changed over because of the differential sensing.




Detecting irrelevant products

Extraneous products are sorted out that differ from normal products in reflection ratio.




Ascertaining the number of translucent films

The number of translucent films overlaid is inspected by beam penetration.




Sensing turbidity of liquid

The turbidness of liquid inside a clear-wall tank is analogically observed.




Measuring inner diameter of rings

Rings are classified according to inner diameter.













ORDER GUIDE

Amplifier

Appearance	Model No.	Supply voltage	Analog output
	UZF36	12 to 24V DC $\pm$ 10%	Analog voltage • Voltage output: 1 to 5V

Fibers

Type	Shape of sensing probe (mm inch)	Sensing range (*1)	Features	Fiber optic cable length	Model No.
Thru-beam	Long sensing range	 160mm 6.299inch	• Sensing range is about double of that of conventional mode	Free Cut 2m 6.562ft	UZFTB8
	Standard	 Lens applicable	• Free cuttable type	Free Cut 2m 6.562ft	UZFTF8
		 With sleeve $\phi 1.48 \phi .058$			UZFTF89 With sleeve 90mm 3.543inch
		 $\phi 2.5 \phi .098$			UZFTF84 With sleeve 40mm 1.575inch
	Small diameter	 Lens applicable	• Same sensing range as the standard with a smaller sensing probe	Free Cut 2m 6.562ft	UZFTT8
		 Lens applicable	• Suitable for sensing in the intricate apparatus • Free cuttable type	Free Cut 2m 6.562ft	UZFTF4
		 With sleeve $\phi 0.88 \phi .035$			UZFTF49 With sleeve 90mm 3.543inch
	Small diameter	 Small diameter $\phi 1.5 \phi .059$			UZFTF44 With sleeve 40mm 1.575inch
		 $\phi 2.5 \phi .098$			UZFTS4
	Long sensing range with lenses	 $\phi 2.5 \phi .098$	• A long sensing range is achieved with a very small sensing probe $\phi 2.5\text{mm } \phi .098\text{inch}$	Free Cut 2m 6.562ft	UZFTL8
Reflective	Array	 Top sensing $\phi 15 \phi .591$	• Arrayed beam does not miss by detecting object regardless of its position	Free Cut 2m 6.562ft	UZFTA8
		 Side sensing $\phi 15 \phi .591$			UZFTA8E
		 $\phi 2.5 \phi .098$			
	Standard	 Coaxial	• Long sensing range	Free Cut 2m 6.562ft	UZFR8B
		 With sleeve $\phi 2.5 \phi .098$	• Free cuttable type	Free Cut 2m 6.562ft	UZFRF8
		 $\phi 2.5 \phi .098$			UZFRF89 With sleeve 90mm 3.543inch
	Small sensing probe	 $\phi 2.5 \phi .098$			UZFRF84 With sleeve 40mm 1.575inch
		 Small diameter $\phi 3 \phi .118$	• Same sensing range as the standard with small sensing probe	Free Cut 2m 6.562ft	UZFRF4
		 $\phi 3 \phi .118$			UZFRF49 With sleeve 90mm 3.543inch
		 $\phi 2.5 \phi .098$			UZFRF44 With sleeve 40mm 1.575inch
	Small diameter	 $\phi 2.5 \phi .098$	• Suitable for sensing in the intricate apparatus • Free cuttable type	Free Cut 2m 6.562ft	UZFRS4
		 With sleeve $\phi 1.48 \phi .058$			UZFRF4
		 $\phi 2.5 \phi .098$			UZFRF49 With sleeve 90mm 3.543inch
	High precision	 Lens applicable	• A highly precise positioning is possible with coaxial reflective mode	Free Cut 2m 6.562ft	UZFRG4
		 Coaxial Small diameter $\phi 3 \phi .118$			UZFRG4
	Array	 Top sensing $\phi 20 \phi .787$	• Approx. $\phi 0.3\text{mm } \phi .012\text{inch}$ is achieved by means of combining with ultra-small spot lens UZFMR3	500mm 19.685inch	UZFREG1
		 Side sensing $\phi 20 \phi .787$			UZFREG1

(*1) : The sensing range is defined as the range until the saturation indicator lights up. With the reflective fibers, it is specified with using white non-glossy paper (50×50mm 1.969×1.969inch). (**UZFR8B** : 100×100mm 3.937×3.937inch)

OPTION


Designation		Model No.	Description
For thru-beam fiber	Long sensing range lens	UZFXLE1	Six times longer or more • Sensing range (Two lenses on both sides)(*1) : 900mm 35.433inch (UZFTB8), 750mm 29.528inch (UZFTF8 , UZFTT8)
	Ultra-long sensing range lens	UZFXLE2	The farthest expansion with large aperture lenses • Sensing range (Two lenses on both sides)(*1) : 3,000mm 118.11inch (UZFTB8), 2,500mm 98.425inch (UZFTF8)
	Side-view lens	UZFXSV1	Beam axis is bent by 90°. • Sensing range (Two lenses on both sides)(*1) : 220mm 8.661inch (UZFTB8), 200mm 7.874inch (UZFTF8 , UZFTT8)
For reflective fiber	Pinpoint spot lens	UZFXMR1	Pinpoint spot of $\phi 0.5\text{mm}$ $\phi .020\text{inch}$ • Applicable fiber : UZFRG4 • Distance to focal point : $6 \pm 1\text{mm}$ $.236 \pm .039\text{mm}$
	Zoom lens	UZFXMR2	The spot diameter is adjustable from $\phi 0.7$ to $\phi 2\text{mm}$ $\phi .028$ to $\phi .079\text{inch}$ according to how much it is screwed in. • Applicable fiber : UZFRG4 • Distance to focal point : Approx. 18.5 to 43mm .728 to 1.693inch (Screw-in depth : 7 to 14mm .276 to .551inch) • Spot diameter : $\phi 0.7$ to $\phi 2\text{mm}$ $\phi .028$ to $\phi .079\text{inch}$ (Screw-in depth : 7 to 14mm .276 to .551inch)
	Ultra-small pinpoint lens	UZFXMR3	Finest spot of $\phi 0.3\text{mm}$ $\phi .012\text{inch}$ • Applicable fiber : UZFREG1 , UZFRG4 • Distance to focal point : $7.5 \pm 0.5\text{mm}$ $.295 \pm .020\text{inch}$ • Spot diameter : $\phi 0.3\text{mm}$ $\phi .012\text{inch}$ (UZFREG1), $\phi 0.5\text{mm}$ $\phi .020\text{inch}$ (UZFRG4)

(*1) : The sensing range is defined as the range until the saturation indicator lights up.

Long sensing range lens



Ultra-long sensing range lens




Side-view lens




Pinpoint spot lens



Zoom lens



Ultra-small pinpoint lens



SPECIFICATIONS

Fibers

Item	Type	Standard, Small fiber head, Small diameter, Long sensing range with lenses, Array, and High precision
Allowable bending radius		R25mm .984inch or more
Ambient temperature		-40 to +70°C -40 to +158°F (UZFREG1 : -20 to +60°C -4 to +140°F) (No dew condensation nor icing allowed)
Ambient humidity		35 to 85%RH
Material		Fiber core : Acrylic, Sheath : Polyethylene Fiber head : Brass with nickel-plated (Threaded part of standard, Threaded part of small diameter, High precision, Array) SUS (UZFTS8 , Small fiber head, UZFTS4 , UZFTL8 , UZFRS4 , Sleeve part of sleeve-attached fiber)
Accessories		Threaded head fiber : 2 pcs. of nuts (thru-beam type : 4pcs.) and 1 pc. of toothed lock washer (thru-beam type : 2pcs.) Free-cut fiber : 1 pc. of UZFXCT1 (Fiber cutter) Small diameter and high precision of free-cut fiber : 2 sets of plug attachments

SPECIFICATIONS

Amplifier


Item	Model No.	UZF36
Supply voltage		12 to 24V DC $\pm 10\%$ Ripple P-P 10% or less
Current consumption		35mA or less
Analog output		Analog voltage • Output voltage : 1 to 5V (proportional to incident beam) • Output current : 5mA or less • Output impedance : 47 Ω • Load resistance : 2k Ω or more • Temperature characteristic : 0.3% F.S. / $^{\circ}\text{C}$ or less
Response time (*1)		Switchable either 1ms or less or 10ms or less
Incident beam indicator		Red LED (brightens up in proportion to analog output voltage)
Saturation indicator		Green LED (lights up when the analog output voltage reaches 5V)
Sensitivity adjuster		8-turn adjuster with the pointer
Automatic crosstalk prevention function		Incorporated
Environmental resistance	Ambient temperature	- 10 to + 55 $^{\circ}\text{C}$ + 14 to + 131 $^{\circ}\text{F}$ (No dew condensation nor icing allowed)
	Ambient humidity	35 to 85%RH, Storage : 35 to 85%RH
	Ambient illuminance (Extraneous light immunity)	Sun light : 1,000lx at the light-receiving face, Incandescent light : 1,000lx at the light-receiving face
	Noise immunity	Power line : 240Vp, 10ms cycle, and 0.5 μs pulse duration, Radiation : 300Vp, 10ms cycle, and 0.5 μs pulse duration (with noise simulator)
	Voltage withstandability	1,000V AC for one min. between all terminals connected and enclosure (*1)
	Insulation resistivity	20M Ω or more at 250V DC Megger between all terminals connected and enclosure (*1)
	Vibration-proof	10 to 150Hz frequency, 0.75mm amplitude, and X, Y, and Z directions each for two hours (unenergized)
	Shock-proof	100m/s ² acceleration {approx. 10G}, and X, Y, and Z directions each for five times (unenergized)
Emitting element		Red LED (modulated)
Material		Enclosure : Heat-resistant ABS, Case cover : Polycarbonate, Fiber lock lever : PPS
Cable		Cabletyre cable 2m 6.562ft long with four 0.2mm ² conductors
Cable extension		Maximum extension is 100m 328.084ft overall with an equivalent cable with conductors 0.3mm ² or more (*2)
Weight		Approx. 60g 2.12oz
Accessories		UZF811 (Mounting bracket) : 1pc., Adjusting screw-driver : 1pc.

(*1) : The voltage withstandability and the insulation resistivity described in the above table are inherent in the **UZF36** amplifier only.

(*2) : Pay attention that the voltage drops when the cable is extended.


I/O CIRCUIT AND WIRING DIAGRAMS

I/O circuit diagram




Symbol . . . D1 : Reverse polarity protection diode
D2, D3 : Surge absorption diode

Wiring diagram




SENSING FIELDS (TYPICAL)

Correlation between setting distance and output voltage




Correlation between setting distance and output voltage with UZFXLE1 applied on both sides



SENSING FIELDS (TYPICAL)

Correlation between setting distance and output voltage with UZFXSV1 applied on both sides



PRECAUTIONS FOR PROPER USE

Amplifier




These products are **not** safety sensors and are **not** designed or intended to be used to protect life and prevent bodily injury or property damage.

Mounting


How to mount the amplifier

- ① Hook the rear part to the attached mounting bracket (**UZF811**) or DIN rail.
- ② Press the amplifier down on the bracket or DIN rail.




How to remove the amplifier

- ① Push the amplifier frontward.
- ② With keeping on it, lift up the front part of the amplifier.




How to connect fiber cables

- ① Unlock the fiber lock lever upright.
- ② Insert fiber cables into the inlets slowly until fully deepened.
- ③ Lock the fiber lock lever on the original position.




(*1) : With the coaxial diffuse fiber such as the **UZFRG4** or the **UZFRF8**, insert the mono-core fiber cable into the beam-emitting inlet and the multi-core fiber cable into the beam-receiving inlet. If they are inserted in opposition, the repeatability will deteriorate.




Crosstalk prevention function

- Two sets of fibers can be mounted close together that connected to the **UZF36** amplifiers because of the crosstalk prevention function. Two sets of the **UZF36** amplifiers should be set the wiring and switches on them as follows.



1) Wiring

- Connect both crosstalk prevention wires together under both 0V wires in common.



2) Crosstalk prevention selection switch


- Set the crosstalk prevention selection switch on "MAIN" for the first amplifier and on "SUB" for the second amplifier.
- * To neglect crosstalk prevention function
 - If the amplifier is used singly, set the crosstalk prevention selection switch on "MAIN", otherwise it is not operable.
 - Insulate the crosstalk prevention wire.

PRECAUTIONS FOR PROPER USE


Amplifier

Response time selection

- The response time of the **UZF36** can be selected either "1ms" or "10ms". If your detecting application does not need the quick response, "10ms" is recommended as it makes the detection secure against inductive noises and ambient lights. If you choose "1ms", pay attention to inductive noises and ambient lights.
- The response time stands for the processing time that the output follows to an input change, either from the complete Dark level (1V) up to 90% extent of a certain Light level or from the Light level down to the complete Dark level 10% extent beforehand. The response time of the **UZF36** is constant regardless of the amplitude of the output voltage. The usage with "10ms" is recommended to gain the output reliability if you do not require quick response. When you select "1ms", carefully consider the influence of extraneous lights or inductive noises.



Designation



Sensitivity adjustment

Procedure	Adjusting	Sensitivity adjuster
(1)	Turn the sensitivity adjuster counterclockwise fully up to the minimum sensitivity.	
(2)	Adjust the relative positions between fiber heads or between the fiber head and an object so as to receive as much the incident beam as possible. Thru-beam fibers Perfect beam-alignment Diffuse-reflective fibers The largest amount of reflected beam	
(3)	Turn the sensitivity adjuster clockwise until the saturation indicator lights up. Once it lights up, turn the sensitivity adjuster counterclockwise until the saturation indicator lights off. This is the point most sensitive before the saturation.	

Others


- The transient time duration is 50ms after power-up.

DIMENSIONS (Unit: mm inch)

UZF36


Amplifier

Assembled dimensions with attached mounting bracket



UZF811

Amplifier mounting bracket (Accessory for UZF36)



Material : SPCC (Uni-chrome plated)