

3/2-way; G 1/8, G 1/4 and sub-base connection;
DN 1.2 – 2.5 mm; flow rate: up to 175 l/min



Advantages/Benefits

- ▶ EEx m II T4, T5 and T6 or EEx me II T4, T5 and T6 approved
- ▶ Coil can be changed easily with valve in place
- ▶ Coil can be locked in 4 x 90° positions or freely moved in between, as required
- ▶ Medium is only in contact with the valve internals and body
- ▶ High-quality seal material FPM (Viton) as standard

Design/Function

The valve type 6014 is based on a modular concept comprising two basic elements: Valve body and push-over coil with moulded-in cable or with terminal box.

The valve consists of a body to which the armature guide tube, containing the plunger, seals and springs, is attached.

The coil is pushed over the guide tube and thus isolated from the medium.

The medium is only in contact with the valve internals and body.


Valve bodies are available in polyamide, brass or stainless steel. All valves have high quality viton (FPM) seals as standard.



Applications

Applications:

- Chemical industry
- Pharmaceutical processing equipment
- Industrial waste water treatment
- Oil and gas industry



Mechanical System
(Process + Pilot Valve)

burkert
Fluid Control Systems


Technical Data Type 6014 Ex

Circuit functions

C 3/2-way valve,
when de-energized, outlet A
pressure relieved



T Universal mixer or distributor valve,
when de-energized R $\leftrightarrow$ A open
and P $\leftrightarrow$ A closed,
for universal use



Specifications

Circuit function	Orifice DN [mm]	Flow rate Q _{Nn} -Value (air) [l/min]	Coil size [mm]	Power consumption [W]	Response times ¹⁾		Pressure range [bar]
					opening [ms]	closing [ms]	
C	1.2	55	40	1.8	10 – 15	15 – 20	0 – 10
C	1.2	55	32	3.0	10 – 15	15 – 20	0 – 10
C	1.5	75	32	7.0	10 – 15	15 – 20	0 – 10
C	2.0	120	32	7.0	10 – 15	15 – 20	0 – 6
C	2.0	120	40	9.0	10 – 15	15 – 20	0 – 10
C	2.5	175	40	9.0	15 – 20	10 – 22	0 – 6
T	1.5	75	40	9.0	10 – 15	15 – 20	0 – 7

¹⁾ When using electronics (diodes for controlling LEDs or for rectifying), the closing time is delayed 8 up to 10 ms.

Flow rate: Q_{Nn}-Value air [l/min]

Measured at +20°C, 6 bar pressure at valve inlet and 1 bar pressure difference

Pressure ranges [bar]

Measured as overpressure to the atmospheric pressure

Response times [ms]

Measured at valve outlet at 6 bar and +20°C

Opening Pressure rise from 0 to 90%
Closing Pressure drop from 100 to 10%

Operating Data (Valve)

Valve body	Brass Stainless Steel PA
Seal material	FPM (Viton)
Pressure range	0-10 bar max. (see specifications)
Port connection	G 1/8, G 1/4 and Sub-base connection
Orifice	DN 1.2, 1.5, 2.0 and 2.5 mm
Fluid	Neutral gases and fluids as e.g. compressed air, town and natural gas, water, hydraulic oil, technical vacuum
Medium temperature	-10 up to +90°C
Max. ambient temperature	
Single valve	T4 & T5: -30 up to +60°C
Block mounted	T4: -30 up to +40°C T5: -30 up to +50°C T6: -30 up to +60°C
Max. viscosity	21 mm ² /s
Installation	As required, but preferably with solenoid system upright

Operating Data (Actuator)

Operating voltages 24, 110, 230 V/UC

Voltage tolerance $\pm 10\%$

Power consumption (PC)

Temperature class	T4 coil	T4 coil	T5 coil	T6 coil
Coil size	32 mm	40 mm	32 mm	40 mm
PC	7 W	9 W	3 W	1.8 W

Duty cycle 100 % continuously rated

Cycling rate Up to 1 000 c.p.m.

Rating IP 65

Ex-approval EEx m II T4, T5 and T6 or
EEx me II T4, T5 and T6
(EExi see data sheet
6014 EExi)

Specifications - Ordering Chart (Other Versions on Request)

6014 Ex-coil with moulded-in cable (3 m length)

Circuit function	Orifice DN [mm]	Manual override	Port connection	Coil [mm]	Power consumption [W]	Pressure range [bar] ^{1) 2)}	Body material	Seal material	Ex-approval	Item-No. Voltage		
										024/UC	110/UC	230/UC

For manifold mounting:

C	1.2*	YES	Sub-base	32.0	3.0	0 – 10	PA	FPM	EEx m II T5	140 002 G	140 003 H	140 004 A
C	1.5	YES	Sub-base	32.0	7.0	0 – 10	PA	FPM	EEx m II T4	136 100 T	136 101 Q	136 102 R
C	1.5	YES	Sub-base	32.0	7.0	0 – 10	Brass	FPM	EEx m II T4	136 106 M	136 107 N	136 108 X
C	2.0	YES	Sub-base	32.0	7.0	0 – 6	Brass	FPM	EEx m II T4	136 109 Y	136 110 L	136 111 H

For single mounting:

C	1.2*	YES	Sub-base	32.0	3.0	0 – 10	PA	FPM	EEx m II T5	136 103 J	136 104 K	136 105 L
C	1.2*	YES	Sub-base	40.0	1.8	0 – 10	PA	FPM	EEx m II T6	136 552 K	136 553 L	136 554 M
C	2.0	NO	G 1/8	40.0	9.0	0 – 10	Brass	FPM	EEx m II T4	136 076 R	136 077 J	136 078 T
C	2.0	NO	G 1/4	40.0	9.0	0 – 10	Brass	FPM	EEx m II T4	136 079 U	136 080 J	136 081 F
C	2.5	NO	G 1/8	40.0	9.0	0 – 6	Brass	FPM	EEx m II T4	136 082 G	136 083 H	136 084 A
C	2.5	NO	G 1/4	40.0	9.0	0 – 6	Brass	FPM	EEx m II T4	136 085 B	136 086 C	136 087 D
C	2.0	YES	G 1/8	40.0	9.0	0 – 10	Brass	FPM	EEx m II T4	136 088 N	136 089 P	136 090 L
C	2.0	YES	G 1/4	40.0	9.0	0 – 10	Brass	FPM	EEx m II T4	136 091 H	136 092 A	136 093 B
C	2.5	YES	G 1/8	40.0	9.0	0 – 6	Brass	FPM	EEx m II T4	139 981 M	139 982 N	139 983 P
C	2.5	YES	G 1/4	40.0	9.0	0 – 6	Brass	FPM	EEx m II T4	139 987 K	139 988 U	139 989 V
C	2.0	NO	G 1/8	40.0	9.0	0 – 10	SS	FPM	EEx m II T4	136 112 A	136 113 B	136 114 C
C	2.0	NO	G 1/4	40.0	9.0	0 – 10	SS	FPM	EEx m II T4	136 115 D	136 116 E	136 117 F
T	1.5	NO	G 1/8	40.0	9.0	0 – 7	Brass	FPM	EEx m II T4	136 094 C	136 095 D	136 096 E
T	1.5	NO	G 1/4	40.0	9.0	0 – 7	Brass	FPM	EEx m II T4	136 097 F	136 098 Q	136 099 R
T	1.5	NO	G 1/8	40.0	9.0	0 – 7	SS	FPM	EEx m II T4	136 118 Q	136 119 R	136 120 N
T	1.5	NO	G 1/4	40.0	9.0	0 – 7	SS	FPM	EEx m II T4	136 121 B	136 122 C	136 123 D

6014 Ex-coil with terminal box

Circuit function	Orifice DN [mm]	Manual override	Port connection	Coil [mm]	Power consumption [W]	Pressure range [bar] ^{1) 2)}	Body material	Seal material	Ex-approval	Item-No. Voltage		
										024/UC	110/UC	230/UC

For single mounting:


C	1.2*	YES	Sub-base	32.0	3.0	0 – 10	PA	FPM	EEx me II T5	139 999 X	140 000 J	140 001 F
C	1.2*	YES	Sub-base	40.0	1.8	0 – 10	PA	FPM	EEx me II T6	140 005 B	140 006 C	140 007 D
C	1.5	YES	Sub-base	32.0	7.0	0 – 10	PA	FPM	EEx me II T4	139 996 L	139 997 M	139 998 W
C	2.0	NO	G 1/8	40.0	9.0	0 – 10	Brass	FPM	EEx me II T4	139 963 S	139 964 T	139 965 U
C	2.0	NO	G 1/4	40.0	9.0	0 – 10	Brass	FPM	EEx me II T4	139 966 V	139 967 W	139 968 F
C	2.5	NO	G 1/8	40.0	9.0	0 – 6	Brass	FPM	EEx me II T4	139 969 G	139 970 D	139 971 S
C	2.5	NO	G 1/4	40.0	9.0	0 – 6	Brass	FPM	EEx me II T4	139 972 T	139 973 U	139 974 V
C	2.0	YES	G 1/8	40.0	9.0	0 – 10	Brass	FPM	EEx me II T4	139 975 W	139 976 X	139 977 Y
C	2.0	YES	G 1/4	40.0	9.0	0 – 10	Brass	FPM	EEx me II T4	139 978 H	139 979 A	139 980 Y
C	2.5	YES	G 1/8	40.0	9.0	0 – 6	Brass	FPM	EEx me II T4	139 984 Q	139 985 R	139 986 J
C	2.5	YES	G 1/4	40.0	9.0	0 – 6	Brass	FPM	EEx me II T4	139 990 S	139 991 P	139 992 Q
C	2.0	NO	G 1/8	40.0	9.0	0 – 10	SS	FPM	EEx me II T4	140 011 Y	140 012 Z	140 013 S
C	2.0	NO	G 1/4	40.0	9.0	0 – 10	SS	FPM	EEx me II T4	140 014 T	140 015 U	140 016 V
T	1.5	NO	G 1/8	40.0	9.0	0 – 7	Brass	FPM	EEx me II T4	139 993 R	139 994 J	139 995 K
T	1.5	NO	G 1/8	40.0	9.0	0 – 7	SS	FPM	EEx me II T4	140 017 W	140 018 F	140 019 G
T	1.5	NO	G 1/4	40.0	9.0	0 – 7	SS	FPM	EEx me II T4	140 020 D	140 021 S	140 022 T

* Circuit function C, DN 1.2 mm: P-orifice 1.2 mm, exhaust orifice 1.5 mm


¹⁾ Measured with 6 bar upstream pressure and 1 bar pressure drop across the valve at +20 °C.²⁾ All pressures quoted are gauge pressures with respect to the prevailing atmospheric pressure.

Dimensions (mm)


With cable




With terminal box



Threaded version




Sub-base version




	Armature						Coil size
	A	B	C	D	E	F	
Threaded Port	1/8	32	20.8	32.6	32	45	32
	1/4	46	26.8	49	40	51	40
Sub-base	1/8	32	14.3	32.6	32	45	32

Dimensions Accessories (mm)

Single manifold



Multiple manifold



Multiple manifold

The pressure port of the manifold is marked with P (R), the outlet port with A (B). Only similar ports can be coupled together. Unused connections to be plugged (see accessories). Manifolds may be coupled together using special push-fit O-ring connection nipples for linking the pressure inlets P (R). Manifolds joined together in this way should be securely mounted.

Ordering Chart for Manifolds/Accessories

Device/Accessory	Features			Item-No.
Single manifold	Aluminium			005 020 W
Multiple manifold (aluminium)	Hole spacing A	Overall length B	Hole spacing C	
2 valves	57	65	—	005 023 M
3 valves	90	98	—	005 286 S
4 valves	123	131	—	005 287 T
5 valves	156	164	57	005 035 R
6 valves	189	197	57	005 038 U
8 valves	255	263	57	005 386 W
10 valves	321	329	90	005 764 G
Connector nipples	with O-rings			005 040 A
Blanking screw	with seal ring, G 1/8			005 041 X
Blanking plug	with screws + O-ring			005 630 E