


- Samples can deviate in the execution from the serie.



Tab material: Isotan (54%Cu,44%Ni,Mn)

All framed values will be used for dimension checking !

- Dimensions and tolerances can be specified only after the testing of the devices for the mass production definitely

Rev.	☐			Rev.	☐			 	Customer's Approval			
Rev.	☐			Rev.	☐				Date			
Rev.	☐			Rev.	☐				Signature			
Titel: CR1025SM								Scale 2:1	Drawn	02.11.07	SRI	
									Checked	02.11.07	BBö	
									Approved	16.11.07	MHo	
renata batteries								CH-4452 Itingen Switzerland		3.9192.4-		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Renata:](#)

[CR1025SM](#)