# BLDC Motors & Drives





- High performance, low cost, brushless speed control systems
- 30 to 105 watts continuous shaft output
- Operates from 12 to 48V DC power supply
- Driver can supply up to 6.25A continuous, 12.5A peak
- Excellent speed stability
- Eight digital inputs for commanding a variety of functions
- Two digital outputs for interfacing to other equipment
- Two on board potentiometers plus 12 bit analog input for setting speed, acceleration, deceleration






- High performance, low cost speed control drive
- Operates from 12 to 48V DC power supply
- Output current: up to 6.25Arms continuous, 12.5A peak
- Eight digital inputs for commanding a variety of functions
- Two digital outputs for interfacing to other equipment
- Two on board potentiometers plus 12 bit analog input for setting speed, acceleration, deceleration


CE ROHS


For more information go to www.applied-motion.com/BLDC

# **IO Connections**



# **BD5 Dimensions**







# **Brushless Drive Technical Specifications**

#### POWER AMPLIFIER:

AMPLIFIER TYPE	Triple half bridge, 4 quadrant						
CURRENT CONTROL	ate PWM at 10 kHz						
OUTPUT CURRENT	BD5-G1-AH: 1.75Arms cont, 3.5Arms peak (5 seconds max)						
	BD5-G2-AH: 3.6Arms cont, 7.2Arms peak (5 seconds max)						
	BD5-G3-AH: 6.25Arms cont, 12.5Arms peak (5 seconds max)						
POWER SUPPLY	External 12 - 48 VDC power supply required						
	Under-voltage alarm: 8.5 VDC						
	Over-voltage shutdown: 62 VDC						

#### CONTROLLER:

MODE OF OPERATION	Velocity control. Speed can be selected by digital input from on-board potentiometer, external analog signal, or 7 preset speeds. Accel/decel rate set by on-board potentiometer						
DIGITAL INPUTS	Eight inputs, 5-24 VDC, bidirectional (can be driven by sinking or sourcing signals) 2 kHz max freq response. Common terminal (INCOM) can be connected to an external power supply (5 to 24 VDC), or internally connected to 5V or GND (selected by internal DIP switches)  CW/CCW: selects direction of motor shaft rotation  STP: commands motor to stop quickly using electromagnetic braking  EN/RE: removes power from motor windings  M0,M1,M2: selects one of seven preset speeds  STMD: selects which mode of stopping is used  SPST: selects whether speed is set by on-board pot or external analog signal						
DIGITAL OUTPUTS	30 VDC max, 80 mA max, open collector, open emitter.  FLT is a dedicated fault output.  SPO is a dedicated tachometer output (30 pulses per revolution).  Both outputs can be reconfigred at the factory for qualified OEM applications.						
ANALOG INPUT	AIN referenced to GND, Range = 0 to 5 VDC, Resolution = 12 bits, 5v = 4500 rpm.						
COMMUNICATION INTERFACE	RS-232 (for factory configuration only)						

#### APPROVALS:

AGENCY APPROVALS	RoHS
	CE PENDING

#### PHYSICAL:

OPERATING TEMPERATURE	0 to 100°C (32 to 212°F) Internal temperature of the electronics section					
AMBIENT TEMPERATURE	to 40°C (32 to 104°F) When mounted to a suitable heatsink					
HUMIDITY	90% max, non-condensing					
MASS	6.0 oz (170 g)					








# **Motor Specifications**

PART #	POWER	RELATED VOLTAGE	RATED CURRENT		RATED T	ORQUE	KE	ROTOR INERTIA	MASS
	W cont.	VDC	A cont.	A peak	N-M cont.	N-M peak	V/krpm	g-cm <sup>2</sup>	g
BL030-H03-G	30	24	1.75	3.5	0.065	0.13	3.65	38.8	320
BL060-H03-G	60	24	3.6	7.2	0.13	0.26	2.7	72	550
BL105-H03-G	105	24	6.25	12.5	0.225	0.45	2.65	114	830


# **Motor Dimensions**





# **BLDC Drive Part Numbering System**

# BD5-G1-AH



Feedback

H = Hall devices

Communication

A = RS-232 (for factory configuration only)

BL105-H03-G

Motor Winding

1 = 30 W, 24 V

2 = 60 W, 24 V

3 = 105 W, 24 V

Order this BD5 model...

1. BD5-G1-AH

2. BD5-G2-AH

3. BD5-G3-AH

For use with this BL motor...


1. BL030-H03-G


2. BL060-H03-G

3. BL105-H03-G

# **BLDC Motor Part Numbering System**

#### BL000-000-0 Series -BL = Brushless DC Motor **Frame Size** G = 42mm**Voltage** Wattage Rating 3 = 24 VDC030 = 30 watts060 = 60 watts105 = 105 watts RESERVED **Standard Part Numbers:** Feedback H = Hall devices only BL030-H03-G BL060-H03-G







# **Accessories**

#### **Power Supplies**

Applied Motion offers the following DC power supplies for use with the brushless DC drives and motors.

PS50A24: 50 Watts at 24 VDC, recommended for BL030-H03-G motor. PS150A24: 150 Watts at 24 VDC, recommended for BL060-H03-G motor. PS320A48: 320 Watts at 48 VDC, recommended for BL105-H03-G motor.






#### **RC-050 Regeneration Clamp**

The RC-050 regeneration clamp is for use where regeneration from the motor may be excessive for the power supply. In these cases the RC-050 is connected between the drive and power supply and absorbs regenerated energy.

#### **Extension Cable**

For applications where motors and drives are separated by more than 30cm (1 foot)







404 Westridge Dr. Watsonville, CA 95076 Tel: 800-525-1609

Fax: 831-761-6544 www.applied-motion.com DISTRIBUTED BY:

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

#### **Applied Motion:**

BD5-G1-AH BD5-G2-AH BD5-G3-AH BL030-H03-G BL030-H03-GP005 BL030-H03-GP014 BL030-H03-GP019 BL030-H03-GP029 BL030-H03-GP051 BL030-H03-GP100 BL060-H03-G BL060-H03-GP005 BL060-H03-GP014 BL060-H03-GP019 BL060-H03-GP051 BL105-H03-G BL105-H03-GP005 BL105-H03-GP014 BL180-H04-H BL120-H03-H BD10-I8-AH BD10-H5-AH BL300-H04-I BL060-H03-H BL090-H03-G BD10-I7-AH BL100-H03-I