Honeywell Sensing and Control

Search

narrow your search

- **Products** ? Controls and Monitoring
- ? Machine Safety (865) ? Sensors (5919)
- Switches (9620)
- ? Wireless (45)

Technology

- ? Electromechanical(9137)
- Magnetic (534)
- Microstructure (1830)
- Platinum thin film(56)
- Thick Film(1372) More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site WGLA and WPMM XYR6000™

find out more

White Papers

Wireless Switches Offer **Unlimited Benefit**

Basic Switches Are Not Created

Applying Precision Switches

Sensors for Medical Devices

New Ways to Measure Torque

Choosing Safety Switches Specifying Hour Meters

Need Help?

Click here to contact us

HAFRSF0200C2AX5

(Home: Products: Sensors » Airflow Sensors » HAF)

Documentation

compensation provides digital (*C) outputs with a response time of 1 ms.

precise and calculated airflow channel to provide repeatable flow response.

are designed and manufactured according to ISO 9001 standards.



Honeywell Zephyr™ Digital Airflow Sensors: HAF Series -High Accuracy, bidirectional flow, short port, fastener mount, 200 SCCM flow range, digital I ²C address: 0x29, 5.0 Vdc supply

Actual product appearance may vary.

Specs

Application Specific Integrated Circuit (ASIC).

Overview

Sales & Service 2

Application Notes

Honeywell Zephyr™ Digital Airflow Sensors: HAF Series -High Accuracy, provide a digital interface for

Zephyr™ sensors are designed to measure mass flow of air and other non -corrosive gases. They are

The HAF Series is compensated over the temperature range of 0 °C to 50 °C [32 °F to 122 °F] and

These sensors operate on the heat transfer principle to measure mass airflow. They consist of a

Zephyr™ sensors provide customers with enhanced reliability, digital accuracy, repeatable

microbridge Microelectronic and Microelectromechanical System (MEMS) with temperatureensitive

resistors deposited with thin films of platinum and silicon nitride. The MEMS sensing die is located in a

measurements and the ability to customize sensor options to meet many specific application needs. The

combination of rugged housings with a stable substrate makes these products extremely robust. They

available in standard flow ranges and are fully calibrated and temperature compensated with an on-board

operates across a temperature range of -20 °C to 70 °C [4 °F to 158 °F]. The stateof-the-art ASIC-based

reading airflow over the specified full scale flow span and temperature range. Their thermally isolated heater and temperature sensing elements help these sensors provide a fast response to air or gas flow.

Distributor Inventory

Meet Dr. Larry

My Links

Meet Dr. Larry

contacts

Login to iCOM Login to Rep/AD Portal Login to Digital University

Customer Service

Technical Support

View Site Demo

Site Comments?

VIDEO- Dr. Larry

Goldstein explains

best technologies.

our newest and

SENSORS

Global Sales & Service

News Center

HONEYWELL INTRODUCES NEW HUMIDICON™ DIGITAL HUMIDITY/TEMPERATURE

HONEYWELL EXPANDS **INDUSTRYLEADING** TRUSTABILIT® PLATFORM WITH NEW BOARD MOUNT **ULTRALOW PRESSURE SENSORS**

HONEYWELL INTRODUCES TRUSTABILITY NSC SERIES, UNCOMPENSATED / UNAMPLIFIE **BOARD MOUNT PRESSURE SENSORS**



MICRO SWITCH Anniversary site

Potential Applications

Potential Applications

- Ventricular assist devices
- Hospital diagnostics (spectrometry, gas
- (respiratory monitoring)
- Ventilators
- Air-to-fuel ratio
- (spectrometry,
- Fuel cells
- Gas leak detection
- VAV system on HVAC systems
- Meteorolgy

Features

Features and Benefits

- ? High ±2.5% accuracy allows for very precise airflow measurement, often ideal for demanding applications with high accuracy requirements
- Full calibration and temperature compensation typically allow customer to remove additional components associated with signal conditioning from the PCB, reducing PCB size as well as costs often associated with those components (e.g., acquisition, inventory, assembly)
- Customizable for specific end-user needs
- High sensitivity at very low s allows a custome application to detect presence or absence of airflow
- High stability reduces errors due to thermal effects and null shift to provide accurate readings over time, often eliminating need for system calibration after PCB mount and periodically over time
- ? Low pressure drop typically improves patient comfort in medical applications, and reduces noise and system wear on other components such as motors and pumps
- Linear output provides more intuitive sensor signal than the raw output of basic airflow sensors, which can help reduce production costs, design, and implementation
- Fast response time allows a customer's application to respond quickly to airflow change, important in critical medical (i.e., anesthesia) and industrial (i.e., fume hood) applications
- High 12-bit resolution increases ability to sense small airflow changes, allowing customers to more precisely control their application
- Low 3.3 Vdc operating voltage option and low power consumption allow for use in battery-driven and other portable applications
- ASIC-based PC digital output compatibility eases integration to microprocessors or microcontrollers, reducing PCB complexity and component count
- Bidirectional flow sensing capability eliminates the need for two airflow sensors, helping to reduce production
- costs and implementation time Insensitivity to mounting orientation allows customer to position sensor in most optimal point in the system, eliminating concern for positional effects
- Insensitivity to altitude eliminates customer implemented altitude adjustments in the system, easing integration and reducing production costs by not having to purchase additional sensors for altitude adjustments
- Small size occupies less space on PCB, allowing easier fit and potentially reducing production costs; PCB size may also be reduced for easier fit into space-constrained applications
- RoHS-compliant materials meet Directive 2002/95/EC

Medical

- Anesthesia delivery machines
- (heart pumps)
- chromatography)
- Nebulizers
- Oxygen concentrators
- Patient monitoring systems
- Sleep apnea machines
- Spirometers
- Industrial
- Analytical instrumentation chromatography)
- Gas meters
 - **HVAC** filters